

# 204679A-8



Boot Assembly, 4 in, for 2-1/4 in corrugated coaxial cable

**OBSOLETE**

**Replaced By:**

SEC-1214

SnapSeal™ Entry Cushion with 1 hole for 2-1/4 in corrugated coaxial cable

## Product Classification

<b>Product Type</b>	Boot assembly
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cable Type</b>	Corrugated
<b>Cables per Cushion</b>	1
<b>Color</b>	Black

## Dimensions

<b>Height</b>	101.6 mm   4 in
<b>Length</b>	76.2 mm   3 in
<b>Nominal Size</b>	2-1/4 in

## Material Specifications

<b>Material Type</b>	EPDM rubber
----------------------	-------------

## Environmental Specifications

<b>UV Resistance Test Method</b>	MIL-STD-810E, Procedure 11, Method 505
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours

# 204679A-8

---

**Weather Resistance Test Method**

04AS00-03.9.0 | IEC 60529:2001, IP66

## Packaging and Weights

**Height, packed**

149.86 mm | 5.9 in

**Width, packed**

149.86 mm | 5.9 in

**Length, packed**

78.74 mm | 3.1 in

**Included**

Boot | Cushion | Two clamps

**Packaging quantity**

1

**Weight, gross**

0.64 kg | 1.411 lb