



## Single Entrance Panel for elliptical waveguide 85

### Product Classification

**Product Type** Entrance panel

### General Specifications

**Color** Gray  
**Entry Panel Port Size** 101.6 mm | 4 in  
**Number of Ports** 1  
**Panel Type** Single

### Dimensions

**Height** 76.2 mm | 3 in  
**Width** 127 mm | 5 in  
**Waveguide Size** WR90 | WG16 | R100

### Material Specifications

**Material Type** Aluminum

### Environmental Specifications

**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529.14.2

### Packaging and Weights

**Height, packed** 279.4 mm | 11 in  
**Width, packed** 203.2 mm | 8 in  
**Length, packed** 165.1 mm | 6.5 in  
**Included** Boot | Plate  
**Packaging quantity** 1  
**Weight, gross** 1.28 kg | 2.822 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

## Included Products

- 204673-1 – One 4" Port Entrance Panel 1 x 1
- WGB4-85 – Boot Assembly, 4 in, for elliptical waveguide 85

# 204673-1

---



## One 4" Port Entrance Panel 1 x 1

### Product Classification

<b>Product Type</b>	Entrance panel
<b>Ordering Note</b>	CommScope® non-standard product

### General Specifications

<b>Color</b>	Gray
<b>Entry Panel Port Size</b>	101.6 mm   4 in
<b>Number of Ports</b>	1
<b>Panel Type</b>	Single

### Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	177.8 mm   7 in

### Material Specifications

<b>Material Type</b>	Aluminum
----------------------	----------

### Environmental Specifications

<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66
---------------------------------------	--------------------------------------

### Packaging and Weights

<b>Height, packed</b>	177.8 mm   7 in
<b>Width, packed</b>	177.8 mm   7 in
<b>Length, packed</b>	40.64 mm   1.6 in
<b>Included</b>	Entry cap   Hardware   Port
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.28 kg   0.617 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# WGB4-85

---



Boot Assembly, 4 in, for elliptical waveguide 85

## Product Classification

**Product Type** Boot assembly

## General Specifications

**Cable Type** Elliptical waveguide

**Cables per Cushion** 1

**Color** Black

## Dimensions

**Width** 101.6 mm | 4 in

**Length** 76.2 mm | 3 in

**Waveguide Size** WR90 | WG16 | R100

## Material Specifications

**Material Type** EPDM rubber

## Environmental Specifications

**UV Resistance Test Method** MIL-STD-810E, Procedure 11, Method 557

**Weather Resistance Test Method** 04AS00-03.9.52 | IEC 60529:2001, IP66

## Packaging and Weights

**Height, packed** 193.04 mm | 7.6 in

**Width, packed** 170.18 mm | 6.7 in

**Length, packed** 86.36 mm | 3.4 in

**Included** Boot | Cushion

**Packaging quantity** 1

**Weight, gross** 0.25 kg | 0.551 lb

# WGB4-85

---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

