



Lace-up Hoisting Grip for 2-1/4 in and elliptical waveguide 37

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	660.4 mm 26 in
Leader Length, minimum	355.6 mm 14 in
Nominal Size	2-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel Tin-coated bronze
----------------------	-------------------------------------

Mechanical Specifications

Pull Load Capacity	526.167 kg 1160 lb
---------------------------	----------------------

Packaging and Weights

Height, packed	388.62 mm 15.3 in
Width, packed	83.82 mm 3.3 in

31535

Length, packed	388.62 mm 15.3 in
Packaging quantity	1
Weight, gross	0.77 kg 1.698 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

