

3CCGRIP



Support Hoisting Grip for 1/4 in ATCB-B01 series RET cable

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Support hoisting grip
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	142.24 mm 5.6 in
Leader Length, minimum	76.2 mm 3 in
Nominal Size	1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	PPE
----------------------	-----

Mechanical Specifications

Pull Load Capacity	45.359 kg 100 lb
---------------------------	--------------------

Packaging and Weights

Height, packed	25.4 mm 1 in
Width, packed	254 mm 10 in
Length, packed	203.2 mm 8 in

3CCGRIP

Packaging quantity 1
Weight, gross 0.04 kg | 0.088 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

