## CTBC

### Crimping Tool for CNT-300 and CNT-400 connectors



#### **Product Classification**

Product Type Too

Ordering Note CommScope® non-standard product

## General Specifications

**Application** Crimps the ferrule for CNT® connectors

**Tool Type** Crimp tool

#### Dimensions

**Crimp Die Diameter** 10.16 mm | 0.4 in | 7.62 mm | 0.3 in

Wrench Opening 0 mm | 0 in

### Material Specifications

Material Type Stainless steel

## Mechanical Specifications

**Torque Value** 0 in lb | 0 N-m

## Packaging and Weights

 Height, packed
 20.32 mm | 0.8 in

 Width, packed
 99.06 mm | 3.9 in

 Length, packed
 279.4 mm | 11 in

Packaging quantity 1

**Weight, gross** 0.66 kg | 1.455 lb

Regulatory Compliance/Certifications



# CTBC

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

