

HSR-1-58-MHK-KT-25



Metal Hanger Kit for 1-5/8 in RADIAX® Radiating cable. Designed for 350km/h high speed railway tunnel applications

Product Classification

Product Type	Hanger kit
Product Brand	RADIAX®

General Specifications

Accessories	Hangers
Cable Type	Smoothwall
Color	Silver
Hanger Type	Hanger kits

Dimensions

Compatible Diameter, maximum	50.5 mm 1.988 in
Compatible Diameter, minimum	46.5 mm 1.831 in
Nominal Size	1-5/8 in
Hanger Spacing, maximum	10 m 32.808 ft

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

Packaging and Weights

Height, packed	20 cm 7.874 in
Width, packed	14 cm 5.512 in
Length, packed	30 cm 11.811 in
Packaging quantity	25
Weight, gross	3.27 kg 7.209 lb

HSR-1-58-MHK-KT-25

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- 42396A-2 – Butterfly Hanger for 1-5/8 in coaxial cable
- HSR-MHK-Y – Stand-Off Kit for Metal RADIAX® Cable Hangers