

HSR-MHK-Y



Stand-Off Kit for Metal RADIAX® Cable Hangers

Product Classification

Product Type Hardware kit

General Specifications

Accessories Hardware
Installation Tool 8 mm drill bit required for installation
Thread Size M8

Dimensions

Maximum Stack Height 1
Hole Size 50–55 mm deep

Material Specifications

Material Type Stainless steel

Packaging and Weights

Height, packed 279.4 mm | 11 in
Width, packed 71.12 mm | 2.8 in
Length, packed 220.98 mm | 8.7 in
Packaging quantity 50
Weight, gross 4.001 kg | 8.82 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

HSR-MHK-Y

UK-ROHS

Compliant



Included Products

- HSR-ANCHOR-FHS-S - Stainless Steel Socket Cap Screw
- HSR-ANCHOR-S - Stainless Steel Stud Anchor with washer and hex nut
- HSR-ANCHOR-SW-S - Stainless Steel Spring Washer
- HSR-ANCHOR-W-S - Stainless Steel Flat Washer

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power