

# L1SGRIP

---



Support Hoisting Grip for 1/4 in coaxial cable

## Product Classification

<b>Product Type</b>	Hoisting grip
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Attachment Spacing Intervals</b>	60.96 m   200 ft
<b>Hoisting Grip Type</b>	Support hoisting grip
<b>Installation Tool</b>	Required, not included
<b>Support Clamp</b>	Included
<b>Tool Type</b>	Hoisting grip

## Dimensions

<b>Grip Length, minimum</b>	101.6 mm   4 in
<b>Leader Length, minimum</b>	152.4 mm   6 in
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Stainless steel   Tin-coated bronze
----------------------	-------------------------------------

## Mechanical Specifications

<b>Pull Load Capacity</b>	158.757 kg   350 lb
---------------------------	---------------------

# L1SGRIP

---

## Packaging and Weights

<b>Height, packed</b>	25.4 mm   1 in
<b>Width, packed</b>	177.8 mm   7 in
<b>Length, packed</b>	127 mm   5 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.3 kg   0.661 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

