

L7SGRIP



Support Hoisting Grip for 1-5/8 in coaxial cable

Product Classification

| | |
|----------------------|--|
| Product Type | Hoisting grip |
| Ordering Note | CommScope® standard product in Europe, the Middle East, and Africa CommScope® standard product in Mexico, Central America, and South America CommScope® standard product in the United States and Canada |

General Specifications

| | |
|-------------------------------------|------------------------|
| Attachment Spacing Intervals | 60.96 m 200 ft |
| Hoisting Grip Type | Support hoisting grip |
| Installation Tool | Required, not included |
| Support Clamp | Included |
| Tool Type | Hoisting grip |

Dimensions

| | |
|-------------------------------|------------------|
| Grip Length, minimum | 685.8 mm 27 in |
| Leader Length, minimum | 304.8 mm 12 in |
| Nominal Size | 1-5/8 in |

Electrical Specifications

| | |
|------------------------------------|--------|
| Return Loss Effect, maximum | 0.1 dB |
| DTF Effect, maximum | 0.1 dB |

Material Specifications

| | |
|----------------------|-----------------|
| Material Type | Stainless steel |
|----------------------|-----------------|

Mechanical Specifications

| | |
|---------------------------|---------------------|
| Pull Load Capacity | 430.913 kg 950 lb |
|---------------------------|---------------------|

L7SGRIP

Packaging and Weights

| | |
|---------------------------|-------------------|
| Packaging quantity | 1 |
| Weight, gross | 0.4 kg 0.882 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

