

# PG-RMBH12

---



PIM-Guard Round Member Cable Support Bracket for Block Hangers - Two 3/8" stainless steel threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.

## Product Classification

<b>Product Type</b>	Support bracket
<b>Product Brand</b>	PIM-Guard

## General Specifications

<b>Cable Runs, quantity</b>	12
<b>Mounting</b>	Pipe, 60.3–88.9 mm (2-3/8 in to 3-1/2 in) OD

## Dimensions

<b>Height</b>	38.1 mm   1.5 in
<b>Width</b>	139.7 mm   5.5 in
<b>Length</b>	304.8 mm   12 in
<b>Mounting Diameter, maximum</b>	60.96 mm   2.4 in
<b>Mounting Diameter, minimum</b>	88.9 mm   3.5 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel   Stainless steel
----------------------	--

## Packaging and Weights

<b>Included</b>	Attachment hardware   Clamps   Threaded rod
<b>Packaging quantity</b>	1
<b>Weight, net</b>	2.6 kg   5.732 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



