

SHK-114-1-P



Single Hanger Kit for 1-1/4 in coaxial cable, single stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	1
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	1
Height	61.5 mm 2.421 in
Width	25.9 mm 1.02 in
Length	78.7 mm 3.098 in
Compatible Cable Diameter Range	38.1–40.1 mm
Compatible Diameter, maximum	40.1 mm 1.579 in
Compatible Diameter, minimum	38.1 mm 1.5 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

SHK-114-1-P

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 31.8 cm | 12.52 in

Width, packed 31.8 cm | 12.52 in

Length, packed 7.6 cm | 2.992 in

Included Angle adapter | Hardware

Packaging quantity 1

Weight, gross 0.45 kg | 0.992 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power