SHK-12-2-P



Single Hanger Kit for 1/2 in coaxial cable, double stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	CommScope® non-standard product
General Specifications	
Cables per Hanger	2
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware
Dimensions	
Maximum Stack Height	2
Height	52.1 mm 2.051 in
Width	25.9 mm 1.02 in
Length	46.2 mm 1.819 in
Compatible Cable Diameter Range	15.2-16.3 mm
Compatible Diameter, maximum	16.3 mm 0.642 in
Compatible Diameter, minimum	15.2 mm 0.598 in
Nominal Size	1/2 in
Electrical Specifications	
Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB
Material Specifications	
Material Type	Engineered plastic

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2024



SHK-12-2-P

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
Environmental Specifications	
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degredation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	30.4 cm 11.969 in
Width, packed	27.9 cm 10.984 in
Length, packed	2.5 cm 0.984 in
Included	Angle adapter Hardware
Packaging quantity	1
Weight, gross	0.45 kg 0.992 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2024

