FGS-MSHS-H10



FiberGuide® Horizontal Straight Section, 4x24in, 10ft Length, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type CommScope®

Straight section

Product Brand FiberGuide®

Product Series FGS

General Specifications

Product Feature Slotted

Color Yellow

Orientation Horizontal

Section Type Straight section

Dimensions

 Height
 102 mm | 4.016 in

 Width
 610 mm | 24.016 in

 Length
 3048 mm | 120 in

System Dimensions 102 mm x 610 mm (4 in x 24 in)

Ordering Tree



FGS-MSHS-H10



Section Color

9	empty	yellow
	В	black

Section Length

11	empty	6 ft
	10	10 ft
	12	12 ft

Section Size

10	А	4 x 4 in
	В	4 x 6 in
	С	2 x 2 in
	D	4 x 4 in, slotted duct, 2 in slot spacing
	F	4 x 12 in
	F-CF	4 x 12 in, with center divider
	G	2 x 6 in
	Н	4 x 24 in
	К	2 x 4 in, slotted duct, 2 in slot spacing
	STOR-B	4 x 6 in, with slack storage spools
	STOR-G	2 x 6 in, with slack storage spools
	STOR-F	4 x 12 in, with slack storage spools

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Packaging quantity 2

Weight, net 5.103 kg | 11.25 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

COMMSC PE®

FGS-MSHS-H10



