FJ-3S30U1B0J



Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product TypeWireless Fiber Cable Assemblies

Product Brand HELIAX®

General Specifications

Construction Type Discrete fiber tail

Interface, Connector A LC

Interface Body Style, connector A Straight
Interface, Connector B HMFOC
Interface Feature, connector B Outdoor
Interface Body Style, connector B Straight
Jacket Color Black

Total Fibers, quantity 3

Dimensions


Cable Assembly Length Range (m) 4 - 50

Diameter Over Jacket 5.4 mm | 0.213 in

Ordering Tree



FJ-3S30U1B0J



Optical Specifications

Fiber Type G.657.A2/B2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.75

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Indoor | Outdoor

Packaging and Weights

Cable weight 29 kg/km | 19.487 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

FJ-3S30U1B0J

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of $+20^{\circ}$ C ($+68^{\circ}$ F)

