1RU-SP2132001 | 1RU SPLTR PNL 1X32 UPC/LC



1RU panel, 1X32 split ratio, 1 splitter, LC/UPC connectors

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

Product Type Splitter patch panel

Product Series 1RU

Government Funding Build America Buy America (BABA) compliant*

General Specifications

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Distribution Type 1 x 32 splitter

Interface, Input LC/UPC

Interface, Output LC/UPC

Splitter, quantity 1

Dimensions

 Height
 43.69 mm | 1.72 in

 Width
 482.6 mm | 19 in

 Length
 199.89 mm | 7.87 in

Optical Specifications

Directivity, minimum55 dBPolarization Dependent Loss, maximum0.3 dBUniformity, maximum1.85 dB

Wavelength Range 1260–1650 nm

Insertion Loss, Splitter, maximum 17.5 dB

COMMSCOPE®

1RU-SP2132001 | 1RU SPLTR PNL 1X32 UPC/LC

Return Loss, Splitter, minimum

50 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity 5%–95%, non-condensing

Packaging and Weights

Packaging quantity

