# F1-XMHM-SGW1-D

#### **Base Product**



D-CLASS FSJ1-50A SureFlex® Jumper with interface types Nex10 Male and 4.3-10 Male

WARNING: DO NOT MATE WITH 4.1-9.5 DIN

### **Product Classification**

**Product Type** Wireless transmission cable assembly

Product Brand HELIAX® | SureFlex®

**Product Series** FSJ1-50A

General Specifications

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector ANEX10 MaleInterface, Connector B4.3-10 Male

**Specification Sheet Revision Level** A

Variable Length For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local

CommScope representative

**Dimensions** 

Nominal Size 1/4 in

Logo Image



# F1-XMHM-SGW1-D



# **Electrical Specifications**

**3rd Order IMD Dynamic** -119 dBm

**3rd Order IMD Dynamic Test Method**Two +43 dBm carriers per IEC 62037

### VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
698-960 MHz	1.065	30.04
1700-2200 MHz	1.083	27.99
2500-2700 MHz	1.106	25.96
3400-3800 MHz	1.222	20.01

Jumper Assembly Sample Label



# F1-XMHM-SGW1-D



## **Environmental Specifications**

**Immersion Test Method** 

Meets IEC 60529:2001, IP68 in mated condition

### Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system