

Angle Adapter, compact 3/8 in tapped hole

Product Classification

Product Type Adapter

Ordering Note CommScope® non-standard product

General Specifications

Adapter Type Angle adapter

Mounting 3/8 in tapped hole

Dimensions

Inside Width 16.002 mm | 0.63 in

Outside Width 38.1 mm | 1.5 in

Inside Length 16.002 mm | 0.63 in

Outside Length 46.99 mm | 1.85 in

Material Thickness 2.972 mm | 0.117 in

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Installation Torque, maximum 13 ft lb | 17.626 N-m

Installation Torque, minimum 11 ft lb | 14.914 N-m

Maximum Loading Double stack, 1-5/8 in cable

Packaging and Weights

Height, packed 14 cm | 5.512 in

COMMSCOPE®

243684

Width, packed $14 \text{ cm} \mid 5.512 \text{ in}$ Length, packed $11 \text{ cm} \mid 4.331 \text{ in}$

Packaging quantity 10

Weight, gross 1.32 kg | 2.91 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

