

# 31768A-M

---



Angle Adapter, standard, M10 tapped hole

## Product Classification

<b>Product Type</b>	Adapter
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Adapter Type</b>	Angle adapter
<b>Mounting</b>	M10 tapped hole

## Dimensions

<b>Inside Width</b>	22.352 mm   0.88 in
<b>Outside Width</b>	49.784 mm   1.96 in
<b>Inside Length</b>	22.352 mm   0.88 in
<b>Outside Length</b>	44.958 mm   1.77 in
<b>Material Thickness</b>	4.191 mm   0.165 in

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

<b>Installation Torque, maximum</b>	15 ft lb   20.337 N-m
<b>Installation Torque, minimum</b>	11 ft lb   14.914 N-m
<b>Maximum Loading</b>	Triple stack, 1-5/8 in cable

## Packaging and Weights

<b>Height, packed</b>	14.2 cm   5.591 in
<b>Width, packed</b>	14.2 cm   5.591 in
<b>Length, packed</b>	10.2 cm   4.016 in
<b>Packaging quantity</b>	10

# 31768A-M

---

**Weight, gross** 2.33 kg | 5.137 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system