## U3XQVUCT8

#### **Base Product**



Ultra Low Loss (ULL) OM4 MPO8 APC (Non-Pinned) to Unconnectorized, Fiber Array Cable Assembly, 8-Fiber, LSZH B2ca

#### **Product Classification**

Regional Availability Europe

Portfolio CommScope®

 Product Type
 Fiber array cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

### General Specifications

Connector A, quantity 1

Color, boot AGrayColor, connector AGreenConnector B, quantity0

Construction Type Stranded

Furcation Color Aqua

Interface, Connector A MPO-08/APC Female

Interface, Connector B Unterminated

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 8

#### **Dimensions**


Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999



## U3XQVUCT8

## Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Multimode

Fiber Type OM4, LazrSPEED®

**Environmental Specifications** 

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$ 

**EN50575 CPR Cable EuroClass Fire Performance** B2ca

Environmental Space Indoor | Low Smoke Zero Halogen (LSZH)

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 2 of 3



# U3XQVUCT8

**UK-ROHS** 

Compliant



#### Included Products

760253116 N-008-MP-5K-F08AQ/20T/B2 Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk with 2.0mm Subunits, 8 fiber, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color, B2ca flame rating

860662232 – MPO8,ULL,Multimode,FEMALE,APC,GREEN,2 mm

