



Fiber Optic Pigtail, Simplex, Singlemode, LC/APC to Stub, yellow, 2 m

## Product Classification

|                              |                         |
|------------------------------|-------------------------|
| <b>Regional Availability</b> | EMEA                    |
| <b>Product Type</b>          | Fiber pigtail, jacketed |
| <b>Product Series</b>        | OCP                     |

## General Specifications

|                               |        |
|-------------------------------|--------|
| <b>Color, boot A</b>          | Green  |
| <b>Color, connector A</b>     | Green  |
| <b>Connector A, quantity</b>  | 1      |
| <b>Interface, Connector A</b> | LC/APC |
| <b>Jacket Color</b>           | Yellow |
| <b>Total Fibers, quantity</b> | 1      |

## Dimensions

|                    |                |
|--------------------|----------------|
| <b>Cord Length</b> | 2 m   6.562 ft |
|--------------------|----------------|

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
| <b>Fiber Type</b> | G.657.A1   |

## Environmental Specifications

|                            |                               |
|----------------------------|-------------------------------|
| <b>Environmental Space</b> | Low Smoke Zero Halogen (LSZH) |
|----------------------------|-------------------------------|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| Agency     | Classification                    |
|------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS       | Compliant/Exempted                |

