

RF-NL12-4-96



Non-Penetrating Roof Frame, 12 ft face, Four 3-1/2 in OD x 96 in pipes

Product Classification

Product Type Non-penetrating roof frame

General Specifications

Mounting Non-penetrating
Note Four 96 in x 18 in panel antennas per sector
Pipe, quantity 4

Dimensions

Height 96 in | 2,438.4 mm
Face Width 12.5 ft | 3.81 m
Width 126 in | 3,200.4 mm
Length 8.3 ft | 2.53 m
Pipe Length 96 in | 2,438.4 mm
Pipe Outer Diameter 3.5 in | 88.9 mm

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Rubber mats, with or without pipe mounts

RF-NL12-4-96

Packaging quantity 1
Weight, net 374.1 kg | 824.748 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code