

760231456 | SD-2U



Standard Density 2U sliding Panel, accepts (6) LGX/1000 style splice cassettes, modules or panels, providing up to 72 duplex LC ports

OBSOLETE

This product was discontinued on: October 31, 2022

Replaced By:

760251045	EPX 2U sliding panel, accepts (6) LGX/PNL style splice cassettes, modules or panels, providing up to
EPX-2U-PNL-ENC	72 duplex LC ports

Product Classification

Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	SD

General Specifications

Application	Accepts six LGX/1000 footprint panels/cassettes
Color	Black
Interface, front	Unloaded
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	474.98 mm 18.7 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC) Steel
----------------------	--------------------------------------------------------------------

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Weight, net 7.847 kg | 17.3 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

