



2RU patch panel which interfaces with MPO-8 ports including QSFP to easily break them out into LC connections. The MPO and shuttered LC ports are both front facing for easy mapping and patching. 20 singlemode MPO-8 and 80 duplex LC ports, Enhanced Method

2RU patch panel which interfaces with MPO-8 ports including QSFP to easily break them out into LC connections. The MPO and shuttered LC ports are both front facing for easy mapping and patching. 20 singlemode MPO-8 and 80 duplex LC ports, Enhanced Method B

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FD

General Specifications

Color	Black
Interface, front	LC/UPC MPO
Interface Feature, front	Pinned
Rack Units	2
Shelf Movement	Fixed
Total Ports, quantity	80

Dimensions

Height	82.55 mm 3.25 in
Width	482.6 mm 19 in
Depth	292.1 mm 11.5 in

Optical Specifications

Insertion Loss, maximum	0.6 dB
--------------------------------	--------

Environmental Specifications

Safety Standard	UL 60950
------------------------	----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

