



AMP STACK™ III Connector Half-Tap Kit, dry, 25-pair

OBSOLETE

This product was discontinued on: December 30, 2019

Replaced By:

9-737708-2

AS-25-Halftap-Dry

AMP STACK™ III Connector Half-Tap Kit, dry, 25-pair

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Connector kit

Product Brand

AMP STACK™

Product Series

AMP STACK

Ordering Note

Minimum order quantity, 120 parts

General Specifications

Color

Green ivory | Transparent

Connector Sealant

Dry

Connector Splicing Type

Half-tap

Pairs, quantity

25

Dimensions

Compatible Insulated Conductor Diameter, maximum

1.65 mm | 0.065 in

Compatible Conductor Gauge, solid

28–20 AWG

Material Specifications

Contact Base Material

Phosphor Bronze

Contact Plating Material

Tin

Material Type

Glass filled polycarbonate

Environmental Specifications

Environmental Space Outdoor

Packaging and Weights

Included Base with covers

Packaging quantity 12

Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

