# 760248831 | G2-SP-12SCX-PT



#### G2 Splice Cassette, 12SC, OM4 with pigtails

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Series	G2

## General Specifications

Color, front	Aqua
Interface, front	SC/UPC
Interface, rear	Stranded pigtail
Polarity	Pairs, straight
Shuttered	No
Total Fibers, quantity	12

#### Dimensions

Height	26.416 mm   1.04 in
Width	96.52 mm   3.8 in
Depth	165.354 mm   6.51 in

### Material Specifications

Alignment Sleeve Material	Zirconia
---------------------------	----------

#### **Optical Specifications**

Fiber Mode	Multimode
Fiber Type	OM4
Insertion Loss, maximum	0.185 dB
Return Loss, minimum	35 dB

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2024



# 760248831 | G2-SP-12SCX-PT

### **Environmental Specifications**

Qualification Standards	IEC 61753-1   TIA-568.3-D
Safety Standard	UL

### Packaging and Weights

Included	SMOUV holder   SMOUV splice protection
Packaging quantity	1
Weight, net	0.116 kg   0.256 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted





©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 7, 2024

