



MiniPod, category 6, 4 port, unloaded with angled adapters, unshielded

- Improved speed of redeployment in the workplace through rapid mechanism
- Simplified cabling of raised floor spaces and ideal for high density environments
- Ideal to be terminated at an early stage in the building works
- Designed for use with all standard flexible conduit systems

OBSOLETE

Replaced By:

2153216-6

MiniPod, category 6, 6 port, unloaded with angled adapters, unshielded

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Modular jack enclosure
Product Series	MiniPod

General Specifications

ANSI/TIA Category	6
Application	Used with KJ Series outlets
Cable Entry Location	Side
Color	Black
Conduit Fitting Size	32.1 mm 1.264 in
Integrated Dust Cover Type	Sliding
Mounting	Surface
Outlet Orientation	Flat
Total Ports, quantity	4

Dimensions

Height	85 mm 3.346 in
Width	195 mm 7.677 in

2153216-4

Depth 55 mm | 2.165 in

Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS)

Environmental Specifications

Environmental Space Indoor

Flammability Rating UL 94 V-0

Packaging and Weights

Included Angled Keystone Adaptor (3) | Clear Label Window (3) | Label Insert (3) | MiniPod Subassembly (1) | Mounting screw (1)

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

