
MT-357-24



Trapeze Kit, 24 in wide, one rung

Product Classification

Product Type Trapeze kit

General Specifications

Application Waveguide bridge kit, 24 in

Cable Runs, quantity 14
Hole, quantity 14

Mounting Waveguide bridge channel

Rungs, quantity 1

Dimensions


 Height
 50.8 mm | 2 in

 Width
 660.4 mm | 26 in

 Length
 254 mm | 10 in

 Hole Size
 3/4 in | 7/16 in

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Hardware | Threaded rod | Z-bracket

Packaging quantity 1

Weight, net 3.2 kg | 7.055 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance



Page 2 of 3

MT-357-24

ROHS

Compliant

UK-ROHS

Compliant



Included Products

ZB-H8 - Horizontal Z-bracket, 23 in, for 14 coaxial cable

runs

