SHK-78-1-P



Single Hanger Kit for 7/8 in coaxial cable, single stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	ANDREW® non-standard product
General Specifications	
Cables per Hanger	1
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware
Dimensions	
Maximum Stack Height	1
Height	50.8 mm 2 in
Width	26.2 mm 1.031 in
Length	60.2 mm 2.37 in
Compatible Cable Diameter Range	26.7–28.2 mm
Compatible Diameter, maximum	28.2 mm 1.11 in
Compatible Diameter, minimum	26.7 mm 1.051 in
Nominal Size	7/8 in
Electrical Specifications	
Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB
Material Specifications	
Material Type	Engineered plastic Stainless steel 304

Page 1 of 2



SHK-78-1-P

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
Environmental Specifications	
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degredation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	15 cm 5.906 in
Width, packed	15 cm 5.906 in
Length, packed	3 cm 1.181 in
Included	Angle adapter Hardware
Packaging quantity	1
Weight, gross	0.45 kg 0.992 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025

Page 2 of 2