# WB-K110-B



Safety Grated Waveguide Bridge Kit, 12 in x 10 ft, with two 13 ft 4 in direct burial posts

#### Product Classification

Product Type

Waveguide bridge kit

#### General Specifications

Application	Direct burial
Cable Runs, quantity	12
Pipe, quantity	2
Dimensions	
Haimha	1061 mana   160 im


Height	4064 mm   160 in
Width	304.8 mm   12 in
Length	3048 mm   120 in
Pipe Length	4,053.84 mm   159.6 in

Page 1 of 14



# WB-K110-B

## Outline Drawing



## Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

 Included
 Caps | Channel | Hardware | Posts | Support brackets | Trapeze

 Packaging quantity
 1

 Weight, net
 147.4 kg | 324.961 lb

#### Regulatory Compliance/Certifications

Agency

Classification

Page 2 of 14



# WB-K110-B

CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted
50	

#### Included Products

MF-130	-	Direct Burial Pipe Column, 13 ft 4 in
WB-CY110	-	Safety Grated Waveguide Bridge Channel, 12 in x 10 ft
WB-LB12-3	-	Waveguide Bridge Support Bracket, 12 in wide for 3-1/2 in OD legs $% \left( 12,12,12,12,12,12,12,12,12,12,12,12,12,1$
WB-T12-3	-	Trapeze Kit, triple tee, 12 in wide, three rungs

Page 3 of 14



# MF-130

Direct Burial Pipe Column, 13 ft 4 in

#### Product Classification

Product Type

Pipe column

#### General Specifications


Application	Direct burial
Mounting	Waveguide bridge support bracket
Pipe, quantity	1
Dimensions	

Height	4064 mm   160 in
Width	88.9 mm   3.5 in
Length	88.9 mm   3.5 in
Pipe Length	4,053.84 mm   159.6 in
Pipe Outer Diameter	88.9 mm   3.5 in

Page 4 of 14



## Outline Drawing



#### Material Specifications

Material Type Hot dip ga

Hot dip galvanized steel

#### Packaging and Weights

Included Anchors | Pipe

Packaging quantity

1

 Weight, net
 45.8 kg | 100.972 lb

#### Regulatory Compliance/Certifications

Agency

Classification

Page 5 of 14



## MF-130

CHINA-ROHS

ISO 9001:2015

ROHS

UK-ROHS



Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

Compliant/Exempted





# WB-CY110



Safety Grated Waveguide Bridge Channel, 12 in x 10 ft

#### Product Classification

Product Type Waveguide bridge channel

## General Specifications

Application	Waveguide bridge kit, 12 in

#### Dimensions


Height	76.2 mm   3 in
Width	304.8 mm   12 in
Length	3048 mm   120 in





# WB-CY110

## Outline Drawing



#### Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

Included	Bridge channel
Packaging quantity	1

Weight, net 31.8 kg | 70.107 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

Page 8 of 14



# WB-CY110



Page 9 of 14



# WB-LB12-3



Waveguide Bridge Support Bracket, 12 in wide for 3-1/2 in OD legs

#### Product Classification

Product Type Support bracket

#### **General Specifications**

Application	Waveguide bridge kit, 12 in	
Cable Runs, quantity	12	
Mounting	Pipe, 88.9 mm (3-1/2 in) OD	

#### Dimensions


Height	50.8 mm   2 in
Width	508 mm   20 in
Length	152.4 mm   6 in

Page 10 of 14



## WB-LB12-3

## Outline Drawing



#### Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

Included	Brackets   Hardware
Packaging quantity	1
Weight, net	5.4 kg   11.905 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 11 of 14



# WB-T12-3



Trapeze Kit, triple tee, 12 in wide, three rungs

#### Product Classification

Product Type

Trapeze kit

#### General Specifications

Application	Waveguide bridge kit, 12 in
Cable Runs, quantity	12
Hole, quantity	12
Mounting	Waveguide bridge channel
Rungs, quantity	3


#### Dimensions

Height	76.2 mm   3 in
Width	304.8 mm   12 in
Length	635 mm   25 in
Hole Size	3/4 in   7/16 in

Page 12 of 14



## Outline Drawing



## Material Specifications

Material Type

Hot dip galvanized steel

## Packaging and Weights

Included	Angle brackets   Mounting hardware
Packaging quantity	1
Weight, net	4.1 kg   9.039 lb

#### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 13 of 14



Page 14 of 14

