WB-K110-S



Safety Grated Waveguide Bridge Kit, 12 in x 10 ft, with two 10 ft 6 in base shoe posts

Product Classification

Product Type Waveguide bridge kit

General Specifications

Application Base shoe

Cable Runs, quantity 12
Pipe, quantity 2

Dimensions

 Height
 3,200.4 mm | 126 in


 Width
 304.8 mm | 12 in

 Length
 3048 mm | 120 in

 Pipe Length
 3,200.4 mm | 126 in

WB-K110-S

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Caps | Channel | Hardware | Posts | Support brackets | Trapeze

Packaging quantity 1

Weight, net 139.7 kg | 307.985 lb

Regulatory Compliance/Certifications

Agency Classification



WB-K110-S

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

MF-126 – Base Shoe Pipe Column, 10 ft 6 in

WB-CY110 - Safety Grated Waveguide Bridge Channel, 12 in x 10 ft

WB-LB12-3 – Waveguide Bridge Support Bracket, 12 in wide for 3-1/2 in OD

legs

WB-T12-3 - Trapeze Kit, triple tee, 12 in wide, three rungs

