SSC-760251532E1 | Radio Enclosure DBHP for Ericsson radios



Middle of Pole Concealment Enclosure for 4449/8843 and C-Band 8863 high power radios

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

Mid Pole Concealment for:

- (1) 8843 and (1) 4449 or
- (1) 8843 <u>or</u> 4449 <u>and</u> (1) 8863 C-BAND and
- (1) Raycap
- (4) Rectifiers
- (1) Quad SDX Diplexer

Inlcudes mounting hardware to be attached to wood poles via through bolt or metal poles up 10.75" OD. Can accomodate up to 12.75" OD metal poles with adapter kit "860663246-xx", ordered separate.

Additional Configurations avail utiliziing below kits:

- -860661736-MV2-C03x DBHP & MV2 Fan Tray Kit (x = color)
- -860664550-AMK-001 Retrofit kit for up to (2) the following radios 4415/4435/4455/4480/6347
- -860665492-AMK-003 Retrofit kit for (2) CAP-H radios
- -860665492-AMK-004 Retrofit kit for Raycap RSD 16 Position Power Distrib
- -860665492-AMK-006 Retrofit kit for 4890/4490 to be used in lieu of 8843/4449 also adds option for (1) PSU 6302/6304/6308
- -860665492-AMK-007 Adds Raycap or PTS plus 6308 PSU on lower right side of DBHP plus baffle for the radio opposite. Used in conjunction with other AMKs to provide more configuration options

Product Classification

Product Type Mid pole
Product Brand Metro Cell

Ordering Note ANDREW® standard product with terms

Warranty One year

General Specifications

Antennas Included None

Color Light Gray (RAL 7035)

Color Options Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green (RAL 6012) | Brown (RAL

8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Umbra Grey (RAL 7022)

Cooling Passive Cooling

Doors, quantity 2

Page 1 of 2

SSC-760251532E1 | Radio Enclosure DBHP for Ericsson radios

Front Door Type Single hinged

Mounting Options Non-tapered poles | Tapered poles | Wood poles

Power Supply Compatibility 6304 | 6308 | PSU-AC-08

Radio Compatibility, Ericsson 4415 | 4435 | 4449 | 4455 | 4480 | 6347 | 8843 | 8863 | Diplexer | Power

Distribution

Radios Included None

Dimensions

 Height
 1,422.4 mm | 56 in

 Width
 609.6 mm | 24 in

 Depth
 444.5 mm | 17.5 in

Electrical Specifications

Power/Fiber Input Trade size knockouts at rear side

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.385 m³ | 13.6 ft³ **Weight (unloaded)** 65.771 kg | 145 lb

