



# Preferred ordering guide for NETCONNECT®

CALA Region  
Q1 2023

COMMSCOPE®

# Contents

<b>Copper solutions</b> .....	<b>3</b>
<b>Category 6A Products</b> .....	<b>3</b>
Category 6A U/UTP copper cables.....	3
Category 6A U/UTP panels.....	4
Category 6A U/UTP jacks .....	5
Category 6A U/UTP copper patch cords .....	6
Category 6A F/UTP copper cables.....	8
Category 6A shielded panels.....	8
Category 6A shielded jacks .....	9
Category 6A shielded copper patch cords .....	10
Category 6A ceiling connector assemblies.....	11
<b>Category 6 Products</b> .....	<b>12</b>
Category 6 U/UTP copper cables .....	12
Category 6 U/UTP copper panels.....	13
Category 6 U/UTP jacks.....	14
Category 6 U/UTP copper patch cords.....	15
Category 6 ceiling connector assemblies .....	16
<b>Faceplates &amp; Surface Mount Boxes</b> .....	<b>17</b>
<b>Fiber Solutions</b> .....	<b>20</b>
Fiber optic cables .....	20
<b>Fiber connectivity</b> .....	<b>27</b>
<b>1000-type Solutions</b> .....	<b>27</b>
- 1000-type panels and wall enclosures .....	27
- 1000-type adapter plates .....	28
- 1000-type splice cassettes .....	29
<b>G2 Solutions</b> .....	<b>30</b>
- G2 panels and wall enclosures.....	30
- G2 adapter panels.....	31
- G2 splice and pigtail cassettes .....	32

<b>Duplex Patch Cords</b> .....	<b>33</b>
<b>Fiber Optic Pigtails</b> .....	<b>34</b>
<b>Fiber Optic Connectors and Tool Kits</b> .....	<b>35</b>
- Qwik II fiber optic connectors .....	35
- Qwik II connector tool kits.....	36
- Qwik-Fuse fiber optic connectors.....	37
- Qwik-Fuse connector tool kits .....	38
- Qwik-Fuse MPO connectors.....	39
<b>FiberGuide®</b> .....	<b>40</b>
<b>Straight Sections &amp; Fittings</b> .....	<b>40</b>
<b>Junctions</b> .....	<b>40</b>
<b>Fixed Downspouts</b> .....	<b>40</b>
<b>Express Exit Downspouts</b> .....	<b>41</b>
<b>Downspout Accessories</b> .....	<b>41</b>
<b>C-Brackets for Threaded Rods</b> .....	<b>41</b>
<b>Tools</b> .....	<b>41</b>
<b>Powered Fiber Cable</b> .....	<b>42</b>
<b>Powered Fiber Cables</b> .....	<b>42</b>
<b>Plenum Round Powered Fiber Cable</b> .....	<b>43</b>
<b>1 and 2 Port Extenders</b> .....	<b>44</b>
<b>Power Extenders/Fiber Pass-Thru</b> .....	<b>44</b>
<b>Power Supply</b> .....	<b>44</b>
<b>Surface Mount Boxes</b> .....	<b>44</b>
<b>Plenum Powered Fiber Cable Transition Box</b> .....	<b>44</b>
<b>Cable Management</b> .....	<b>45</b>
<b>Equipment Racks</b> .....	<b>45</b>
<b>Vertical Cable Managers (VCM)</b> .....	<b>46</b>
<b>Horizontal Cable Manager (HCM)</b> .....	<b>47</b>
<b>Filler Panels</b> .....	<b>48</b>

The CommScope NETCONNECT ordering guide for Central and Latin America regions contains commonly ordered copper and fiber structured cabling products. This information is subject to change. For a comprehensive, up-to-date listing of CommScope products, please go to [www.commscope.com](http://www.commscope.com).

### Category 6A U/UTP products



Material ID	Description	Rating	AWG	Jacket Color	Length	Packaging	Availability
<b>Category 6A U/UTP cables</b>							
884031004/10	CS44R BLU C6A 4/23 U/UTP RL 1KFT	CMR	23 AWG	Blue	305 m/ 1000 ft	Reel	Mexico - CA&C
884019304/10	CS44R GRY C6A 4/23 U/UTP RL 1KFT	CMR	23 AWG	Gray	305 m/ 1000 ft	Reel	Mexico - CA&C
884025504/10	CS44R WHT C6A 4/23 U/UTP RL 1KFT	CMR	23 AWG	White	305 m/ 1000 ft	Reel	Mexico - CA&C
884031704/10	CS44R YEL C6A 4/23 U/UTP RL 1KFT	CMR	23 AWG	Yellow	305 m/ 1000 ft	Reel	Mexico - CA&C
884030404/10	CS44R RED C6A 4/23 U/UTP RL 1KFT	CMR	23 AWG	Red	305 m/ 1000 ft	Reel	Mexico - CA&C
884031014/10	CS44R BLU C6A 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Blue	305 m/ 1000 ft	CommPak	Mexico - CA&C
884019314/10	CS44R GRY C6A 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Gray	305 m/ 1000 ft	CommPak	Mexico - CA&C
884025514/10	CS44R WHT C6A 4/23 U/UTP CPK 1KFT	CMR	23 AWG	White	305 m/ 1000 ft	CommPak	Mexico - CA&C
874035104/10	CS44P BLU C6A 4/23 U/UTP RL 1KFT	CMP	23 AWG	Blue	305 m/ 1000 ft	Reel	Mexico - CA&C
874044404/10	CS44P GRY C6A 4/23 U/UTP RL 1KFT	CMP	23 AWG	Gray	305 m/ 1000 ft	Reel	Mexico - CA&C
874026804/10	CS44P WHT C6A 4/23 U/UTP RL 1KFT	CMP	23 AWG	White	305 m/ 1000 ft	Reel	Mexico - CA&C
884037504/10	CS41CM WHT C6A 4/24 U/UTP RL 305M	CM	24 AWG	White	305 m/ 1000 ft	Reel	All Sub-Regions
884044904/10	CS41CM GRY C6A 4/24 U/UTP RL 305M	CM	24 AWG	Gray	305 m/ 1000 ft	Reel	All Sub-Regions
884048304/10	CS41CM BLU C6A 4/24 U/UTP RL 305M	CM	24 AWG	Blue	305 m/ 1000 ft	Reel	All Sub-Regions
884042604/10	CS41Z3 WHT C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	White	305 m/ 1000 ft	Reel	All Sub-Regions
884018004/10	CS41Z3 GRY C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	Gray	305 m/ 1000 ft	Reel	All Sub-Regions
884047004/10	CS41Z3 BLU C6A 4/24 U/UTP RL 305M	LSZH	24 AWG	Blue	305 m/ 1000 ft	Reel	All Sub-Regions
884062604/10	CS41Z3 GRY C6A 4/24 U/UTP RL 305M ANATEL	LSZH	24 AWG	Gray	305 m/ 1000 ft	Reel	All Sub-Regions
84054604/10	CS41Z3 WHT C6A 4/24 U/UTP RL 305M ANATEL	LSZH	24 AWG	White	305 m/ 1000 ft	Reel	All Sub-Regions
884061804/10	CS41Z3 BLU C6A 4/24 U/UTP RL 305M ANATEL	LSZH	24 AWG	Blue	305 m/ 1000 ft	Reel	All Sub-Regions

### Category 6A U/UTP products



Material ID	Description	Availability
<b>Category 6A U/UTP discrete panels (Jacks not included)</b>		
760237040	CPP-UDDM-SL-1U-24 - Discrete Distribution Module Panel, SL, UTP, 1U, 24 port	Mexico - CA&C
760237041	CPP-UDDM-SL-2U-48 - Discrete Distribution Module Panel, SL, UTP, 2U, 48 port	Mexico - CA&C
760237042	CPPA-UDDM-SL-1U-24 - Angled Discrete Distribution Module Panel, SL, UTP, 1U, 24 port	Mexico - CA&C
760237043	CPPA-UDDM-SL-2U-48 - Angled Discrete Distribution Module Panel, SL, UTP, 2U, 48 port	Mexico - CA&C
760237044	CPPR-UDDM-SL-1U-24 - Recessed Angled Discrete Distribution Module Panel, SL, UTP, 1U, 24 port	Mexico - CA&C
760237045	CPPR-UDDM-SL-2U-48 - Recessed Angled Discrete Distribution Module Panel, SL, UTP, 2U, 48 port	Mexico - CA&C



Material ID	Description	Availability
<b>Category 6A U/UTP module panels</b>		
760237032	NPP-6A-DM-1U-24 - Distribution Module Panel, Cat 6A, UTP, 1U, 24 port	Mexico - CA&C
760237033	NPP-6A-DM-2U-48 - Distribution Module Panel, Cat 6A, UTP, 2U, 48 port	Mexico - CA&C
760237034	NPPA-6A-DM-1U-24 - Angled Distribution Module Panel, Cat 6A, UTP, 1U, 24 port	Mexico - CA&C
760237035	NPPA-6A-DM-2U-48 - Angled Distribution Module Panel, Cat 6A, UTP, 2U, 48 port	Mexico - CA&C
760237036	NPPR-6A-DM-1U-24 - Recessed Angled Distribution Module Panel, Cat 6A, UTP, 1U, 24 port	Mexico - CA&C
760237037	NPPR-6A-DM-2U-48 - Recessed Angled Distribution Module Panel, Cat 6A, UTP, 2U, 48 port	Mexico - CA&C
760244168	CPPD-6A-DM-1U-24 - Dynamic Angled Distribution Module Panel, Cat6A, UTP, 1U, 24 port	Mexico - CA&C

### Category 6A U/UTP products

Material ID	Description	Color	Availability
<b>Category 6A unshielded U/UTP jacks</b>			
<b>SL Opening (without dust cover)</b>			
760241184	SL10G-L.ALD Category 6A U/UTP SL jack - without dust cover	Almond	Mexico - CA&C
760241185	SL10G-BLK Category 6A U/UTP SL jack - without dust cover	Black	Mexico - CA&C
760241186	SL10G-GRY Category 6A U/UTP SL jack - without dust cover	Gray	Mexico - CA&C
760241187	SL10G-ORG Category 6A U/UTP SL jack - without dust cover	Orange	Mexico - CA&C
760241188	SL10G-BLU Category 6A U/UTP SL jack - without dust cover	Blue	Mexico - CA&C
760241189	SL10G-RED Category 6A U/UTP SL jack - without dust cover	Red	Mexico - CA&C
760241190	SL10G-YEL Category 6A U/UTP SL jack - without dust cover	Yellow	Mexico - CA&C
760241191	SL10G-GRN Category 6A U/UTP SL jack - without dust cover	Green	Mexico - CA&C
760241192	SL10G-VIO Category 6A U/UTP SL jack - without dust cover	Violet	Mexico - CA&C
760241193	SL10G-E.IVY Category 6A U/UTP SL jack - without dust cover	Electrical Ivory	Mexico - CA&C
760241194	SL10G-A.WHT Category 6A U/UTP SL jack - without dust cover	Alpine White	Mexico - CA&C
760241195	SL10G-BLK-24 Category 6A U/UTP SL jack - without dust cover	Black	Mexico - CA&C



Material ID	Description	Color	Availability
<b>Category 6A unshielded U/UTP jacks</b>			
<b>SL Opening (with dust cover)</b>			
760241196	SL10G-DC-L.ALD Category 6A U/UTP SL jack - with dust cover	Almond	Mexico - CA&C
760241197	SL10G-DC-BLK Category 6A U/UTP SL jack - with dust cover	Black	Mexico - CA&C
760241198	SL10G-DC-GRY Category 6A U/UTP SL jack - with dust cover	Gray	Mexico - CA&C
760241199	SL10G-DC-ORG Category 6A U/UTP SL jack - with dust cover	Orange	Mexico - CA&C
760241200	SL10G-DC-BLU Category 6A U/UTP SL jack - with dust cover	Blue	Mexico - CA&C
760241201	SL10G-DC-RED Category 6A U/UTP SL jack - with dust cover	Red	Mexico - CA&C
760241202	SL10G-DC-YEL Category 6A U/UTP SL jack - with dust cover	Yellow	Mexico - CA&C
760241203	SL10G-DC-GRN Category 6A U/UTP SL jack - with dust cover	Green	Mexico - CA&C
760241204	SL10G-DC-VIO Category 6A U/UTP SL jack - with dust cover	Violet	Mexico - CA&C
760241205	SL10G-DC-E.IVY Category 6A U/UTP SL jack - with dust cover	Electrical Ivory	Mexico - CA&C
760241206	SL10G-DC-A.WHT Category 6A U/UTP SL jack - with dust cover	Alpine White	Mexico - CA&C



### Category 6A U/UTP products



Material ID	Description	Rating	Color	Availability
<b>Category 6A U/UTP patch cords - LSZH</b>				
NPC6AUZDB-WT __ _M	Category 6A, U/UTP, LSZH, White, Meter	LSZH	White	Mexico - CA&C
NPC6AUZDB-BL __ _M	Category 6A, U/UTP, LSZH, Blue, Meter	LSZH	Blue	Mexico - CA&C
NPC6AUZDB-GY __ _M	Category 6A, U/UTP, LSZH, Gray, Meter	LSZH	Gray	Mexico - CA&C
NPC6AUZDB-GN __ _M	Category 6A, U/UTP, LSZH, Green, Meter	LSZH	Green	Mexico - CA&C
NPC6AUZDB-OR __ _M	Category 6A, U/UTP, LSZH, Orange, Meter	LSZH	Orange	Mexico - CA&C
NPC6AUZDB-RD __ _M	Category 6A, U/UTP, LSZH, Red, Meter	LSZH	Red	Mexico - CA&C
NPC6AUZDB-YL __ _M	Category 6A, U/UTP, LSZH, Yellow, Meter	LSZH	Yellow	Mexico - CA&C
NPC6AUZDB-BK __ _M	Category 6A, U/UTP, LSZH, Black, Meter	LSZH	Black	Mexico - CA&C

### LSZH (Z) Patch Cords Length Options

Length (M)	Increment
0.5-3	50 CM
3-10	1 M
10-20	2 M
20-35	5 M

### Category 6A U/UTP products




Material ID	Description	Rating	Color	Availability
<b>MiNo Category 6A U/UTP patch cords - LSZH/CM</b>				
CO199K2-01* ---	MiNo6A-BK - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Black Jacket	LSZH/CM	Black	All Sub-Regions - Excluding Brazil
CO199K2-02* ---	MiNo6A-LB - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Light Blue Jacket	LSZH/CM	Light Blue	All Sub-Regions - Excluding Brazil
CO199K2-03* ---	MiNo6A-DG - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Dark Gray Jacket	LSZH/CM	Dark Gray	All Sub-Regions - Excluding Brazil
CO199K2-04* ---	MiNo6A-SG - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Spring Green Jacket	LSZH/CM	Spring Green	All Sub-Regions - Excluding Brazil
CO199K2-06* ---	MiNo6A-OR - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Orange Jacket	LSZH/CM	Orange	All Sub-Regions - Excluding Brazil
CO199K2-07* ---	MiNo6A-RD - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Red Jacket	LSZH/CM	Red	All Sub-Regions - Excluding Brazil
CO199K2-08* ---	MiNo6A-WH - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, White Jacket	LSZH/CM	White	All Sub-Regions - Excluding Brazil
CO199K2-09* ---	MiNo6A-YL - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Yellow Jacket	LSZH/CM	Yellow	All Sub-Regions - Excluding Brazil
CO199K2-0L* ---	MiNo6A-PR - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Purple Jacket	LSZH/CM	Purple	All Sub-Regions - Excluding Brazil
CO199K2-0Z* ---	MiNo6A-BL - MiNo6A Series Category 6A U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Blue Jacket	LSZH/CM	Blue	All Sub-Regions - Excluding Brazil
Available in FT (*=F) or MT (*=M) Ask your CommScope representative for other available Lengths				

#### Patch Cords Length Options

Length (in)	Length (ft)
6 in-120 in	1-130 ft
Length (cm)	Length (m)
15 cm-300 cm	1-40 m

### Category 6A F/UTP products



Material ID	Description	Rating	AWG	Jacket Color	Length	Packaging	Availability
<b>Category 6A F/UTP cables</b>							
884031108/10	Copper cable, Category 6A, 4 pair, F/UTP CS44CM WHT C6A 4/23 F/UTP RL 305M ANATEL	CM	23 AWG	White	305 m/ 1000 ft	Reel	Argentina, Colombia, Chile/Peru, Brazil
884026308/10	Copper cable, Category 6A, 4 pair, F/UTP CS44CM GRY C6A 4/23 F/UTP RL 305M ANATEL	CM	23 AWG	Gray	305 m/ 1000 ft	Reel	Argentina, Colombia, Chile/Peru, Brazil
884025308/10	Copper cable, Category 6A, 4 pair, F/UTP CS44CM BLU C6A 4/23 F/UTP RL 305M ANATEL	CM	23 AWG	Blue	305 m/ 1000 ft	Reel	Argentina, Colombia, Chile/Peru, Brazil
5-1859349-6	Copper cable, Category 6A, 4 pair, F/UTP CS44R BLU C6A 4/23 F/UTP RL 305M ANATEL	CMR	23 AWG	Blue	305 m/ 1000 ft	Reel	Argentina, Colombia, Chile/Peru, Brazil
884019708/10	Copper cable, Category 6A, 4 pair, F/UTP CS44Z1 WHT C6A 4/23 F/UTP RL 305M ANATEL	LSZH	23 AWG	White	305 m/ 1000 ft	Reel	Argentina, Colombia, Chile/Peru, Brazil
884015608/10	Copper cable, Category 6A, 4 pair, F/UTP CS44Z1 GRY C6A 4/23 F/UTP RL 305M ANATEL	LSZH	23 AWG	Gray	305 m/ 1000 ft	Reel	Argentina, Colombia, Chile/Peru, Brazil
884040108/10	Copper cable, Category 6A, 4 pair, F/UTP CS44Z1 BLU C6A 4/23 F/UTP RL 305M ANATEL	LSZH	23 AWG	Blue	305 m/ 1000 ft	Reel	Argentina, Colombia, Chile/Peru, Brazil
1859381-2	Copper cable, Category 6A, 4 pair, F/UTP	LSZH	23 AWG	White	305 m/ 1000 ft	Reel	Colombia, Chile/Peru
884017404/10	CS44R WHT C6A 4/23 F/UTP RL 1KFT	CMR	23 AWG	White	305 m/ 1000 ft	Reel	Mexico - CA&C
884033904/10	CS44R GRY C6A 4/23 F/UTP RL 1KFT	CMR	23 AWG	Gray	305 m/ 1000 ft	Reel	Mexico - CA&C
884018404/10	CS44R BLU C6A 4/23 F/UTP RL 1KFT	CMR	23 AWG	Blue	305 m/ 1000 ft	Reel	Mexico - CA&C



Material ID	Description	Availability
<b>Category 6A Shielded copper panels - Discrete panels - Jacks not Included</b>		
760237046	CPP-SDDM-SL-1U-24 - Discrete Distribution Module Panel, SL, STP, 1U, 24 port	All Sub-Regions
760237047	CPP-SDDM-SL-2U-48 - Discrete Distribution Module Panel, SL, STP, 2U, 48 port	All Sub-Regions
760237048	CPPA-SDDM-SL-1U-24 - Angled Discrete Distribution Module Panel, SL, STP, 1U, 24 port	All Sub-Regions
760237049	CPPA-SDDM-SL-2U-48 - Angled Discrete Distribution Module Panel, SL, STP, 2U, 48 port	All Sub-Regions
760237050	CPPR-SDDM-SL-1U-24 - Recessed Angled Discrete Distribution Module Panel, SL, STP, 1U, 24 port	All Sub-Regions
760237051	CPPR-SDDM-SL-2U-48 - Recessed Angled Discrete Distribution Module Panel, SL, STP, 2U, 48 port	All Sub-Regions
760237066	CPP-6A-SDDM-SL-1U-48 - Distribution Module Panel, Category 6A, SL, STP, 1U, 48 port (Jacks Included)	All Sub-Regions



### Category 6A F/UTP products

Material ID	Description	Color	Availability
<b>Category 6A Shielded Jacks - Without dust cover</b>			
2153449-1	AMP-TWIST SLX, 6AS Jack Almond without Dust Cover	Almond	All Sub-Regions
2153449-2	AMP-TWIST SLX, 6AS Jack Black without Dust Cover	Black	All Sub-Regions
2153449-4	AMP-TWIST SLX, 6AS Jack Gray without Dust Cover	Gray	All Sub-Regions
2153449-5	AMP-TWIST SLX, 6AS Jack Orange without Dust Cover	Orange	All Sub-Regions
2153449-6	AMP-TWIST SLX, 6AS Jack Blue without Dust Cover	Blue	All Sub-Regions
2153449-7	AMP-TWIST SLX, 6AS Jack Red without Dust Cover	Red	All Sub-Regions
2153449-8	AMP-TWIST SLX, 6AS Jack Yellow without Dust Cover	Yellow	All Sub-Regions
2153449-9	AMP-TWIST SLX, 6AS Jack Green without Dust Cover	Green	All Sub-Regions
1-2153449-3	AMP-TWIST SLX, 6AS Jack Al-White without Dust Cover	White	All Sub-Regions
760245049	Four-Direction Cable Exit Cap for SLX Jacks, bag of 50 pcs	–	All Sub-Regions
4-2153449-6*	AMP-TWIST SLX Series Modular Jack, category 6A, shielded, 4 Pair, without dust cover, blue (24 ea/pkg)	Blue	All Sub-Regions



\*Eco-friendly packaging. Does not contain single use plastics in packaging.

Material ID	Description	Color	Availability
<b>Category 6A Shielded Jacks - With dust cover</b>			
2153365-1	AMP-TWIST SLX, 6AS Jack Almond with Dust Cover	Almond	All Sub-Regions
2153365-2	AMP-TWIST SLX, 6AS Jack Black with Dust Cover	Black	All Sub-Regions
2153365-4	AMP-TWIST SLX, 6AS Jack Gray with Dust Cover	Gray	All Sub-Regions
2153365-5	AMP-TWIST SLX, 6AS Jack Orange with Dust Cover	Orange	All Sub-Regions
2153365-6	AMP-TWIST SLX, 6AS Jack Blue with Dust Cover	Blue	All Sub-Regions
2153365-7	AMP-TWIST SLX, 6AS Jack Red with Dust Cover	Red	All Sub-Regions
2153365-8	AMP-TWIST SLX, 6AS Jack Yellow with Dust Cover	Yellow	All Sub-Regions
2153365-9	AMP-TWIST SLX, 6AS Jack Green with Dust Cover	Green	All Sub-Regions
1-2153365-3	AMP-TWIST SLX, 6AS Jack Al-White with Dust Cover	White	All Sub-Regions
760245049	Four-Direction Cable Exit Cap for SLX Jacks, bag of 50 pcs	–	All Sub-Regions



### Category 6A shielded products

Material ID	Description	Rating	Color	Availability
<b>Category 6A shielded copper patch cords - CM</b>				
NPC6ASVDB-WT ___F	Category 6A, S/FTP, CM (PVC), White, Feet	CM	White	All Sub-Regions
NPC6ASVDB-BL ___F	Category 6A, S/FTP, CM (PVC), Blue, Feet	CM	Blue	All Sub-Regions
NPC6ASVDB-GY ___F	Category 6A, S/FTP, CM (PVC), Gray, Feet	CM	Gray	All Sub-Regions
NPC6ASVDB-GN ___F	Category 6A, S/FTP, CM (PVC), Green, Feet	CM	Green	All Sub-Regions
NPC6ASVDB-OR ___F	Category 6A, S/FTP, CM (PVC), Orange, Feet	CM	Orange	All Sub-Regions
NPC6ASVDB-RD ___F	Category 6A, S/FTP, CM (PVC), Red, Feet	CM	Red	All Sub-Regions
NPC6ASVDB-YL ___F	Category 6A, S/FTP, CM (PVC), Yellow, Feet	CM	Yellow	All Sub-Regions
NPC6ASVDB-BK ___F	Category 6A, S/FTP, CM (PVC), Black, Feet	CM	Black	All Sub-Regions



#### CM (V) Patch Cords Length Options

Length (FT)	Increment
1–20	1 FT
20–50	5 FT
50–100	10 FT

Material ID	Description	Rating	Color	Availability
<b>Category 6A Shielded patch cords - LSZH</b>				
NPC6ASZDB-WT ___M	Category 6A, S/FTP, LSZH, White, Meter	LSZH	White	All Sub-Regions
NPC6ASZDB-BL ___M	Category 6A, S/FTP, LSZH, Blue, Meter	LSZH	Blue	All Sub-Regions
NPC6ASZDB-GY ___M	Category 6A, S/FTP, LSZH, Gray, Meter	LSZH	Gray	All Sub-Regions
NPC6ASZDB-GN ___M	Category 6A, S/FTP, LSZH, Green, Meter	LSZH	Green	All Sub-Regions
NPC6ASZDB-OR ___M	Category 6A, S/FTP, LSZH, Orange, Meter	LSZH	Orange	All Sub-Regions
NPC6ASZDB-RD ___M	Category 6A, S/FTP, LSZH, Red, Meter	LSZH	Red	All Sub-Regions
NPC6ASZDB-YL ___M	Category 6A, S/FTP, LSZH, Yellow, Meter	LSZH	Yellow	All Sub-Regions
NPC6ASZDB-BK ___M	Category 6A, S/FTP, LSZH, Black, Meter	LSZH	Black	All Sub-Regions



#### LSZH (Z) Patch Cords Length Options

Length (M)	Increment
0.5–3	50 CM
3–10	1 M
10–20	2 M
20–35	5 M


### Category 6A Ceiling Connector Assembly Solutions



Material ID	Description	Availability
COP1KW2-88F0XX*	CCA-CAT6A-SHIELDED PLENUM-ECO PKG (2 PC)	All Sub-Regions
COP1KZ2-88F0XX*	CCA-CAT6A-SHIELDED LSZH-ECO PKG (2 PC)	All Sub-Regions
COP1KW2-88N018	CCA-CAT6A-SHIELDED PLENUM-ECO PKG (2 PC) -18 INCH	All Sub-Regions
COP1KZ2-88N018	CCA-CAT6A-SHIELDED LSZH-ECO PKG (2 PC) – 18 INCH	All Sub-Regions
CO1SJO2-11F0XX*	CommScope Category 6A U/UTP Cord, Plenum, RJ45 to Ceiling connector, Black	All Sub-Regions
CO13JX2-88N018	CommScope Category 6A U/UTP Cord, Plenum, RJ45 to Ceiling connector, Black - 18 Inch	All Sub-Regions
760235590	CCA-CAT6A-LSZH-WHITE-N018	All Sub-Regions
760235589	CCA-CAT6A-LSZH-BLACK-N018	All Sub-Regions
760244061	Ceiling Connector Assembly (CCA) without cordage, Black	All Sub-Regions
760234921	Ceiling Connector Assembly (CCA) without cordage, White	All Sub-Regions
760250028	ECO CCA, SHIELDED – KIT (5 PCS)	All Sub-Regions

\*XX – 02, 03, 07, 11, 15, 20, 25, 30, 40, 50 ft.

### Category 6 U/UTP products



Material ID	Description	Rating	AWG	Jacket Color	Length	Packaging	Availability
<b>Category 6 U/UTP copper cables</b>							
884028514/10	CS31CM WHT C6 4/23 U/UTP CPK 305M	CM	23 AWG	White	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
884027814/10	CS31CM GRY C6 4/23 U/UTP CPK 305M	CM	23 AWG	Gray	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
884016914/10	CS31CM BLU C6 4/23 U/UTP CPK 305M	CM	23 AWG	Blue	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
5-1427071-2	Category 6, 4 pair, UTP	CM	24 AWG	White	305 m/ 1000 ft	RIB	Argentina, Colombia, Chile/Peru, Brazil
5-1427071-4	Category 6, 4 pair, UTP	CM	24 AWG	Gray	305 m/ 1000 ft	RIB	Argentina, Colombia, Chile/Peru, Brazil
5-1427071-6	Category 6, 4 pair, UTP	CM	24 AWG	Blue	305 m/ 1000 ft	RIB	Argentina, Colombia, Chile/Peru, Brazil
884024314/10	CS31R WHT C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	White	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
884031114/10	CS31R GRY C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Gray	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
884022314/10	CS31R BLU C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Blue	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
884036414/10	CS31Z1 WHT C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	White	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
884035914/10	CS31Z1 GRY C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	Gray	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
884037614/10	CS31Z1 BLU C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	Blue	305 m/ 1000 ft	CommPak	Colombia, Chile/Peru
5-1427070-2	Category 6, 4 pair, UTP	LSZH	24 AWG	White	305 m/ 1000 ft	RIB	Argentina, Colombia, Chile/Peru, Brazil
5-1427070-4	Category 6, 4 pair, UTP	LSZH	24 AWG	Gray	305 m/ 1000 ft	RIB	Argentina, Colombia, Chile/Peru, Brazil
5-1427070-6	Category 6, 4 pair, UTP	LSZH	24 AWG	Blue	305 m/ 1000 ft	RIB	Argentina, Colombia, Chile/Peru, Brazil
884017814/10	CS31Z3 WHT C6 4/23 U/UTP CPK 305M	LSZH	23 AWG	White	305 m/ 1000 ft	CommPak	Chile/Peru
884024414/10	CS34R WHT C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	White	305 m/ 1000 ft	CommPak	Mexico - CA&C
884015814/10	CS34R GRY C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Gray	305 m/ 1000 ft	CommPak	Mexico - CA&C
884017214/10	CS34R BLU C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Blue	305 m/ 1000 ft	CommPak	Mexico - CA&C
884025814/10	CS34R YEL C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Yellow	305 m/ 1000 ft	CommPak	Mexico - CA&C
884029184/30	CS34R RED C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Red	305 m/ 1000 ft	CommPak	Mexico - CA&C
874019914/10	CS34P WHT C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	White	305 m/ 1000 ft	CommPak	Mexico - CA&C
874042114/10	CS34P GRY C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	Gray	305 m/ 1000 ft	CommPak	Mexico - CA&C
874049914/10	CS34P BLU C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	Blue	305 m/ 1000 ft	CommPak	Mexico - CA&C
874034114/10	CS34P YEL C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	Yellow	305 m/ 1000 ft	CommPak	Mexico - CA&C
874017414/10	CS34P RED C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	Red	305 m/ 1000 ft	CommPak	Mexico - CA&C
884019114/10	CS37R WHT C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	White	305 m/ 1000 ft	CommPak	Mexico - CA&C
884033314/10	CS37R GRY C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Gray	305 m/ 1000 ft	CommPak	Mexico - CA&C
884026814/10	CS37R BLU C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Blue	305 m/ 1000 ft	CommPak	Mexico - CA&C
884022614/10	CS37R YEL C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Yellow	305 m/ 1000 ft	CommPak	Mexico - CA&C
884022814/10	CS37R RED C6 4/23 U/UTP CPK 1KFT	CMR	23 AWG	Red	305 m/ 1000 ft	CommPak	Mexico - CA&C
874049714/10	CS37P WHT C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	White	305 m/ 1000 ft	CommPak	Mexico - CA&C
874026714/10	CS37P GRY C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	Gray	305 m/ 1000 ft	CommPak	Mexico - CA&C
874043014/10	CS37P BLU C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	Blue	305 m/ 1000 ft	CommPak	Mexico - CA&C
874029514/10	CS37P YEL C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	Yellow	305 m/ 1000 ft	CommPak	Mexico - CA&C
874045214/10	CS37P RED C6 4/23 U/UTP CPK 1KFT	CMP	23 AWG	Red	305 m/ 1000 ft	CommPak	Mexico - CA&C

Note: CS34R & CS34P U/UTP available also in 3KFT reels. CS37R & CS37P U/UTP available also in 1KFT & 3KFT reels.

### Category 6 U/UTP products



Material ID	Product Number	Description	Availability
<b>Category 6 U/UTP Discrete panels (Jacks not included)</b>			
760237040	CPP-UDDM-SL-1U-24	Discrete Distribution Module Panel, SL, UTP, 1U, 24 port	All Sub-Regions
760237041	CPP-UDDM-SL-2U-48	Discrete Distribution Module Panel, SL, UTP, 2U, 48 port	All Sub-Regions
760237042	CPPA-UDDM-SL-1U-24	Angled Discrete Distribution Module Panel, SL, UTP, 1U, 24 port	All Sub-Regions
760237043	CPPA-UDDM-SL-2U-48	Angled Discrete Distribution Module Panel, SL, UTP, 2U, 48 port	All Sub-Regions
760237044	CPPR-UDDM-SL-1U-24	Recessed Angled Discrete Distribution Module Panel, SL, UTP, 1U, 24 port	All Sub-Regions
760237045	CPPR-UDDM-SL-2U-48	Recessed Angled Discrete Distribution Module Panel, SL, UTP, 2U, 48 port	All Sub-Regions
760237052	CPP-UDDM-KJ-1U-24	Discrete Distribution Module Panel, Keystone, UTP, 1U, 24 port	Colombia
760241547	CPP-UDDM-KJ-2U-48	Discrete Distribution Module Panel, Keystone, UTP, 1U, 48 port	Colombia



Material ID	Product Number	Description	Availability
<b>Category 6 U/UTP Module panels</b>			
760237024	NPP-6-DM-1U-24	Distribution Module Panel, Category 6, UTP, 1U, 24 port	All Sub-Regions
760237025	NPP-6-DM-2U-48	Distribution Module Panel, Category 6, UTP, 2U, 48 port	All Sub-Regions
760237026	NPPA-6-DM-1U-24	Angled Distribution Module Panel, Category 6, UTP, 1U, 24 port	All Sub-Regions
760237027	NPPA-6-DM-2U-48	Angled Distribution Module Panel, Category 6, UTP, 2U, 48 port	All Sub-Regions
760237028	NPPR-6-DM-1U-24	Recessed Angled Distribution Module Panel, Category 6, UTP, 1U, 24 port	All Sub-Regions
760237029	NPPR-6-DM-2U-48	Recessed Angled Distribution Module Panel, Category 6, UTP, 2U, 48 port	All Sub-Regions
760237060	NPP-UDDM-SL-1U-48	Discrete Distribution Module Panel, Category 6, UTP, 1U, 48 port	All Sub-Regions
760237061	NPPA-UDDM-SL-1U-48	Angled Discrete Distribution Module Panel, Category 6, UTP, 1U, 48 port	All Sub-Regions
760244166	CPPD-6-DM-1U-24	Dynamic Angled Distribution Module Panel, Cat6, UTP, 1U, 24 port	All Sub-Regions
Note: 760237060 / 760237061 are Discrete panel with jacks included			

### Category 6 U/UTP products



Material ID	Description	Color
<b>Category 6 U/UTP jacks</b>		
<b>SL-Series opening without dust cover (All sub-regions)</b>		
1375055-1	Category 6 U/UTP jack, SL	Almond
1375055-2	Category 6 U/UTP jack, SL	Black
1375055-4	Category 6 U/UTP jack, SL	Gray
1375055-5	Category 6 U/UTP jack, SL	Orange
1375055-6	Category 6 U/UTP jack, SL	Blue
1375055-7	Category 6 U/UTP jack, SL	Red
1375055-8	Category 6 U/UTP jack, SL	Yellow
1375055-9	Category 6 U/UTP jack, SL	Green
1-1375055-0	Category 6 U/UTP jack, SL	Violet
1-1375055-1	Category 6 U/UTP jack, SL	Electrical Ivory
1-1375055-3	Category 6 U/UTP jack, SL	Alpine White
9-1375055-2	Category 6 U/UTP jack, SL (Bag 24pcs)	Black
<b>SL-Series opening with dust cover (All sub-regions)</b>		
1375187-1	Category 6 U/UTP jack, SL, with dust cover	Almond
1375187-2	Category 6 U/UTP jack, SL, with dust cover	Black
1375187-4	Category 6 U/UTP jack, SL, with dust cover	Gray
1375187-5	Category 6 U/UTP jack, SL, with dust cover	Orange
1375187-6	Category 6 U/UTP jack, SL, with dust cover	Blue
1375187-7	Category 6 U/UTP jack, SL, with dust cover	Red
1375187-8	Category 6 U/UTP jack, SL, with dust cover	Yellow
1375187-9	Category 6 U/UTP jack, SL, with dust cover	Green
1-1375187-0	Category 6 U/UTP jack, SL, with dust cover	Violet
1-1375187-1	Category 6 U/UTP jack, SL, with dust cover	Electrical Ivory
1-1375187-3	Category 6 U/UTP jack, SL, with dust cover	Alpine White
<b>Keystone opening (Colombia only)</b>		
2291216-1	Category 6 U/UTP jack, keystone	Almond
2291216-2	Category 6 U/UTP jack, keystone	Black
2291216-4	Category 6 U/UTP jack, keystone	Gray
2291216-5	Category 6 U/UTP jack, keystone	Orange
2291216-6	Category 6 U/UTP jack, keystone	Blue
2291216-7	Category 6 U/UTP jack, keystone	Red
2291216-8	Category 6 U/UTP jack, keystone	Yellow
2291216-9	Category 6 U/UTP jack, keystone	Green
1-2291216-0	Category 6 U/UTP jack, keystone	Violet
1-2291216-1	Category 6 U/UTP jack, keystone	Electrical Ivory
1-2291216-3	Category 6 U/UTP jack, keystone	Alpine White
9-2291216-2	Category 6 U/UTP jack, keystone	Black

### Category 6 U/UTP products



Material ID	Description	Rating	Color	Availability
<b>Category 6 U/UTP patch cords - CM</b>				
NPC06UVDB-WT ___F	Category 6, U/UTP, CM (PVC), White, Feet	CM	White	All Sub-Regions
NPC06UVDB-BL ___F	Category 6, U/UTP, CM (PVC), Blue, Feet	CM	Blue	All Sub-Regions
NPC06UVDB-GY ___F	Category 6, U/UTP, CM (PVC), Gray, Feet	CM	Gray	All Sub-Regions
NPC06UVDB-GN ___F	Category 6, U/UTP, CM (PVC), Green, Feet	CM	Green	All Sub-Regions
NPC06UVDB-OR ___F	Category 6, U/UTP, CM (PVC), Orange, Feet	CM	Orange	All Sub-Regions
NPC06UVDB-RD ___F	Category 6, U/UTP, CM (PVC), Red, Feet	CM	Red	All Sub-Regions
NPC06UVDB-YL ___F	Category 6, U/UTP, CM (PVC), Yellow, Feet	CM	Yellow	All Sub-Regions
NPC06UVDB-BK ___F	Category 6, U/UTP, CM (PVC), Black, Feet	CM	Black	All Sub-Regions

### CM (V) Patch Cords Length Options

Length (FT)	Increment
1–20	1 FT
20–50	5 FT
50–100	10 FT



Material ID	Description	Rating	Color	Availability
<b>Category 6 U/UTP patch cords - LSZH</b>				
NPC06UZDB-WT ___M	Category 6, U/UTP, LSZH, White, Meter	LSZH	White	All Sub-Regions
NPC06UZDB-BL ___M	Category 6, U/UTP, LSZH, Blue, Meter	LSZH	Blue	All Sub-Regions
NPC06UZDB-GY ___M	Category 6, U/UTP, LSZH, Gray, Meter	LSZH	Gray	All Sub-Regions
NPC06UZDB-GN ___M	Category 6, U/UTP, LSZH, Green, Meter	LSZH	Green	All Sub-Regions
NPC06UZDB-OR ___M	Category 6, U/UTP, LSZH, Orange, Meter	LSZH	Orange	All Sub-Regions
NPC06UZDB-RD ___M	Category 6, U/UTP, LSZH, Red, Meter	LSZH	Red	All Sub-Regions
NPC06UZDB-YL ___M	Category 6, U/UTP, LSZH, Yellow, Meter	LSZH	Yellow	All Sub-Regions
NPC06UZDB-BK ___M	Category 6, U/UTP, LSZH, Black, Meter	LSZH	Black	All Sub-Regions

### LSZH (Z) Patch Cords Length Options

Length (M)	Increment
0.5–3	50 CM
3–10	1 M
10–20	2 M
20–35	5 M



Material ID	Description	Rating	Color	Availability
<b>Category 6 U/UTP Slim patch cords - CM</b>				
#-1989795-#	Category 6, U/UTP, CM (PVC)	CM	White	All Sub-Regions
#-1989798-#	Category 6, U/UTP, CM (PVC)	CM	Blue	All Sub-Regions
#-1989796-#	Category 6, U/UTP, CM (PVC)	CM	Gray	All Sub-Regions
#-1989799-#	Category 6, U/UTP, CM (PVC)	CM	Green	All Sub-Regions
#-1989797-#	Category 6, U/UTP, CM (PVC)	CM	Red	All Sub-Regions
#-1989800-#	Category 6, U/UTP, CM (PVC)	CM	Yellow	All Sub-Regions
#-1989801-#	Category 6, U/UTP, CM (PVC)	CM	Black	All Sub-Regions
Available in 2, 3, 4, 5, 6, 7, 8, 10, 15, 20, 25, 30 FT				

### Category 6 U/UTP products



Material ID	Product Number	Description (jacket/ boot)	Rating	Color	Availability
<b>MINO Category 6 U/UTP patch cords - LSZH/CM</b>					
CO166S2-01* _ _ _	MINO6-BK	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Black Jacket	LSZH/CM	Black	All Sub-Regions - Excluding Brazil
CO166S2-02* _ _ _	MINO6-LB	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Light Blue Jacket	LSZH/CM	Light Blue	All Sub-Regions - Excluding Brazil
CO166S2-03* _ _ _	MINO6-DG	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Dark Gray Jacket	LSZH/CM	Dark Gray	All Sub-Regions - Excluding Brazil
CO166S2-04* _ _ _	MINO6-SG	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Spring Green Jacket	LSZH/CM	Spring Green	All Sub-Regions - Excluding Brazil
CO166S2-06* _ _ _	MINO6-OR	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Orange Jacket	LSZH/CM	Orange	All Sub-Regions - Excluding Brazil
CO166S2-07* _ _ _	MINO6-RD	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Red Jacket	LSZH/CM	Red	All Sub-Regions - Excluding Brazil
CO166S2-08* _ _ _	MINO6-WH	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, White Jacket	LSZH/CM	White	All Sub-Regions - Excluding Brazil
CO166S2-09* _ _ _	MINO6-YL	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Yellow Jacket	LSZH/CM	Yellow	All Sub-Regions - Excluding Brazil
CO166S2-0L* _ _ _	MINO6-PR	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Purple Jacket	LSZH/CM	Purple	All Sub-Regions - Excluding Brazil
CO166S2-0Z* _ _ _	MINO6-BL	MiNo6 Series Category 6 Performance U/UTP Reduced Diameter LS-CM Dual Rated Patch Cord, Blue Jacket	LSZH/CM	Blue	All Sub-Regions - Excluding Brazil
Available in FT (*=F) or MT (*=M)		Ask your CommScope representative for other available Lengths			

#### Patch Cords Length Options

Length (in)	Length (ft)	Length (cm)	Length (m)
6 in-120 in	1-130 ft	15 cm-300 cm	1-40 m




### Category 6 Ceiling Connector Assembly Solutions

Material ID	Description	Availability
CO13JX2-11F0XX*	CommScope Category 6 U/UTP Cord, Plenum, RJ45 to Ceiling connector, Black	All Sub-Regions
CO13JX2-88F0XX*	CommScope Category 6 U/UTP Cord, Plenum, RJ45 to Ceiling connector, White	All Sub-Regions
CO1SJO2-88F0XX*	CommScope Category 6 U/UTP Cord, Plenum, RJ45 to Ceiling connector, White	All Sub-Regions
CO13JX2-11N018	CommScope Category 6 U/UTP Cord, Plenum, RJ45 to Ceiling connector, Black - 18 Inch	All Sub-Regions
CO1SJO2-11N018	CommScope Category 6 U/UTP Cord, Plenum, RJ45 to Ceiling connector, White - 18 Inch	All Sub-Regions
CO1SJO2-88N018	CommScope Category 6 U/UTP Cord, Plenum, RJ45 to Ceiling connector, White - 18 Inch	All Sub-Regions
760235586	CCA-CAT6-LSZH-WHITE-N018	All Sub-Regions
760235585	CCA-CAT6-LSZH-BLACK-N018	All Sub-Regions
760244061	Ceiling Connector Assembly (CCA) without cordage, Black	All Sub-Regions
760234921	Ceiling Connector Assembly (CCA) without cordage, White	All Sub-Regions
760250028	ECO CCA, SHIELDED – KIT (5 PCS)	All Sub-Regions

\*XX – 02, 03, 07, 11, 15, 20, 25, 30, 40, 50 ft.



# Faceplates & Surface Mount Boxes



Material ID	Product Number	Description	Jack
<b>Modular flush-mount faceplates</b>			
760249144	FP-LBL-1P-266	Faceplate Kit, labeled, 1-gang, 1 port, prowhite	universal opening
760249145	FP-LBL-2P-266	Faceplate Kit, labeled, 1-gang, 2 port, prowhite	universal opening
760249146	FP-LBL-4P-266	Faceplate Kit, labeled, 1-gang, 4 port, prowhite	universal opening
760249147	FP-LBL-6P-266	Faceplate Kit, labeled, 1-gang, 6 port, prowhite	universal opening
760249148	FP-NLBL-1P-266	Faceplate Kit, non-labeled, 1-gang, 1 port, prowhite	universal opening
760249149	FP-NLBL-2P-266	Faceplate Kit, non-labeled, 1-gang, 2 port, prowhite	universal opening
760249150	FP-NLBL-4P-266	Faceplate Kit, non-labeled, 1-gang, 4 port, prowhite	universal opening
760249151	FP-NLBL-6P-266	Faceplate Kit, non-labeled, 1-gang, 6 port, prowhite	universal opening
760248924	FP-LBL-1P-003	Faceplate Kit, labeled, 1-gang, 1 port, black	universal opening
760248925	FP-LBL-2P-003	Faceplate Kit, labeled, 1-gang, 2 port, black	universal opening
760248926	FP-LBL-4P-003	Faceplate Kit, labeled, 1-gang, 4 port, black	universal opening
760248927	FP-LBL-6P-003	Faceplate Kit, labeled, 1-gang, 6 port, black	universal opening
760248928	FP-NLBL-1P-003	Faceplate Kit, non-labeled, 1-gang, 1 port, black	universal opening
760248929	FP-NLBL-2P-003	Faceplate Kit, non-labeled, 1-gang, 2 port, black	universal opening
760248930	FP-NLBL-4P-003	Faceplate Kit, non-labeled, 1-gang, 4 port, black	universal opening
760248931	FP-NLBL-6P-003	Faceplate Kit, non-labeled, 1-gang, 6 port, black	universal opening
760249136	FP-LBL-1P-270	Faceplate Kit, labeled, 1-gang, 1 port, gray	universal opening
760249137	FP-LBL-2P-270	Faceplate Kit, labeled, 1-gang, 2 port, gray	universal opening
760249138	FP-LBL-4P-270	Faceplate Kit, labeled, 1-gang, 4 port, gray	universal opening
760249139	FP-LBL-6P-270	Faceplate Kit, labeled, 1-gang, 6 port, gray	universal opening
760249140	FP-NLBL-1P-270	Faceplate Kit, non-labeled, 1-gang, 1 port, gray	universal opening
760249141	FP-NLBL-2P-270	Faceplate Kit, non-labeled, 1-gang, 2 port, gray	universal opening
760249142	FP-NLBL-4P-270	Faceplate Kit, non-labeled, 1-gang, 4 port, gray	universal opening
760249143	FP-NLBL-6P-270	Faceplate Kit, non-labeled, 1-gang, 6 port, gray	universal opening
760249168	FP-LBL-1P-246	Faceplate Kit, labeled, 1-gang, 1 port, ivory	universal opening
760249169	FP-LBL-2P-246	Faceplate Kit, labeled, 1-gang, 2 port, ivory	universal opening
760249170	FP-LBL-4P-246	Faceplate Kit, labeled, 1-gang, 4 port, ivory	universal opening
760249171	FP-LBL-6P-246	Faceplate Kit, labeled, 1-gang, 6 port, ivory	universal opening
760249172	FP-NLBL-1P-246	Faceplate Kit, non-labeled, 1-gang, 1 port, ivory	universal opening
760249173	FP-NLBL-2P-246	Faceplate Kit, non-labeled, 1-gang, 2 port, ivory	universal opening
760249174	FP-NLBL-4P-246	Faceplate Kit, non-labeled, 1-gang, 4 port, ivory	universal opening
760249175	FP-NLBL-6P-246	Faceplate Kit, non-labeled, 1-gang, 6 port, ivory	universal opening
760249128	FP-LBL-1P-262	Faceplate Kit, labeled, 1-gang, 1 port, elec white	universal opening
760249129	FP-LBL-2P-262	Faceplate Kit, labeled, 1-gang, 2 port, elec white	universal opening
760249130	FP-LBL-4P-262	Faceplate Kit, labeled, 1-gang, 4 port, elec white	universal opening
760249131	FP-LBL-6P-262	Faceplate Kit, labeled, 1-gang, 6 port, elec white	universal opening
760249132	FP-NLBL-1P-262	Faceplate Kit, non-labeled, 1-gang, 1 port, elec white	universal opening
760249133	FP-NLBL-2P-262	Faceplate Kit, non-labeled, 1-gang, 2 port, elec white	universal opening
760249134	FP-NLBL-4P-262	Faceplate Kit, non-labeled, 1-gang, 4 port, elec white	universal opening
760249135	FP-NLBL-6P-262	Faceplate Kit, non-labeled, 1-gang, 6 port, elec white	universal opening
760249152	FP-LBL-1P-448	Faceplate Kit, labeled, 1-gang, 1 port, light almond	universal opening
760249153	FP-LBL-2P-448	Faceplate Kit, labeled, 1-gang, 2 port, light almond	universal opening
760249154	FP-LBL-4P-448	Faceplate Kit, labeled, 1-gang, 4 port, light almond	universal opening
760249155	FP-LBL-6P-448	Faceplate Kit, labeled, 1-gang, 6 port, light almond	universal opening
760249156	FP-NLBL-1P-448	Faceplate Kit, non-labeled, 1-gang, 1 port, light almond	universal opening
760249157	FP-NLBL-2P-448	Faceplate Kit, non-labeled, 1-gang, 2 port, light almond	universal opening
760249158	FP-NLBL-4P-448	Faceplate Kit, non-labeled, 1-gang, 4 port, light almond	universal opening
760249159	FP-NLBL-6P-448	Faceplate Kit, non-labeled, 1-gang, 6 port, light almond	universal opening
760249160	FP-LBL-1P-148	Faceplate Kit, labeled, 1-gang, 1 port, elec almond	universal opening
760249161	FP-LBL-2P-148	Faceplate Kit, labeled, 1-gang, 2 port, elec almond	universal opening
760249162	FP-LBL-4P-148	Faceplate Kit, labeled, 1-gang, 4 port, elec almond	universal opening
760249163	FP-LBL-6P-148	Faceplate Kit, labeled, 1-gang, 6 port, elec almond	universal opening
760249164	FP-NLBL-1P-148	Faceplate Kit, non-labeled, 1-gang, 1 port, elec almond	universal opening
760249165	FP-NLBL-2P-148	Faceplate Kit, non-labeled, 1-gang, 2 port, elec almond	universal opening
760249166	FP-NLBL-4P-148	Faceplate Kit, non-labeled, 1-gang, 4 port, elec almond	universal opening
760249167	FP-NLBL-6P-148	Faceplate Kit, non-labeled, 1-gang, 6 port, elec almond	universal opening

# Faceplates & Surface Mount Boxes



Material ID	Product Number	Description	Jack
<b>Faceplates</b>			
1-2111008-3	FP KT,LBL,SGL GNG,1P,SL,A.WHT	Faceplate Kit, labeled, 1-gang, 1 port, alpine white	SL/SLX
2111008-1	FP KT,LBL,SGL GNG,1P,SL,L.ALD	Faceplate Kit, labeled, 1-gang, 1 port, vertical orientation, almond	SL/SLX
1-2111009-1	FP KT,LBL,SGL GNG,2P,SL,E.IVY	Faceplate Kit, labeled, 1-gang, 2 port, electrical ivory	SL/SLX
1-2111009-3	FP KT,LBL,SGL GNG,2P,SL,A.WHT	Faceplate Kit, labeled, 1-gang, 2 port, alpine white	SL/SLX
2111009-1	FP KT,LBL,SGL GNG,2P,SL,L.ALD	Faceplate Kit, labeled, 1-gang, 2 port, vertical orientation, almond	SL/SLX
2111009-2	FP KT,LBL,SGL GNG,2P,SL,BLK	Faceplate Kit, labeled, 1-gang, 2 port, vertical orientation, black	SL/SLX
2111009-4	FP KT,LBL,SGL GNG,2P,SL,GRY	Faceplate Kit, labeled, 1-gang, 2 port, vertical orientation, gray	SL/SLX
1-2111010-3	FP KT,LBL,SGL GNG,3P,SL,A.WHT	Faceplate Kit, labeled, 1-gang, 3 port, alpine white	SL/SLX
2111010-1	FP KT,LBL,SGL GNG,3P,SL,L.ALD	Faceplate Kit, labeled, 1-gang, 3 port, vertical orientation, almond	SL/SLX
1-2111011-1	FP KT,LBL,SGL GNG,4P,SL,E.IVY	Faceplate Kit, labeled, 1-gang, 4 port, electrical ivory	SL/SLX
1-2111011-3	FP KT,LBL,SGL GNG,4P,SL,A.WHT	Faceplate Kit, labeled, 1-gang, 4 port, alpine white	SL/SLX
2111011-1	FP KT,LBL,SGL GNG,4P,SL,L.ALD	Faceplate Kit, labeled, 1-gang, 4 port, vertical orientation, almond	SL/SLX
2111011-2	FP KT,LBL,SGL GNG,4P,SL,BLK	Faceplate Kit, labeled, 1-gang, 4 port, vertical orientation, black	SL/SLX
2111011-4	FP KT,LBL,SGL GNG,4P,SL,GRY	Faceplate Kit, labeled, 1-gang, 4 port, vertical orientation, gray	SL/SLX
1-2111012-1	FP KT,LBL,SGL GNG,6P,SL,E.IVY	Faceplate Kit, labeled, 1-gang, 6 port, electrical ivory	SL/SLX
1-2111012-3	FP KT,LBL,SGL GNG,6P,SL,A.WHT	Faceplate Kit, labeled, 1-gang, 6 port, alpine white	SL/SLX
2111012-1	FP KT,LBL,SGL GNG,6P,SL,L.ALD	Faceplate Kit, labeled, 1-gang, 6 port, vertical orientation, almond	SL/SLX
2111012-2	FP KT,LBL,SGL GNG,6P,SL,BLK	Faceplate Kit, labeled, 1-gang, 6 port, vertical orientation, black	SL/SLX
2111012-4	FP KT,LBL,SGL GNG,6P,SL,GRY	Faceplate Kit, labeled, 1-gang, 6 port, vertical orientation, gray	SL/SLX
1-2111022-1	FP KIT,NLBL,SGL GNG,2P,SL,E.IVY	Faceplate Kit, non-labeled, 1-gang, 2 port, electrical ivory	SL/SLX
1-2111022-3	FP KIT,NLBL,SGL GNG,2P,SL,A.WHT	Faceplate Kit, non-labeled, 1-gang, 2 port, alpine white	SL/SLX
2111022-1	FP KIT,NLBL,SGL GNG,2P,SL,L.ALD	Faceplate Kit, non-labeled, 1-gang, 2 port, vertical orientation, almond	SL/SLX
2111022-2	FP KIT,NLBL,SGL GNG,2P,SL,BLK	Faceplate Kit, non-labeled, 1-gang, 2 port, vertical orientation, black	SL/SLX
2111022-4	FP KIT,NLBL,SGL GNG,2P,SL,GRY	Faceplate Kit, non-labeled, 1-gang, 2 port, vertical orientation, gray	SL/SLX
1-2111037-1	FP KT,LBL,SGL GNG,2P,KJ,E.IVY	Faceplate Kit, labeled, 1-gang, 2 port, electrical ivory	KJ
1-2111037-3	FP KT,LBL,SGL GNG,2P,KJ,A.WHT	Faceplate Kit, labeled, 1-gang, 2 port, alpine white	KJ
2111037-1	FP KT,LBL,SGL GNG,2P,KJ,L.ALD	Faceplate Kit, labeled, 1-gang, 2 port, almond	KJ
2111037-2	FP KT,LBL,SGL GNG,2P,KJ,BLK	Faceplate Kit, labeled, 1-gang, 2 port, black	KJ
2111037-4	FP KT,LBL,SGL GNG,2P,KJ,GRY	Faceplate Kit, labeled, 1-gang, 2 port, gray	KJ
2111039-1	FP KT,LBL,SGL GNG,4P,KJ,L.ALD	Faceplate Kit, labeled, 1-gang, 4 port, almond	KJ
2111039-2	FP KT,LBL,SGL GNG,4P,KJ,BLK	Faceplate Kit, labeled, 1-gang, 4 port, black	KJ
2111039-4	FP KT,LBL,SGL GNG,4P,KJ,GRY	Faceplate Kit, labeled, 1-gang, 4 port, gray	KJ
1-1375155-3		Faceplate, 2 port, angled, flush mount, alpine white	SL/SLX
1-1375155-1		Faceplate, 2 port, angled, flush mount, electric ivory	SL/SLX
1375155-1		Faceplate Kit, 1-gang, angled, 2 port, almond	SL/SLX
1375155-2		Faceplate, 2 port, angled, flush mount, black	SL/SLX
1-406185-3		Faceplate Kit, 4-port, angled, alpine white	SL/SLX
1-406185-1		Faceplate Kit, 4-port, angled, electric ivory	SL/SLX
406185-1		Faceplate Kit, 4-port, angled, almond	SL/SLX
406185-2		Faceplate Kit, 4-port, angled, black	SL/SLX




Material ID	Product Number	Description	Color
<b>Ceiling Flush Mount Faceplates</b>			
760253234	FP-CLBL-2P-262	2 Port Ceiling Flush Mount Faceplate	Elec White
760253235	FP-CLBL-2P-003	2 Port Ceiling Flush Mount Faceplate	Black

# Faceplates & Surface Mount Boxes




Material ID	Product Number	Description	Jack
<b>Surface Mount Boxes</b>			
760248524	KIT,SURF MT MODULE,1PT, LT.ALD	Surface Mount Module, 1 port, lt. almond	universal opening
760248523	KIT,SURF MT MODULE,1PT, PROWHITE	Surface Mount Module, 1 port, pro white	universal opening
760246267	KIT,SURF MT MODULE,1PT,BLK	Surface Mount Module, 1 port, black	universal opening
760248522	KIT,SURF MT MODULE,1PT,GRY	Surface Mount Module, 1 port, gray	universal opening
760248528	KIT,SURF MT MODULE,2PT, LT.ALD	Surface Mount Module, 2 port, lt. almond	universal opening
760248527	KIT,SURF MT MODULE,2PT, PROWHITE	Surface Mount Module, 2 port, pro white	universal opening
760246268	KIT,SURF MT MODULE,2PT,BLK	Surface Mount Module, 2 port, black	universal opening
760248526	KIT,SURF MT MODULE,2PT,GRY	Surface Mount Module, 2 port, gray	universal opening
1-1933671-1	KIT,SURF MT MODULE,4PT,E.IVY	Surface Mount Module, 4 port, electrical ivory	SL/SLX
1-1933671-3	KIT,SURF MT MODULE,4PT,A.WHT	Surface Mount Module, 4 port, alpine white	SL/SLX
1933671-1	KIT,SURF MT MODULE,4PT,LT.ALD	Surface Mount Module, 4 port, almond	SL/SLX
1933671-2	KIT,SURF MT MODULE,4PT,BLK	Surface Mount Module, 4 port, black	SL/SLX
1933671-4	KIT,SURF MT MODULE,4PT,GRY	Surface Mount Module, 4 port, gray	SL/SLX
1-1933674-1	KIT,SURF MT MODULE,6PT,E.IVY	Surface Mount Module, 6 port, electrical ivory	SL/SLX
1-1933674-3	KIT,SURF MT MODULE,6PT,A.WHT	Surface Mount Module, 6 port, alpine white	SL/SLX
1933674-1	KIT,SURF MT MODULE,6PT,LT.ALD	Surface Mount Module, 6 port, almond	SL/SLX
1933674-2	KIT,SURF MT MODULE,6PT,BLK	Surface Mount Module, 6 port, black	SL/SLX
1933674-4	KIT,SURF MT MODULE,6PT,GRY	Surface Mount Module, 6 port, gray	SL/SLX



Material ID	Product Number	Description	Environment	Fiber type	Fiber Count	Availability
<b>Fiber optic cables - Riser - Indoor</b>						
700208135	R-004-DS-5L-FSUAQ	Riser Distribution Cable, 4 fiber single-unit, OM3, aqua	Indoor - Riser	OM3	4 fiber	All Sub-Regions
700208143	R-006-DS-5L-FSUAQ	Riser Distribution Cable, 6 fiber single-unit, OM3, aqua	Indoor - Riser	OM3	6 fiber	All Sub-Regions
760008516	R-008-DS-5L-FSUAQ	Riser Distribution Cable, 8 fiber single-unit, OM3, aqua	Indoor - Riser	OM3	8 fiber	All Sub-Regions
700208150	R-012-DS-5L-FSUAQ	Riser Distribution Cable, 12 fiber single-unit, OM3, aqua	Indoor - Riser	OM3	12 fiber	All Sub-Regions
760018556	R-024-DS-5L-FSUAQ	Riser Distribution Cable, 24 fiber single-unit, OM3, aqua	Indoor - Riser	OM3	24 fiber	All Sub-Regions
760088641	R-004-DS-5K-FSUAQ	Riser Distribution Cable, 4 fiber single-unit, OM4, aqua	Indoor - Riser	OM4	4 fiber	All Sub-Regions
760012104	R-006-DS-5K-FSUAQ	Riser Distribution Cable, 6 fiber single-unit, OM4, aqua	Indoor - Riser	OM4	6 fiber	All Sub-Regions
760147603	R-008-DS-5K-FSUAQ	Riser Distribution Cable, 8 fiber single-unit, OM4, aqua	Indoor - Riser	OM4	8 fiber	All Sub-Regions
760012112	R-012-DS-5K-FSUAQ	Riser Distribution Cable, 12 fiber single-unit, OM4, aqua	Indoor - Riser	OM4	12 fiber	All Sub-Regions
760018564	R-024-DS-5K-FSUAQ	Riser Distribution Cable, 24 fiber single-unit, OM4, aqua	Indoor - Riser	OM4	24 fiber	All Sub-Regions
760004416	R-004-DS-8W-FSUYL	Riser Distribution Cable, 4 fiber single-unit, singlemode, yellow	Indoor - Riser	Singlemode	4 fiber	All Sub-Regions
760004424	R-006-DS-8W-FSUYL	Riser Distribution Cable, 6 fiber single-unit, singlemode, yellow	Indoor - Riser	Singlemode	6 fiber	All Sub-Regions
760004432	R-008-DS-8W-FSUYL	Riser Distribution Cable, 8 fiber single-unit, singlemode, yellow	Indoor - Riser	Singlemode	8 fiber	All Sub-Regions
760004440	R-012-DS-8W-FSUYL	Riser Distribution Cable, 12 fiber single-unit, singlemode, yellow	Indoor - Riser	Singlemode	12 fiber	All Sub-Regions
760018515	R-024-DS-8W-FSUYL	Riser Distribution Cable, 24 fiber single-unit, singlemode, yellow	Indoor - Riser	Singlemode	24 fiber	All Sub-Regions
<b>Fiber optic cables - LSZH - Indoor</b>						
700009822	N-004-DS-5L-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 4 fiber single-unit, OM3, aqua	Indoor - LSZH	OM3	4 fiber	All Sub-Regions - Excluded Brazil
700009780	N-006-DS-5L-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 6 fiber single-unit, OM3, aqua	Indoor - LSZH	OM3	6 fiber	All Sub-Regions - Excluded Brazil
760026336	N-008-DS-5L-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 8 fiber single-unit, OM3, aqua	Indoor - LSZH	OM3	8 fiber	All Sub-Regions - Excluded Brazil
700009749	N-012-DS-5L-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 12 fiber single-unit, OM3, aqua	Indoor - LSZH	OM3	12 fiber	All Sub-Regions - Excluded Brazil
760019109	N-024-DS-5L-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber single-unit, OM3, aqua	Indoor - LSZH	OM3	24 fiber	All Sub-Regions - Excluded Brazil
760184820	N-004-DS-5K-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 4 fiber single-unit, OM4, aqua	Indoor - LSZH	OM4	4 fiber	All Sub-Regions - Excluded Brazil
760012153	N-006-DS-5K-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 6 fiber single-unit, OM4, aqua	Indoor - LSZH	OM4	6 fiber	All Sub-Regions - Excluded Brazil
760192260	N-008-DS-5K-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 8 fiber single-unit, OM4, aqua	Indoor - LSZH	OM4	8 fiber	All Sub-Regions - Excluded Brazil
760012161	N-012-DS-5K-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 12 fiber single-unit, OM4, aqua	Indoor - LSZH	OM4	12 fiber	All Sub-Regions - Excluded Brazil
760019117	N-024-DS-5K-FSUAQ/D	Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber single-unit, OM4, aqua	Indoor - LSZH	OM4	24 fiber	All Sub-Regions - Excluded Brazil
760055038	N-004-DS-8W-FSUYL/D	Low Smoke Zero Halogen Riser Distribution Cable, 4 fiber single-unit, singlemode, yellow	Indoor - LSZH	Singlemode	4 fiber	All Sub-Regions - Excluded Brazil
760004242	N-006-DS-8W-FSUYL/D	Low Smoke Zero Halogen Riser Distribution Cable, 6 fiber single-unit, singlemode, yellow	Indoor - LSZH	Singlemode	6 fiber	All Sub-Regions - Excluded Brazil
760004259	N-008-DS-8W-FSUYL/D	Low Smoke Zero Halogen Riser Distribution Cable, 8 fiber single-unit, singlemode, yellow	Indoor - LSZH	Singlemode	8 fiber	All Sub-Regions - Excluded Brazil
760004267	N-012-DS-8W-FSUYL/D	Low Smoke Zero Halogen Riser Distribution Cable, 12 fiber single-unit, singlemode, yellow	Indoor - LSZH	Singlemode	12 fiber	All Sub-Regions - Excluded Brazil
760019075	N-024-DS-8W-FSUYL/D	Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber single-unit, singlemode, yellow	Indoor - LSZH	Singlemode	24 fiber	All Sub-Regions - Excluded Brazil



Material ID	Product Number	Description	Environment	Fiber type	Fiber Count	Availability
<b>Fiber optic cables - LSZH - Indoor/Outdoor</b>						
760046649	Z-004-DS-5L-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 4 fiber single-unit, OM3, black	Indoor/Outdoor - LSZH	OM3	4 fiber	All Sub-Regions
760039966	Z-006-DS-5L-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 6 fiber single-unit, OM3, black	Indoor/Outdoor - LSZH	OM3	6 fiber	All Sub-Regions
760031674	Z-008-DS-5L-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 8 fiber single-unit, OM3, black	Indoor/Outdoor - LSZH	OM3	8 fiber	All Sub-Regions
700210982	Z-012-DS-5L-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 12 fiber single-unit, OM3, black	Indoor/Outdoor - LSZH	OM3	12 fiber	All Sub-Regions
760070292	Z-024-DS-5L-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber single-unit, OM3, black	Indoor/Outdoor - LSZH	OM3	24 fiber	All Sub-Regions
760238329	Z-004-DS-5K-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 4 fiber single-unit, OM4, black	Indoor/Outdoor - LSZH	OM4	4 fiber	All Sub-Regions
760039974	Z-006-DS-5K-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 6 fiber single-unit, OM4, black	Indoor/Outdoor - LSZH	OM4	6 fiber	All Sub-Regions
760039982	Z-008-DS-5K-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 8 fiber single-unit, OM4, black	Indoor/Outdoor - LSZH	OM4	8 fiber	All Sub-Regions
760006650	Z-012-DS-5K-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 12 fiber single-unit, OM4, black	Indoor/Outdoor - LSZH	OM4	12 fiber	All Sub-Regions
760070300	Z-024-DS-5K-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber single-unit, OM4, black	Indoor/Outdoor - LSZH	OM4	24 fiber	All Sub-Regions
760068718	Z-004-DS-8W-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 4 fiber single-unit, singlemode, black	Indoor/Outdoor - LSZH	Singlemode	4 fiber	All Sub-Regions
760009753	Z-006-DS-8W-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 6 fiber single-unit, singlemode, black	Indoor/Outdoor - LSZH	Singlemode	6 fiber	All Sub-Regions
760073403	Z-008-DS-8W-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 8 fiber single-unit, singlemode, black	Indoor/Outdoor - LSZH	Singlemode	8 fiber	All Sub-Regions
760004184	Z-012-DS-8W-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 12 fiber single-unit, singlemode, black	Indoor/Outdoor - LSZH	Singlemode	12 fiber	All Sub-Regions
760070276	Z-024-DS-8W-FSUBK/D	Indoor/Outdoor Low Smoke Zero Halogen Riser Distribution Cable, 24 fiber single-unit, singlemode, black	Indoor/Outdoor - LSZH	Singlemode	24 fiber	All Sub-Regions



Material ID	Product Number	Description	Environment	Fiber type	Fiber Count	Availability
<b>Fiber optic cables -Plenum - Indoor</b>						
700009772	P-006-DS-5L-FSUAQ	Plenum Distribution Cable, single-unit, 6 fiber, OM3, aqua	Indoor - Plenum	OM3	6 fiber	All Sub-Regions
700009731	P-012-DS-5L-FSUAQ	Plenum Distribution Cable, single-unit, 12 fiber, OM3, aqua	Indoor - Plenum	OM3	12 fiber	All Sub-Regions
760018689	P-024-DS-5L-FSUAQ	Plenum Distribution Cable, single-unit, 24 fiber, OM3, aqua	Indoor - Plenum	OM3	24 fiber	All Sub-Regions
760012138	P-006-DS-5K-FSUAQ	Plenum Distribution Cable, single-unit, 6 fiber, OM4, aqua	Indoor - Plenum	OM4	6 fiber	All Sub-Regions
760006411	P-012-DS-5K-FSUAQ	Plenum Distribution Cable, single-unit, 12 fiber, OM4, aqua	Indoor - Plenum	OM4	12 fiber	All Sub-Regions
760018697	P-024-DS-5K-FSUAQ	Plenum Distribution Cable, single-unit, 24 fiber, OM4, aqua	Indoor - Plenum	OM4	24 fiber	All Sub-Regions
760004333	P-006-DS-8W-FSUYL	Plenum Distribution Cable, single-unit, 6 fiber, singlemode, yellow	Indoor - Plenum	Singlemode	6 fiber	All Sub-Regions
760004358	P-012-DS-8W-FSUYL	Plenum Distribution Cable, single-unit, 12 fiber, singlemode, yellow	Indoor - Plenum	Singlemode	12 fiber	All Sub-Regions
760018630	P-024-DS-8W-FSUYL	Plenum Distribution Cable, single-unit, 24 fiber, singlemode, yellow	Indoor - Plenum	Singlemode	24 fiber	All Sub-Regions
760127639	P-006-DZ-5L-FSUAQ	Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, single-unit, 6 fiber, OM3, aqua	Indoor - Plenum	OM3	6 fiber	Mexico - CA&C
760127647	P-012-DZ-5L-FSUAQ	Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, single-unit, 12 fiber, OM3, aqua	Indoor - Plenum	OM3	12 fiber	Mexico - CA&C
760128181	P-006-DZ-5K-FSUAQ	Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, single-unit, 6 fiber, OM4, aqua	Indoor - Plenum	OM4	6 fiber	Mexico - CA&C
760128017	P-012-DZ-5K-FSUAQ	Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, single-unit, 12 fiber, OM4, aqua	Indoor - Plenum	OM4	12 fiber	Mexico - CA&C
760127795	P-006-DZ-8W-FSUYL	Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, single-unit, 6 fiber, singlemode, yellow	Indoor - Plenum	Singlemode	6 fiber	Mexico - CA&C
760127803	P-012-DZ-8W-FSUYL	Plenum Distribution Cable, interlocking aluminum armored with plenum jacket, single-unit, 12 fiber, singlemode, yellow	Indoor - Plenum	Singlemode	12 fiber	Mexico - CA&C




Material ID	Product Number	Description	Availability
<b>Fiber optic cables - Outdoor - All Dielectric - SLT</b>			
760139592	D-004-LN-5L-F04NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 4 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760054163	D-006-LN-5L-F06NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 6 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760151076	D-008-LN-5L-F02NS/LTS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 8 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760054171	D-012-LN-5L-F12NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 12 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760054189	D-024-LN-5L-F12NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 24 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760238342	D-004-LN-5K-F04NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 4 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760054270	D-006-LN-5K-F06NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 6 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760238343	D-008-LN-5K-F08NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 8 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760054288	D-012-LN-5K-F12NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 12 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760054296	D-024-LN-5K-F12NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 24 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760053835	D-006-LN-8W-F06NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 6 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
760053843	D-012-LN-8W-F12NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 12 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
760053850	D-024-LN-8W-F12NS	Single Jacket All-Dielectric, Gel-Free, Outdoor Stranded Loose Tube Cable, 24 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
<b>Fiber optic cables - Outdoor - Metallic Armor - SLT</b>			
760238353	D-004-LA-5L-F04NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 4 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760053611	D-006-LA-5L-F06NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 6 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760238354	D-008-LA-5L-F08NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 8 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760053629	D-012-LA-5L-F12NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 12 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760053637	D-024-LA-5L-F12NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 24 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760210823	D-004-LA-5K-F04NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 4 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760053728	D-006-LA-5K-F06NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 6 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760238344	D-008-LA-5K-F08NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 8 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760053736	D-012-LA-5K-F12NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 12 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760053744	D-024-LA-5K-F12NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 24 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760053272	D-006-LA-8W-F06NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 6 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
760053280	D-012-LA-8W-F12NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 12 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
760053298	D-024-LA-8W-F12NS	Single Jacket/Single Armor, Gel-Free, Outdoor Stranded Loose Tube Cable, 24 fiber, singlemode, black	All Sub-Regions - Excluding Brazil






Material ID	Product Number	Description	Availability
<b>Fiber optic cables - Indoor/Outdoor - Metallic Armor - SLT</b>			
760238364	Z-004-LN-5L-F04BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 4 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760154831	Z-006-LN-5L-F06BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 6 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760238365	Z-008-LN-5L-F08BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 8 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760154849	Z-012-LN-5L-F12BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 12 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760228965	Z-024-LN-5K-F12BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 24 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760229682	Z-004-LN-5K-F04BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 4 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760229690	Z-006-LN-5K-F06BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 6 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760238366	Z-008-LN-5K-F08BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 8 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760228684	Z-012-LN-5K-F12BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 12 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760228965	Z-024-LN-5K-F12BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 24 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760154757	Z-006-LN-8W-F06BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 6 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
760154765	Z-012-LN-8W-F12BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 12 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
760154773	Z-024-LN-8W-F12BK/25D	Indoor/Outdoor, Single Jacket All-Dielectric, LSZH, Gel-Free, Stranded Loose Tube Cable, 24 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
<b>Fiber optic cables - Indoor/Outdoor - All Dielectric - SLT</b>			
760155036	Z-006-LA-5L-F06BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, OM3, black	All Sub-Regions - Excluding Brazil
760155044	Z-012-LA-5L-F12BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, OM3, black	All Sub-Regions - Excluding Brazil
760155051	Z-024-LA-5L-F12BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, OM3, black	All Sub-Regions - Excluding Brazil
760239012	Z-006-LA-5K-F06BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, OM4, black	All Sub-Regions - Excluding Brazil
760218529	Z-012-LA-5K-F12BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, OM4, black	All Sub-Regions - Excluding Brazil
760239011	Z-024-LA-5K-F12BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, OM4, black	All Sub-Regions - Excluding Brazil
760154955	Z-006-LA-8W-F06BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, singlemode, black	All Sub-Regions - Excluding Brazil
760154963	Z-012-LA-8W-F12BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, singlemode, black	All Sub-Regions - Excluding Brazil
760154971	Z-024-LA-8W-F12BK/25D/C	Indoor/Outdoor, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Gel-Free, Stranded Loose Tube Cable, singlemode, black	All Sub-Regions - Excluding Brazil





Material ID	Product Number	Description	Availability
<b>Fiber optic cables - Indoor/Outdoor - Dielectric HTS - SLT</b>			
760243320	C-006-LN-5L-M06BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 6 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760243323	C-012-LN-5L-M12BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 12 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760243326	C-024-LN-5L-M12BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 24 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760243319	C-006-LN-5K-M06BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 6 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760243322	C-012-LN-5K-M12BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 12 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760243325	C-024-LN-5K-M12BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 24 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760245923	C-006-LN-8W-M06BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 6 fiber, OS2, black	All Sub-Regions - Excluding Brazil
760243324	C-012-LN-8W-M12BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 12 fiber, OS2, black	All Sub-Regions - Excluding Brazil
760243327	C-024-LN-8W-M12BK/20G/HTS/D	Indoor/Outdoor High Tensile Strength LSZH - All-Dielectric Single Jacket, Gel-Filled, Stranded Loose Tube, 24 fiber, OS2, black	All Sub-Regions - Excluding Brazil
<b>Fiber optic cables - Outdoor - All Dielectric - SLT</b>			
860646618/DB	O-006-LN-8W-M06BK/20G	Single Jacket All-Dielectric, Gel-Filled, Outdoor Stranded Loose Tube Cable 6 fiber, OS2, black	All Sub-Regions - Excluding Brazil
860646619/DB	O-012-LN-8W-M12BK/20G	Single Jacket All-Dielectric, Gel-Filled, Outdoor Stranded Loose Tube Cable 12 fiber, OS2, black	All Sub-Regions - Excluding Brazil
860646620/DB	O-024-LN-8W-M12BK/20G	Single Jacket All-Dielectric, Gel-Filled, Outdoor Stranded Loose Tube Cable 24 fiber, OS2, black	All Sub-Regions - Excluding Brazil
<b>Fiber optic cables - Indoor/Outdoor - All Dielectric - Dry - Riser - SLT</b>			
760112417	R-006-LN-8W-F06BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 6 fiber, Singlemode, black	All Sub-Regions - Excluding Brazil
760112425	R-012-LN-8W-F12BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 12 fiber, Singlemode, black	All Sub-Regions - Excluding Brazil
760112433	R-024-LN-8W-F12BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 24 fiber, Singlemode, black	All Sub-Regions - Excluding Brazil
760112599	R-006-LN-5L-F06BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 6 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760112607	R-012-LN-5L-F12BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 12 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760112615	R-024-LN-5L-F12BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 24 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760112656	R-006-LN-5K-F06BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 6 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760112664	R-012-LN-5K-F12BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 12 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760112672	R-024-LN-5K-F12BK/25D/LTS	Indoor/Outdoor, Single Jacket All-Dielectric, Riser, Gel-Free, Stranded Loose Tube Cable, 24 fiber, OM4, black	All Sub-Regions - Excluding Brazil



Material ID	Product Number	Description	Availability
<b>Fiber optic cables - Outdoor - Metallic Armor - SLT</b>			
760177832	O-006-LA-5L-F06NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 6 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760177840	O-012-LA-5L-F12NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 12 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760177857	O-024-LA-5L-F12NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 24 fiber, OM3, black	All Sub-Regions - Excluding Brazil
760177790	O-006-LA-5K-F06NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 6 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760177808	O-012-LA-5K-F12NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 12 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760177816	O-024-LA-5K-F12NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 24 fiber, OM4, black	All Sub-Regions - Excluding Brazil
760177907	O-006-LA-8W-F06NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 6 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
760177915	O-012-LA-8W-F12NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 12 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
760177923	O-024-LA-8W-F12NS/25T	Single Jacket/Single Armor, Gel-Filled, Outdoor Stranded Loose Tube Cable 24 fiber, singlemode, black	All Sub-Regions - Excluding Brazil
<b>Fiber optic cables - Outdoor - Metallic Armor - CLT</b>			
BR760171199	O-012-CA-5L-F12NS	Single Jacket All-Dielectric, Gel-Filled, Outdoor Central Tube Cable, 12 fiber, OM3, black	Brazil
760248538	O-012-CA-5L-F12NS	Single Jacket All-Dielectric, Gel-Filled, Outdoor Central Tube Cable, 24 fiber, OM3, black	Brazil
BR760245196	O-012-CA-5K-F12NS	Single Jacket All-Dielectric, Gel-Filled, Outdoor Central Tube Cable, 12 fiber, OM4, black	Brazil
BR760239055	O-024-CA-5K-F12NS	Single Jacket All-Dielectric, Gel-Filled, Outdoor Central Tube Cable, 24 fiber, OM4, black	Brazil
760003947	O-012-CA-8W-F12NS	Single Jacket All-Dielectric, Gel-Filled, Outdoor Central Tube Cable, 12 fiber, singlemode, black	Brazil
760003954	O-024-CA-8W-F12NS	Single Jacket All-Dielectric, Gel-Filled, Outdoor Central Tube Cable, 24 fiber, singlemode, black	Brazil

### 1000-type solutions




Material ID	Product Number	Description	Rack Units	Availability
<b>1000-type panel and wall enclosures</b>				
760249997	EPX-1U-PNL-ENC	EPX 1U sliding panel, accepts (3) LGX/PNL style splice cassettes, modules or panels, providing up to 36 duplex LC ports	1	All Sub-Regions
760251043	EPX-1U-PNL-ENC-FX	EPX 1U fixed panel, accepts (3) LGX/PNL style splice cassettes, modules or panels, providing up to 36 duplex LC ports	1	All Sub-Regions
760251045	EPX-2U-PNL-ENC	EPX 2U sliding panel, accepts (6) LGX/PNL style splice cassettes, modules or panels, providing up to 72 duplex LC ports	2	All Sub-Regions
760251047	EPX-2U-PNL-ENC-FX	EPX 2U fixed panel, accepts (6) LGX/PNL style splice cassettes, modules or panels, providing up to 72 duplex LC ports	2	All Sub-Regions
760251049	EPX-4U-PNL-ENC	EPX 4U sliding panel, accepts (12) LGX/PNL style splice cassettes, modules or panels, providing up to 144 duplex LC ports	4	All Sub-Regions
760251051	EPX-4U-PNL-ENC-FX	EPX 4U fixed panel, accepts (12) LGX/PNL style splice cassettes, modules or panels, providing up to 144 duplex LC ports	4	All Sub-Regions
760251099	EPX-1U-PNL-OPEN-FX	EPX 1U open fixed panel, accepts (3) LGX/PNL style splice cassettes, modules or panels, providing up to 36 duplex LC ports	1	All Sub-Regions



Material ID	Product Number	Description
<b>LGX/1000 style wall boxes</b>		
760248904	WB2-EMT-BK-1P-PNL	24 LC
760248905	WB2-EMT-BK-2P-PNL	48 LC
760248906	WB2-EMT-BK-4P-PNL	96 LC
760248907	WB2-EMT-BK-8P-PNL	192 LC

### 1000-type solutions



Material ID	Product Number	Description	Availability
<b>1000-type adapter plates</b>			
760148171	PNL-BK-024-MFA-LC02-AQ-NS	OM4 LC, 24 fiber, aqua duplex adapter, black panel, no shutter	All Sub-Regions
760148056	PNL-BK-012-MFA-LC12-AQ	OM4 LC, 12 fiber, aqua ganged adapter, black panel	All Sub-Regions
760147975	PNL-BK-006-MFA-SC06-AQ	OM4 SC, 6 fiber, aqua ganged adapter, black panel	All Sub-Regions
760148189	PNL-BK-024-MFA-LC02-BG-NS	OM3 LC, 24 fiber, beige duplex adapter, black panel, no shutter	All Sub-Regions
760148064	PNL-BK-012-MFA-LC12-BG	OM3 LC, 12 fiber, beige ganged adapter, black panel	All Sub-Regions
760147983	PNL-BK-006-MFA-SC06-BG	OM3 SC, 6 fiber, beige ganged adapter, black panel	All Sub-Regions
760021790	PNL-BK-012-MFA-SC02-BG	OM3 SC, 12 fiber, beige duplex adapter, black panel	All Sub-Regions
760066076	PNL-BK-012-MFA-SC02-AQ	OM4 SC, 12 fiber, aqua duplex adapter, black panel	All Sub-Regions
760148361	PNL-BK-024-SFA-LC02-BL-NS	Singlemode LC, 24 fiber, blue duplex adapter, black panel, no shutter	All Sub-Regions
760148254	PNL-BK-012-SFA-LC12-BL	Singlemode LC, 12 fiber, blue ganged adapter, black panel	All Sub-Regions
760147637	PNL-BK-012-AFA-LC12-GR	Singlemode LC angled, 12 fiber, green ganged adapter, black panel	All Sub-Regions
760147652	PNL-BK-006-AFA-SC06-GR	Singlemode SC angled, 6 fiber, green ganged adapter, black panel	All Sub-Regions
760027714	PNL-BK-012-SFA-SC02-BL	Singlemode SC, 12 fiber, blue duplex adapters, black panel	All Sub-Regions
760148213	PNL-BK-006-SFA-SC06-BL	Singlemode SC, 6 fiber, blue ganged adapter, black panel	All Sub-Regions
760150094	PNL-BK-024-AFA-LC02-GR-NS	Singlemode LC/APC, 24 fiber, green duplex adapter, black panel, no shutter	All Sub-Regions
760117267	PNL-BK-012-AFA-SC02-GR	Singlemode SC/APC, 12 fiber, green duplex adapter, black panel	All Sub-Regions
760149344	PNL-BK-012-MFA-LC02-AQ-NS	OM4 panel, 6 multimode duplex LC adapters, aqua, no shutter	All Sub-Regions
760149351	PNL-BK-012-SFA-LC02-BL-NS	Singlemode panel, 6 singlemode duplex LC adapters, blue, no shutter	All Sub-Regions
760149328	PNL-BK-012-AFA-LC02-GR-NS	Singlemode panel, 6 singlemode duplex LC/APC adapters, green, no shutter	All Sub-Regions
760015412	RFE-PNL-2-MPO	Adapter panel, black, 1000-type, with 2 12 fiber MPO adapters	All Sub-Regions
760034280	RFE-PNL-6-MPO	Adapter panel, black, 1000-type, with 6 12 fiber MPO adapters	All Sub-Regions
760056077	RFE-PNL-8-MPO	Adapter panel, black, 1000-type, with 8 12 fiber MPO adapters	All Sub-Regions

Note: MPO listed above are Type B

### 1000-type solutions



Material ID	Product Number	Description	Availability
<b>1000-type splice cassettes</b>			
760221739	PNL-CS-12LCX-PT	Splicing cassette, 12 LC OM4, 900µm	All Sub-Regions
760221697	PNL-CS-24LCX-PT	Splicing cassette, 24 LC OM4, 900µm	All Sub-Regions
760221770	PNL-CS-12SCX-PT	Splicing cassette, 12 SC OM4, 900µm	All Sub-Regions
760221747	PNL-CS-12LCW-PT	Splicing cassette, 12 LC Singlemode, 900µm	All Sub-Regions
760221705	PNL-CS-24LCW-PT	Splicing cassette, 24 LC Singlemode, 900µm	All Sub-Regions
760221788	PNL-CS-12SCW-PT	Splicing cassette, 12 SC Singlemode, 900µm	All Sub-Regions
760236500	PNL-CS-12LCX	Splicing cassette, 12 LC OM4, no pigtail	All Sub-Regions
760236501	PNL-CS-12LCW	Splicing cassette, 12 LC Singlemode, no pigtail	All Sub-Regions
760236502	PNL-CS-12LAW	Splicing cassette, 12 LC APC Singlemode®, no pigtail	All Sub-Regions
760236503	PNL-CS-24LCX	Splicing cassette, 24 LC OM4, no pigtail	All Sub-Regions
760236504	PNL-CS-24LCW	Splicing cassette, 24 LC Singlemode, no pigtail	All Sub-Regions
760236505	PNL-CS-24LAW	Splicing cassette, 24 LC APC Singlemode, no pigtail	All Sub-Regions
760236506	PNL-CS-12SCX	Splicing cassette, 12 SC OM4, no pigtail	All Sub-Regions
760236507	PNL-CS-12SCW	Splicing cassette, 12 SC Singlemode, no pigtail	All Sub-Regions
760236508	PNL-CS-12SAW	Splicing cassette, 12 SC APC Singlemode, no pigtail	All Sub-Regions

## G2 solutions



Material ID	Product Number	Description	Rack Units	Availability
<b>G2 panels</b>				
760249998	EPX-1U-MOD-ENC	EPX 1U sliding panel, accepts (4) G2 style splice cassettes, modules or adapter packs, providing up to 48 duplex LC ports	1	All Sub-Regions
760251042	EPX-1U-MOD-ENC-FX	EPX 1U fixed panel, accepts (4) G2 style splice cassettes, modules or adapter packs, providing up to 48 duplex LC ports	1	All Sub-Regions
760251044	EPX-2U-MOD-ENC	EPX 2U sliding panel, accepts (8) G2 style splice cassettes, modules or adapter packs, providing up to 96 duplex LC ports	2	All Sub-Regions
760251046	EPX-2U-MOD-ENC-FX	EPX 2U fixed panel, accepts (8) G2 style splice cassettes, modules or adapter packs, providing up to 96 duplex LC ports	2	All Sub-Regions
760251048	EPX-4U-MOD-ENC	EPX 4U sliding panel, accepts (16) G2 style splice cassettes, modules or adapter packs, providing up to 192 duplex LC ports	4	All Sub-Regions
760251050	EPX-4U-MOD-ENC-FX	EPX 4U fixed panel, accepts (16) G2 style splice cassettes, modules or adapter packs, providing up to 192 duplex LC ports	4	All Sub-Regions
760251098	EPX-1U-MOD-OPEN-FX	EPX 1U open fixed panel, accepts (4) G2 style splice cassettes, modules or adapter packs, providing up to 48 duplex LC ports	1	All Sub-Regions
760167874	RP-MOD-012-TS-MPO-LC02	LGX/1000 LL singlemode MPO12 module, 12 fibers		All Sub-Regions
760167924	RP-MOD-024-TS-MPO-LC02	LGX/1000 LL singlemode MPO12 module, 24 fibers		All Sub-Regions
760167866	RP-MOD-012-LS-MPO-LC02	LGX/1000 LL multimode OM4 MPO12 module, 12 fibers		All Sub-Regions
760167916	RP-MOD-024-LS-MPO-LC02	LGX/1000 LL multimode OM4 MPO12 module, 24 fibers		All Sub-Regions
760209940	HD-1U	CommScope HD 1U sliding fiber panel, accepts (4) G2 ULL modules or MPO panels, providing up to 48 duplex LC ports or up to 32 MPO ports	1	All Sub-Regions
760209957	HD-2U	CommScope HD 2U sliding fiber panel, accepts (8) G2 ULL modules or MPO panels, providing up to 96 duplex LC ports or up to 64 MPO ports	2	All Sub-Regions
760209965	HD-4U	CommScope HD 4U sliding fiber panel, accepts (16) G2 ULL modules or MPO panels, providing up to 192 duplex LC ports or up to 128 MPO ports	4	All Sub-Regions
760210732	HD-1U-FX	CommScope HD 1U fixed fiber panel, accepts (4) G2 ULL modules or MPO panels, providing up to 48 duplex LC ports or up to 32 MPO ports	1	All Sub-Regions
760210740	HD-2U-FX	CommScope HD 2U fixed fiber panel, accepts (8) G2 ULL modules or MPO panels, providing up to 96 duplex LC ports or up to 64 MPO ports	2	All Sub-Regions
760210757	HD-4U-FX	CommScope HD 4U fixed fiber panel, accepts (16) G2 ULL modules or MPO panels, providing up to 192 duplex LC ports or up to 128 MPO ports	4	All Sub-Regions
760231506	HD-1U-SP	CommScope HD 1U Sliding fiber panel, accepts (4) 360G2 pigtail cassettes or 360DP panels, providing field term/splice capability up to 48 duplex LC ports	1	All Sub-Regions
760231514	HD-2U-SP	CommScope HD 2U Sliding fiber panel, accepts (8) 360G2 pigtail cassettes or 360DP panels, providing field term/splice capability up to 96 duplex LC ports	2	All Sub-Regions
760231522	HD-4U-SP	CommScope HD 4U Sliding fiber panel, accepts (12) 360G2 pigtail cassettes or 360DP panels, providing field term/splice capability up to 192 duplex LC ports	4	All Sub-Regions
760227306	UD-2U	CommScope UD 2U sliding fiber panel, accepts (12) G2 ULL modules or MPO panels, providing up to 144 duplex LC ports or up to 96 MPO ports	2	All Sub-Regions
760227314	UD-4U	CommScope UD 4U sliding fiber panel, accepts (24) G2 ULL modules or MPO panels, providing up to 288 duplex LC ports or up to 192 MPO ports	4	All Sub-Regions
760218461	UD-2U-FX	CommScope UD 2U fixed fiber panel, accepts (12) G2 ULL modules or MPO panels, providing up to 144 duplex LC ports or up to 96 MPO ports	2	All Sub-Regions
760218479	UD-4U-FX	CommScope UD 4U fixed fiber panel, accepts (24) G2 ULL modules or MPO panels, providing up to 288 duplex LC ports or up to 192 MPO ports	4	All Sub-Regions

## G2 solutions



Material ID	Product Number	Description	Availability
<b>G2 wall enclosures</b>			
760248902	WB2-EMT-BK-4P-MOD	Wall Mount Building Enclosure configured for four G2 style modules, splice cassettes or adapter packs	All Sub-Regions
760248903	WB2-EMT-BK-8P-MOD	Wall Mount Building Enclosure configured for eight G2 Style modules, splice cassettes or adapter packs	All Sub-Regions
760248901	WB2-EMT-BK-2P-MOD	Wall Mount Building Enclosure configured for two G2 Style modules, splice cassettes or adapter packs	All Sub-Regions
760248900	WB2-EMT-BK-1P-MOD	Wall Mount Building Enclosure configured for one G2 Style module, splice cassette or adapter pack	All Sub-Regions



Material ID	Product Number	Description	Availability
<b>G2 adapter panels</b>			
760230938	360DPis-12LC-LS	360 Distribution adapter pack 12 LC with internal shutters, Multimode OM4, aqua	All Sub-Regions
760236043	360DPis-12LC-WB	360 Distribution adapter pack 12 LC with internal shutters, Multimode OM5, lime green	All Sub-Regions
760230946	360DPis-12LC-SM	360 Distribution adapter pack 12 LC with internal shutters, Singlemode, blue	All Sub-Regions
760230961	360DPis-12LCA-SM	360 Distribution adapter pack 12 LC with internal shutters, APC Singlemode, green	All Sub-Regions
760216754	360DPis-24LC-LS	360 Distribution adapter pack 24 LC with internal shutters, Multimode OM4, aqua	All Sub-Regions
760236041	360DPis-24LC-WB	360 Distribution adapter pack 24 LC with internal shutters, Multimode OM5, lime green	All Sub-Regions
760216762	360DPis-24LC-SM	360 Distribution adapter pack 24 LC with internal shutters, Singlemode, blue	All Sub-Regions
760216770	360DPis-24LCA-SM	360 Distribution adapter pack 24 LC with internal shutters, APC Singlemode, green	All Sub-Regions



360G2 Cartridge 12-LC-LS-AQ    360G2 Cartridge 12-LCA-SM-GR    360G2 Cartridge 12-LC-SM-BL

Material ID	Product Number	Description	Availability
<b>G2 pigtail cassettes</b>			
760109256	360G2 Cassette 12-LC-LS-AQ	360G2 cassette 12 LC multimode OM4, aqua	All Sub-Regions
760109272	360G2 Cassette 12-LC-SM-BL	360G2 cassette 12 LC singlemode, blue	All Sub-Regions
760109280	360G2 Cassette 12-LCA-SM-GR	360G2 cassette 12 LC angled singlemode, green	All Sub-Regions
760109298	360G2 Cassette 6-SC-LS-AQ	360G2 cassette 6 SC multimode OM4, aqua	All Sub-Regions
760109314	360G2 Cassette 6-SC-SM-BL	360G2 cassette 6 SC singlemode, blue	All Sub-Regions
760109322	360G2 Cassette 6-SCA-SM-GR	360G2 cassette 6 SC angled singlemode, green	All Sub-Regions
760109470	360G2 Cassette 12-LC-LS-AQ-Pigtails	360G2 cassette 12 LC multimode, aqua with pigtails	All Sub-Regions
760109496	360G2 Cassette 12-LC-SM-BL-Pigtails	360G2 cassette 12 LC singlemode, blue with pigtails	All Sub-Regions
760109504	360G2 Cassette 12-LCA-SM-GR-Pigtails	360G2 cassette 12 LC angled singlemode, green with pigtails	All Sub-Regions
760109512	360G2 Cassette 6-SC-LS-AQ-Pigtails A	360G2 cassette 6 SC multimode, aqua with pigtails A	All Sub-Regions
760109520	360G2 Cassette 6-SC-LS-AQ-Pigtails B	360G2 cassette 6 SC multimode, aqua with pigtails B	All Sub-Regions
760109553	360G2 Cassette 6-SC-SM-BL-Pigtails A	360G2 cassette 6 SC singlemode, blue with pigtails A	All Sub-Regions
760109561	360G2 Cassette 6-SC-SM-BL-Pigtails B	360G2 cassette 6 SC singlemode, blue with pigtails B	All Sub-Regions
760109579	360G2 Cassette 6-SCA-SM-GR-Pigtails A	360G2 cassette 6 SC angled singlemode, green with pigtails A	All Sub-Regions
760109587	360G2 Cassette 6-SCA-SM-GR-Pigtails B	360G2 cassette 6 SC angled singlemode, green with pigtails B	All Sub-Regions



### G2 solutions



G2-SP-12LCX-PT

Material ID	Product Number	Description	Availability
<b>G2 splice cassettes</b>			
760244927	G2-SP-24LCX-PT	G2 splice cassette, 24LC, OM4, with pigtails	All Sub-Regions
760244929	G2-SP-24LCG-PT	G2 splice cassette, 24LC, OS2, with pigtails	All Sub-Regions
760245398	G2-SP-24LCV-PT	G2 splice cassette, 24LC, OM5, with pigtails	All Sub-Regions
760245961	G2-SP-24LAG-PT	G2 splice cassette, 24LC/APC, OS2, with pigtails	All Sub-Regions
760245399	G2-SP-12LCX-PT	G2 splice cassette, 12LC, OM4, with pigtails	All Sub-Regions
760245401	G2-SP-12LCG-PT	G2 splice cassette, 12LC, OS2, with pigtails	All Sub-Regions
760245403	G2-SP-12LCV-PT	G2 splice cassette, 12LC, OM5, with pigtails	All Sub-Regions
760245960	G2-SP-12LAG-PT	G2 splice cassette, 12LC/APC, OS2, with pigtails	All Sub-Regions
760245494	G2-SP-24LC	G2 splice cassette, 24LC, no pigtails	All Sub-Regions
760245495	G2-SP-12LC	G2 splice cassette, 12LC, no pigtails	All Sub-Regions
760245496	G2-SP-12SC	G2 splice cassette, 12SC, no pigtails	All Sub-Regions

Material ID	Product Number	Description	Rack Units	Availability
<b>G2 accessories</b>				
760207944	HD-1U-REAR-EXT	1U Rear cable extension	1	All Sub-Regions
760209627	HD-2U-REAR-EXT-06-KIT	2U Rear cable extension	2	All Sub-Regions
760209981	HD-4U-REAR-EXT-06-KIT	4U Rear cable extension—6 cable entries	4	All Sub-Regions
760209999	HD-4U-REAR-EXT-12-KIT	4U Rear cable extension—12 cable entries	4	All Sub-Regions
760209619	CABLE-MOUNT-KIT-12	Cable attachment molding x 12	-	All Sub-Regions
760211078	HD-1U-REAR-DOOR-COVER	1U Rear door	1	All Sub-Regions
760210286	HD-2U-REAR-DOOR	2U Rear door	2	All Sub-Regions
760210294	HD-4U-REAR-DOOR	4U Rear door	4	All Sub-Regions
760109462	360G2-MOD-BLANK-4PK	3CommScope 360G2 modular panel blank, 4 Panels	-	All Sub-Regions
760058677	RMB-6-1/2	InstaPATCH Plus attachment bracket, rack mounted, six 1/2" fittings	-	All Sub-Regions
760058685	RMB-6-3/8	InstaPATCH Plus attachment bracket, rack mounted, six 3/8" fittings	-	All Sub-Regions
760241378	AGL-SPLICE-48	AGL Fiber Optic Splice Tray Kit, stackable, 48-fiber capacity		All Sub-Regions



## Duplex patch cords



Material ID	Fiber Type	Jacket	Performance - Cable OD	Availability
<b>LC to LC duplex patch cords</b>				
FFZLCLC42-MXFxxx	OM3	LSZH/Riser	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FFXLCLC42-MXFxxx	OM4	LSZH/Riser	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FFVLCLC42-MXFxxx	OM5	LSZH/Riser	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FFWLCLC42-JXFxxx	OS2	LSZH/Riser	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FDXLCLC42-MXFxxx	OM4	Plenum	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FDVLCLC42-NXFxxx	OM5	Plenum	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FDWLCLC42-JXFxxx	OS2	Plenum	LL - 1.6mm - Duplex - Zip	All Sub-Regions
Y-2105027-X	OM3	LSZH/Riser	LL - 1.6mm - Duplex - Zip	Brazil
Y-2105061-X	OM4	LSZH/Riser	LL - 1.6mm - Duplex - Zip	Brazil
Y-2105028-X	OS2	LSZH/Riser	LL - 1.6mm - Duplex - Zip	Brazil
UFXLULUK2-MXFxxx	OM4	LSZH/Riser	ULL - 1.5mm - Duplex - Uniboot	All Sub-Regions
UFVLULUK2-NXFxxx	OM5	LSZH/Riser	ULL - 1.5mm - Duplex - Uniboot	All Sub-Regions
UFGLULUK2-JXFxxx	OS2	LSZH/Riser	ULL - 1.5mm - Duplex - Uniboot	All Sub-Regions
UDXLULUK2-MXFxxx	OM4	Plenum	ULL - 1.5mm - Duplex - Uniboot	All Sub-Regions
UDVLULUK2-NXFxxx	OM5	Plenum	ULL - 1.5mm - Duplex - Uniboot	All Sub-Regions
UDGLULUK2-JXFxxx	OS2	Plenum	ULL - 1.5mm - Duplex - Uniboot	All Sub-Regions
UFXLULU62-MXFxxx	OM4	LSZH/Riser	ULL - 2.0mm - Duplex - Uniboot	All Sub-Regions - Excluding Brazil
UFVLULU62-NXFxxx	OM5	LSZH/Riser	ULL - 2.0mm - Duplex - Uniboot	All Sub-Regions - Excluding Brazil
UFGLULU62-JXFxxx	OS2	LSZH/Riser	ULL - 2.0mm - Duplex - Uniboot	All Sub-Regions - Excluding Brazil
UDXLULU62-MXFxxx	OM4	Plenum	ULL - 2.0mm - Duplex - Uniboot	All Sub-Regions - Excluding Brazil
UDVLULU62-NXFxxx	OM5	Plenum	ULL - 2.0mm - Duplex - Uniboot	All Sub-Regions - Excluding Brazil
UDGLULU62-JXFxxx	OS2	Plenum	ULL - 2.0mm - Duplex - Uniboot	All Sub-Regions - Excluding Brazil
<b>LC to SC duplex patch cords</b>				
FFXLCS42-MXFxxx	OM4	LSZH/Riser	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FFWLCS42-JXFxxx	OS2	LSZH/Riser	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FDXLCS42-MXFxxx	OM4	Plenum	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FDWLCS42-JXFxxx	OS2	Plenum	LL - 1.6mm - Duplex - Zip	All Sub-Regions
<b>SC to SC duplex patch cords</b>				
FFXS42-MXFxxx	OM4	LSZH/Riser	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FFWS42-JXFxxx	OS2	LSZH/Riser	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FDXS42-MXFxxx	OM4	Plenum	LL - 1.6mm - Duplex - Zip	All Sub-Regions
FDWS42-JXFxxx	OS2	Plenum	LL - 1.6mm - Duplex - Zip	All Sub-Regions

### Fiber optic pigtails



Material ID	Fiber Type	Jacket	Performance - Cable OD	Availability
<b>Fiber optic pigtails</b>				
FAXLCUC0C-XXFxxx	OM4	Plenum	LL - Tight - LC	All Sub-Regions
FAVLCUC0C-XXFxxx	OM5	Plenum	LL - Tight - LC	All Sub-Regions
FAWLCUC0C-XXFxxx	OS2	Plenum	LL - Tight - LC	All Sub-Regions
FAWLAUC0C-XXFxxx	OS2	Plenum	LL - Tight - LC APC	All Sub-Regions
FBXLCUC11-MXFxxx	OM4	Riser/LSZH	LL - Semi-Tight - LC	All Sub-Regions - Excluding Brazil
FBVLCUC11-NXFxxx	OM5	Riser/LSZH	LL - Semi-Tight - LC	All Sub-Regions - Excluding Brazil
FBWLCUC11-JXFxxx	OS2	Riser/LSZH	LL - Semi-Tight - LC	All Sub-Regions - Excluding Brazil
FBWLAUC11-JXFxxx	OS2	Riser/LSZH	LL - Semi-Tight - LC APC	All Sub-Regions - Excluding Brazil
FAXSCUC0C-XXFxxx	OM4	Plenum	LL - Tight - SC / Kit	All Sub-Regions
FAWSCUC0C-XXFxxx	OS2	Plenum	LL - Tight - SC / Kit	All Sub-Regions
FAWSAUC0C-XXFxxx	OS2	Plenum	LL - Tight - SC APC / Kit	All Sub-Regions
FBXSCUC11-MXFxxx	OM4	Riser/LSZH	LL - Semi-Tight - SC	All Sub-Regions - Excluding Brazil
FBWSCUC11-JXFxxx	OS2	Riser/LSZH	LL - Semi-Tight - SC	All Sub-Regions - Excluding Brazil
FBWSAUC11-JXFxxx	OS2	Riser/LSZH	LL - Semi-Tight - SC APC	All Sub-Regions - Excluding Brazil

### Qwik II fiber optic connectors

The CommScope QWIK II connector is a mechanical splice connector that is easy to use and reliable, and can be terminated in less than one minute and re-terminated up to three times.

Eliminating the need for specialized tools and power, Qwik II connectors can be used virtually anywhere. They are available in LC, SC and ST.



Material ID	Product Number	Connector	Fiber	Cable	Housing color	Package
<b>Qwik II connector kits</b>						
760117887	MFC-LCF-09-5X	LC	OM3/4/5	0.25/0.9 mm	Aqua	Single
760242343	MFC-LCF-UNV-5X*	LC	OM3/4/5	0.25/0.9/2.0/3.0 mm	Aqua	Single
760117903	MFC-LCF-09-6X	LC	OM1	0.25/0.9 mm	Beige	Single
760117895	SFC-LCF-09-8X	LC-UPC	OS2	0.25/0.9 mm	Blue	Single
760242344	SFC-LCF-UNV-8X*	LC-UPC	OS2	0.25/0.9/2.0/3.0 mm	Blue	Single
760242345	SFC-LCAF-UNV-8X*	LC-APC	OS2	0.25/0.9/2.0/3.0 mm	Green	Single
760184697	SFC-LCF-09-8A-25-PACK	LC-APC	OS2	0.25/0.9 mm	Green	25/pack
760117945	MFC-SCF-09-5X	SC	OM3/4/5	0.25/0.9 mm	Aqua	Single
760242346	MFC-SCF-UNV-5X*	SC	OM3/4/5	0.25/0.9/2.0/3.0 mm	Aqua	Single
760117960	MFC-SCF-09-6X	SC	OM1	0.25/0.9 mm	Beige	Single
760117952	SFC-SCF-09-8X	SC-UPC	OS2	0.25/0.9 mm	Blue	Single
760242347	SFC-SCF-UNV-8X*	SC-UPC	OS2	0.25/0.9/2.0/3.0 mm	Blue	Single
760242348	SFC-SCAF-UNV-8X*	SC-APC	OS2	0.25/0.9/2.0/3.0 mm	Green	Single
760184689	SFC-SCF-09-8A-25-PACK	SC-APC	OS2	0.25/0.9 mm	Green	25/pack
760253591	MFC-STF-UNV-5X	ST	OM3/4/5	0.25/0.9 mm	Aqua	Single
760253592	SFC-STF-UNV-8X	ST-UPC	OS2	0.25/0.9 mm	Blue	Single
760253593	MFC-STF-UNV-6X	ST	OM1	0.25/0.9 mm	Beige	Single

## Qwik II connector tool kits

QWIK II connector tool kits consist of all tools and accessories required to ensure fast, consistent and optimal termination. The premium tool kit includes a high-precision cleaver with auto-rotation blade and a handheld visual fault identifier (VFI) for the confirmation of proper termination.

## Qwik II connector tool kit components

Component	Qwik II termination kit (760242377)	Qwik II termination kit, premium (760248225)
Case	√	√
0.9 mm cable clamp	√	√
2.0 mm cable clamp		√
3.0 mm cable clamp		√
Visual fault identifier (VFI)		√
High-precision fiber cleaver		√
Precision fiber cleaver	√	
Fiber stripper, 3-hole	√	√
Cutter, Kevlar	√	√
Marker, Sharpie	√	√
Fiber prep fluid	√	√
Fiber wipes	√	√
Termination instruction	√	√



Material ID	Description
<b>Qwik II connector tool kits and accessories</b>	
760242377	Qwik II connector termination tool kit
760248225	Qwik II connector termination tool kit, premium
760243353	Replacement blade for high-precision cleaver
760243354	VFI 1.25 mm adapter
760243355	VFI 2.5 mm adapter
760243349	Fiber clamp, buffer tube, 900 µm
760243350	Fiber clamp, 2.0 mm
760243351	Fiber clamp, 3.0 mm
760243081	Qwik II LC duplex clip, 6 per pack



### Qwik-Fuse fiber optic connectors

The CommScope Qwik-Fuse connectors are field installable, splice-on, fiber optic connectors, uniquely designed to provide easy-to-use fusion splicing connectivity. Qwik-Fuse connectors enable fast, low-loss and reliable fusion splicing connectivity in the field without concerns about shorts, excess slacks and the need of a splice tray. They provide flexibility for repair and restoration with minimum downtime. Available in LC and SC, Qwik-Fuse connectors are compatible with industry-leading fusion splicers in the market.

Material ID	Product Number	Connector	Fiber	Cable	Housing color	Package
<b>Qwik-Fuse connector kits</b>						
760242874	MFC-LCF-09-5Y-12-PACK	LC	OM3/4/5	0.25/0.9 mm	Aqua	12/pack
760243371	MFC-LCF-20-5Y-12-PACK	LC	OM3/4/5	1.6/2.0 mm	Aqua	12/pack
760243372	SFC-LCF-09-8Y-12-PACK	LC-UPC	OS2	0.25/0.9 mm	Blue	12/pack
760243388	SFC-LCF-20-8Y-12-PACK	LC-UPC	OS2	1.6/2.0 mm	Blue	12/pack
760243389	SFC-LCAF-09-8Y-12-PACK	LC-APC	OS2	0.25/0.9 mm	Green	12/pack
760243390	SFC-LCAF-20-8Y-12-PACK	LC-APC	OS2	1.6/2.0 mm	Green	12/pack
760243391	MFC-SCF-09-5Y-12-PACK	SC	OM3/4/5	0.25/0.9 mm	Aqua	12/pack
760243392	MFC-SCF-20-5Y-12-PACK	SC	OM3/4/5	1.6/2.0 mm	Aqua	12/pack
760243393	MFC-SCF-30-5Y-12-PACK	SC	OM3/4/5	3.0 mm	Aqua	12/pack
760243394	SFC-SCF-09-8Y-12-PACK	SC-UPC	OS2	0.25/0.9 mm	Blue	12/pack
760243395	SFC-SCF-20-8Y-12-PACK	SC-UPC	OS2	1.6/2.0 mm	Blue	12/pack
760243396	SFC-SCF-30-8Y-12-PACK	SC-UPC	OS2	3.0 mm	Blue	12/pack
760243397	SFC-SCAF-09-8Y-12-PACK	SC-APC	OS2	0.25/0.9 mm	Green	12/pack
760243398	SFC-SCAF-20-8Y-12-PACK	SC-APC	OS2	1.6/2.0 mm	Green	12/pack
760243399	SFC-SCAF-30-8Y-12-PACK	SC-APC	OS2	3.0 mm	Green	12/pack

## Qwik-Fuse connector tool kits

CommScope Qwik-Fuse connector tool kits are designed to facilitate fast and reliable connector terminations. The Qwik-Fuse Termination Tool Kit includes all necessary tools and supplies for cable preparation and termination—providing great convenience to installers and contractors. In addition to all components in the tool kit, the Qwik-Fuse Installer Tool Kit includes a purpose-built splicer (Installer Connector Fusion Splicer Tool) and fiber holders, which significantly simplify and speed up the splice-on termination process. Fiber holders to terminate Qwik-Fuse connectors using other industry-leading splicers are also available from CommScope.



## Qwik-Fuse single fiber connector tool kits


Component	Qwik-Fuse Termination Kit (760243402)	Qwik-Fuse Installer Kit (760243403)
Case	√	√
Qwik-Fuse Installer		√
Installer power supply		√
Installer spare electrodes		√
Fiber holder, tight buffer		√
Fiber holder, loose buffer		√
Cord prep tool	√	√
High-precision cleaver	√	√
Fiber stripper, 3-hole	√	√
Cutter, Kevlar	√	√
Marker, Sharpie	√	√
Fiber prep fluid	√	√
Fiber wipes	√	√
Termination instruction	√	√



Material ID	Description
<b>Qwik-Fuse connector tool kits and accessories</b>	
760243402	Qwik-Fuse Termination Tool Kit, LC, SC (for splice-on connector termination)
760243403	Qwik-Fuse Installer Tool Kit, LC, SC, with Qwik-Fuse Installer Connector Fusion Splicer and termination tools
760244684	Qwik-Fuse cord tool, 1.6, 2.0, 3.0 mm
760243576	Qwik-Fuse Installer Connector Fusion Splicer
760243617	Qwik-Fuse fiber holder, tight buffer and cordage (for use with Qwik-Fuse Installer Connector Fusion Splicer and many AFL and Sumitomo splicers)
760244521	Qwik-Fuse fiber holder, loose buffer and 250µm fiber (for use with Qwik-Fuse Installer Connector Fusion Splicer and many AFL and Sumitomo splicers)
760244706	Qwik-Fuse fiber holder, Fitel, set
760245135	Qwik-Fuse connector duplex clip, LC, 10 per pack
760245136	Qwik-Fuse connector duplex clip, SC, 10 per pack
760245969	Qwik-Fuse Metal Ferrule Holder

## Qwik-Fuse MPO connectors


The CommScope QWIK-Fuse MPO connector utilizes mass-fusionsplicing connectivity to facilitate rapid repairs, restorations, and upgrades to multi-fiber cable assemblies. They offer a reliable alternative when factory-terminated MPO solutions cannot be used, such as when high-fiber count cables are being fed through tight conduits or when slack storage of the multi-fiber breakout cannot be accommodated. The ferrule holder that is required for terminations is included with the QWIK-Fuse MPO termination kit and is also available separately.



## Qwik-Fuse field installable MPO connectors

Material ID	Description	Connector	Fiber	Cable	Housing color	Performance	Package
760251300	MFC-12MX-5SP-30-AQ	MPO-PC Pinned	OM3/4/5	12f round, 3.0 mm	Aqua	Standard Loss	Single
760251299	MFC-12MP-5SP-30-AQ	MPO-PC Unpinned	OM3/4/5	12f round, 3.0 mm	Aqua	Standard Loss	Single
760251294	MFC-12MX-5SP-RN-AQ	MPO-PC Pinned	OM3/4/5	12 f ribbon, no jacket	Aqua	Standard Loss	Single
760251293	MFC-12MP-5SP-RN-AQ	MPO-PC Unpinned	OM3/4/5	12 f ribbon, no jacket	Aqua	Standard Loss	Single
760251292	MFC-12MX-5SP-RC-AQ	MPO-PC Pinned	OM3/4/5	12 f ribbon, with jacket	Aqua	Standard Loss	Single
760251291	MFC-12MP-5SP-RC-AQ	MPO-PC Unpinned	OM3/4/5	12 f ribbon, with jacket	Aqua	Standard Loss	Single
760248909	MFC-8MX-5SP-30-AQ	MPO-PC Pinned	OM3/4/5	8f round, 3.0 mm	Aqua	Standard Loss	Single
760248910	MFC-8MP-5SP-30-AQ	MPO-PC Unpinned	OM3/4/5	8f round, 3.0 mm	Aqua	Standard Loss	Single
760248915	MFC-8MX-5SP-RN-AQ	MPO-PC Pinned	OM3/4/5	8f ribbon, no jacket	Aqua	Standard Loss	Single
760248916	MFC-8MP-5SP-RN-AQ	MPO-PC Unpinned	OM3/4/5	8f ribbon, no jacket	Aqua	Standard Loss	Single
760248917	MFC-8MX-5SP-RC-AQ	MPO-PC Pinned	OM3/4/5	8f ribbon, with jacket	Aqua	Standard Loss	Single
760248918	MFC-8MP-5SP-RC-AQ	MPO-PC Unpinned	OM3/4/5	8f ribbon, with jacket	Aqua	Standard Loss	Single
760251302	SFC-12MX-8SP-30-GR	MPO-APC Pinned	OS2	12f round, 3.0 mm	Green	Standard Loss	Single
760251301	SFC-12MP-8SP-30-GR	MPO-APC Unpinned	OS2	12f round, 3.0 mm	Green	Standard Loss	Single
760251298	SFC-12MX-8SP-RN-GR	MPO-APC Pinned	OS2	12f round, no jacket	Green	Standard Loss	Single
760251297	SFC-12MP-8SP-RN-GR	MPO-APC Unpinned	OS2	12f round, no jacket	Green	Standard Loss	Single
760251296	SFC-12MX-8SP-RC-GR	MPO-APC Pinned	OS2	12f round, with jacket	Green	Standard Loss	Single
760251295	SFC-12MP-8SP-RC-GR	MPO-APC Unpinned	OS2	12f round, with jacket	Green	Standard Loss	Single
760249953	SFC-12MP-8LL-30-YL	MPO-PC Unpinned	OS2	12f round, 3.0 mm	Yellow	Low Loss	Single
760249954	SFC-12MP-8LL-RN-YL	MPO-PC Unpinned	OS2	12 f ribbon, no jacket	Yellow	Low Loss	Single
760249955	SFC-12MP-8LL-RC-YL	MPO-PC Unpinned	OS2	12f round, with jacket	Yellow	Low Loss	Single
760249956	SFC-12MX-8LL-30-YL	MPO-PC Pinned	OS2	12f round, 3.0 mm	Yellow	Low Loss	Single
760249957	SFC-12MX-8LL-RN-YL	MPO-PC Pinned	OS2	12 f ribbon, no jacket	Yellow	Low Loss	Single
760249958	SFC-12MX-8LL-RC-YL	MPO-PC Pinned	OS2	12f round, with jacket	Yellow	Low Loss	Single

Material ID	Description
<b>Qwik-Fuse MPO tool kits and accessories</b>	
760188698	Qwik MPO connector termination tool kit (Includes: Assembly platform, ferrule holder, jacket stripper/splitting tool, ribbonizing tool, ribbonizing glue, magnifier, marker, instructions, and soft case)



The FiberGuide® fiber management systems offers the greatest breadth of optical raceway products in the industry. It is designed to protect and route fiber optic patch cords, multi-fiber cable assemblies and intrafacility fiber cable (IFC) to and from fiber splice enclosures, fiber distribution frames and fiber optic terminal devices.

Tool-less, Snap-Fit™ junctions significantly reduce the amount of time required for installation. Fiberguide is available in a variety of sizes and basic components include horizontal and vertical straight sections, horizontal and vertical elbows, downspouts, junctions and numerous support hardware and flex-vertical kits.

Available in a variety of sizes: 50x50, 50x150, 100x100, 100x150, 100x300, and 100x600. Below is a selection of our 100x150, 100x300 and 100x600 systems. For more sizes and options, [please download the full catalog](#).

## STRAIGHT SECTIONS & FITTINGS

DESCRIPTION	100x150mm	100x300mm	100x600mm
Straight Section Horizontal - L= 1,83 mtr	FGS-MSHS-B	FGS-MSHS-F	FGS-MSHS-H
Straight Section Cover	FGS-MSNC-B/G	FGS-MSNC-F	FGS-FSFC-H
Horizontal Cross	FGS-MHXP-B	FGS-MHXP-F	FGS-MHXP-H
Horizontal Cross Cover	FGS-SHXP-B	FGS-SHXP-F	FGS-FHXP-H
T-Adapter - Horizontal	FGS-MHRT-B	FGS-MHRT-F	FGS-MHRT-H
90° Elbow - Horizontal	FGS-MH9E-B	FGS-MH9E-F	
90° Elbow Vertical - Up With Cover	FGS-MU9E-B		
90° Elbow Vertical - Down	FGS-MD9E-B	FGS-MD9E-F	
45° Elbow - Horizontal	FGS-MH4E-B	FGS-MH4E-F	FGS-MH4E-H
45° Elbow Vertical - Up With Cover	FGS-MU4E-B	FGS-MU4E-F	FGS-MU4E-H
45° Elbow Vertical - Down	FGS-MD4E-B	FGS-MD4E-F	FGS-MD4E-H
Trumpet Flare	FGS-MTRM-B	FGS-MTRM-F	FGS-MTRM-H
End Cap	FGS-HMEC-B	FGS-HMEC-F	FGS-HMEC-H

## JUNCTIONS

DESCRIPTION	100x150mm	100x300mm	100x600mm
Junctions/Joiners	FGS-MFAW-B	FGS-MFAW-F	FGS-MFAW-H

## FIXED DOWNSPOUTS

DESCRIPTION	100x150mm	100x300mm	100x600mm
Downspout kit	FGS-MDSP-B	FGS-MDSP-F	
Cover	FGS-MCDS-AB	FGS-SDSP-F	



## EXPRESS EXIT DOWNSPOUTS

DESCRIPTION	100x150mm	100x300mm	100x600mm
50mm Express Exit™	FGS-MEXP-A/B/F	FGS-MEXP-A/B/F	FGS-MEXP-A/B/F
50mm Low-profile Express Exit™	FGS-MEXP-LP-A/B/F	FGS-MEXP-LP-A/B/F	FGS-MEXP-LP-A/B/F
100mm Express Exit™	FGS-MEXP-E-A/B/F	FGS-MEXP-E-A/B/F	FGS-MEXP-E-A/B/F
Express Exit Rear Hinged Cover for 100x300 Raceway, Yellow		FGS-MEXC-E-F	
300mm Express Exit™, No Cover		FGS-MEXP-F-F/H-NC	FGS-MEXP-F-F/H-NC

## DOWNSPOUT ACCESSORIES

DESCRIPTION	100x150mm	100x300mm	100x600mm
Single 50mm Flex Tube Attachment, 50x50mm	FGS-MEX1-C-0F	FGS-MEX1-C-0F	FGS-MEX1-C-0F
Single 50mm Flex Tube Attachment, 100x100mm	FGS-KT03-A1NH	FGS-KT03-A1NH	FGS-KT03-A1NH
Dual 50mm Flex Tube Attachment, 100x100mm	FGS-KT03-ANH	FGS-KT03-ANH	FGS-KT03-ANH
Dual 50mm Flex Tube Attachment, 100x150mm	FGS-KT03-B-0F	FGS-KT03-B-0F	FGS-KT03-B-0F
50mm Flex Tube, Slotted (x= length in feet 5, 10, 15, 20, 25, 30, 35, 40, 45, 50....)	FGS-MIDY-xF	FGS-MIDY-xF	FGS-MIDY-xF
FlexVertical Kit, 50x50mm, 1219mm length	FGS-FLEXV-4F-C	FGS-FLEXV-4F-C	FGS-FLEXV-4F-C
FlexVertical Kit, 50x50mm, 2133mm length	FGS-FLEXVAD-7F-C	FGS-FLEXVAD-7F-C	FGS-FLEXVAD-7F-C
FlexVertical Dual Kit, 100x100mm to Dual 50x50mm, 1219mm length	FGS-FLEXV-4F-A2C	FGS-FLEXV-4F-A2C	FGS-FLEXV-4F-A2C

## BRACKETS FOR THREADED RODS

DESCRIPTION	100x150mm	100x300mm	100x600mm
New Threaded Rod Bracket 12mm	FGS-HNTR-12MM	FGS-HNTR-F-12MM	
New Threaded Rod Bracket 16mm		FGS-HNTP-F-16MM	FGS-HNTP-H-16MM
Trapeze Support Bracket 12mm		FGS-HNTP-F-12MM	
C- Bracket Threaded Rod 12mm	FGS-HNTS-12MM	FGS-HNTS-F-12MM	FGS-HNTS-H-12MM-A
C- Bracket Threaded Rod 16mm	FGS-HNTS-16MM	FGS-HNTS-F-16MM	

## TOOLS

DESCRIPTION	100x150mm	100x300mm	100x600mm
Mitre Box with Saw for 50, 100, 150 & 300mm Straight Section	FGS-MKIT-ABF	FGS-MKIT-ABF	FGS-MKIT-H

# Powered Fiber Cable



## Powered Fiber Cable

Material ID	Product Number	Description	Availability
PFC-302L12	PFC-302L12	PFC,OM3,2F,I/O,12AWG,METER/D	All Sub-Regions
PFC-302L12F	PFC-302L12F	PFC,OM3,2F,I/O,12AWG,FEET/D	All Sub-Regions
PFC-302L16	PFC-302L16	PFC,OM3,2F,I/O,16AWG,METER/D	All Sub-Regions
PFC-302L16F	PFC-302L16F	PFC,OM3,2F,I/O,16AWG,FEET/D	All Sub-Regions
PFC-302O12	PFC-302O12	PFC,OM3,2F,OUTDOOR,12AWG,METER	All Sub-Regions
PFC-302O12F	PFC-302O12F	PFC,OM3,2F,OUTDOOR,12AWG,FEET	All Sub-Regions
PFC-302O16	PFC-302O16	PFC,OM3,2F,OUTDOOR,16AWG,METER	All Sub-Regions
PFC-302O16F	PFC-302O16F	PFC,OM3,2F,OUTDOOR,16AWG,FEET	All Sub-Regions
PFC-304L12	PFC-304L12	PFC,OM3,4F,I/O,12AWG,METER/D	All Sub-Regions
PFC-304L12F	PFC-304L12F	PFC,OM3,4F,I/O,12AWG,FEET/D	All Sub-Regions
PFC-304L16	PFC-304L16	PFC,OM3,4F,I/O,16AWG,METER/D	All Sub-Regions
PFC-304L16F	PFC-304L16F	PFC,OM3,4F,I/O,16AWG,FEET/D	All Sub-Regions
PFC-304O12	PFC-304O12	PFC,OM3,4F,OUTDOOR,12AWG,METER	All Sub-Regions
PFC-304O12F	PFC-304O12F	PFC,OM3,4F,OUTDOOR,12AWG,FEET	All Sub-Regions
PFC-304O16	PFC-304O16	PFC,OM3,4F,OUTDOOR,16AWG,METER	All Sub-Regions
PFC-304O16F	PFC-304O16F	PFC,OM3,4F,OUTDOOR,16AWG,FEET	All Sub-Regions
PFC-S02L12	PFC-S02L12	PFC,SINGLEMODE,2F,I/O,12AWG,METER/D	All Sub-Regions
PFC-S02L12F	PFC-S02L12F	PFC,SINGLEMODE,2F,I/O,12AWG,FEET/D	All Sub-Regions
PFC-S02L16	PFC-S02L16	PFC,SINGLEMODE,2F,I/O,16AWG,METER/D	All Sub-Regions
PFC-S02L16F	PFC-S02L16F	PFC,SINGLEMODE,2F,I/O,16AWG,FEET/D	All Sub-Regions
PFC-S02O12	PFC-S02O12	PFC,SINGLEMODE,2F,OUTDOOR,12AWG,METER	All Sub-Regions
PFC-S02O12F	PFC-S02O12F	PFC,SINGLEMODE,2F,OUTDOOR,12AWG,FEET	All Sub-Regions
PFC-S02O16	PFC-S02O16	PFC,SINGLEMODE,2F,OUTDOOR,16AWG,METER	All Sub-Regions
PFC-S02O16F	PFC-S02O16F	PFC,SINGLEMODE,2F,OUTDOOR,16AWG,FEET	All Sub-Regions
PFC-S04L12	PFC-S04L12	PFC,SINGLEMODE,4F,I/O,12AWG,METER/D	All Sub-Regions
PFC-S04L12F	PFC-S04L12F	PFC,SINGLEMODE,4F,I/O,12AWG,FEET/D	All Sub-Regions
PFC-S04L16	PFC-S04L16	PFC,SINGLEMODE,4F,I/O,16AWG,METER/D	All Sub-Regions
PFC-S04L16F	PFC-S04L16F	PFC,SINGLEMODE,4F,I/O,16AWG,FEET/D	All Sub-Regions
PFC-S04O12	PFC-S04O12	PFC,SINGLEMODE,4F,OUTDOOR,12AWG,METER	All Sub-Regions
PFC-S04O12F	PFC-S04O12F	PFC,SINGLEMODE,4F,OUTDOOR,12AWG,FEET	All Sub-Regions
PFC-S04O16	PFC-S04O16	PFC,SINGLEMODE,4F,OUTDOOR,16AWG,METER	All Sub-Regions
PFC-S04O16F	PFC-S04O16F	PFC,SINGLEMODE,4F,OUTDOOR,16AWG,FEET	All Sub-Regions
PFC-S12L12	PFC-S12L12	PFC,SINGLEMODE,12F,I/O,12AWG,METER/D	All Sub-Regions
PFC-S12L12F	PFC-S12L12F	PFC,SINGLEMODE,12F,I/O,12AWG,FEET/D	All Sub-Regions
PFC-S12L16	PFC-S12L16	PFC,SINGLEMODE,12F,I/O,16AWG,METER/D	All Sub-Regions
PFC-S12L16F	PFC-S12L16F	PFC,SINGLEMODE,12F,I/O,16AWG,FEET/D	All Sub-Regions
PFC-S12O12	PFC-S12O12	PFC,SINGLEMODE,12F,OUTDOOR,12AWG,METER	All Sub-Regions
PFC-S12O12F	PFC-S12O12F	PFC,SINGLEMODE,12F,OUTDOOR,12AWG,FEET	All Sub-Regions
PFC-S12O16	PFC-S12O16	PFC,SINGLEMODE,12F,OUTDOOR,16AWG,METER	All Sub-Regions
PFC-S12O16F	PFC-S12O16F	PFC,SINGLEMODE,12F,OUTDOOR,16AWG,FEET	All Sub-Regions

# Powered Fiber Cable



## Plenum Round Powered Fiber Cable

Material ID	Product Number	Description	Availability
<b>12 AWG</b>			
760250282	P-002-DS-HY-8W-F29YL/2X12AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 12 AWG, Singlemode	All Sub-Regions
760250283	P-002-DS-HY-5L-F29AQ/2X12AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 12 AWG, OM3 Bend Insensitive	All Sub-Regions
760250284	P-002-DS-HY-5K-F29AQ/2X12AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 12 AWG, OM4 Bend Insensitive	All Sub-Regions
760250285	P-004-DS-HY-8W-F29YL/2X12AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 12 AWG, Singlemode	All Sub-Regions
760250286	P-004-DS-HY-5L-F29AQ/2X12AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 12 AWG, OM3 Bend Insensitive	All Sub-Regions
760250287	P-004-DS-HY-5K-F29AQ/2X12AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 12 AWG, OM4 Bend Insensitive	All Sub-Regions
760250288	P-002-DS-HY-8W-F29YL/4X12AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 12 AWG, Singlemode	All Sub-Regions
760250289	P-002-DS-HY-5L-F29AQ/4X12AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 12 AWG, OM3 Bend Insensitive	All Sub-Regions
760250290	P-002-DS-HY-5K-F29AQ/4X12AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 12 AWG, OM4 Bend Insensitive	All Sub-Regions
760250291	P-004-DS-HY-8W-F29YL/4X12AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 12 AWG, Singlemode	All Sub-Regions
760250292	P-004-DS-HY-5L-F29AQ/4X12AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 12 AWG, OM3 Bend Insensitive	All Sub-Regions
760250293	P-004-DS-HY-5K-F29AQ/4X12AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 12 AWG, OM4 Bend Insensitive	All Sub-Regions
<b>16 AWG</b>			
760250294	P-002-DS-HY-8W-F18YL/2X16AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 16 AWG, Singlemode	All Sub-Regions
760250295	P-002-DS-HY-5L-F18AQ/2X16AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 16 AWG, OM3 Bend Insensitive	All Sub-Regions
760250296	P-002-DS-HY-5K-F18AQ/2X16AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 16 AWG, OM4 Bend Insensitive	All Sub-Regions
760250297	P-004-DS-HY-8W-F18YL/2X16AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 16 AWG, Singlemode	All Sub-Regions
760250298	P-004-DS-HY-5L-F18AQ/2X16AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 16 AWG, OM3 Bend Insensitive	All Sub-Regions
760250299	P-004-DS-HY-5K-F18AQ/2X16AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 20 AWG, OM4 Bend Insensitive	All Sub-Regions
760250300	P-002-DS-HY-8W-F18YL/4X16AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 16 AWG, Singlemode	All Sub-Regions
760250301	P-002-DS-HY-5L-F18AQ/4X16AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 16 AWG, OM3 Bend Insensitive	All Sub-Regions
760250302	P-002-DS-HY-5K-F18AQ/4X16AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 16 AWG, OM4 Bend Insensitive	All Sub-Regions
760250303	P-004-DS-HY-8W-F18YL/4X16AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 16 AWG, Singlemode	All Sub-Regions
760250304	P-004-DS-HY-5L-F18AQ/4X16AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 16 AWG, OM3 Bend Insensitive	All Sub-Regions
760250305	P-004-DS-HY-5K-F18AQ/4X16AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 16 AWG, OM4 Bend Insensitive	All Sub-Regions
<b>20 AWG</b>			
760250306	P-002-DS-HY-8W-F16YL/2X20AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 20 AWG, Singlemode	All Sub-Regions
760250307	P-002-DS-HY-5L-F16AQ/2X20AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 20 AWG, OM3 Bend Insensitive Fiber	All Sub-Regions
760250308	P-002-DS-HY-5K-F16AQ/2X20AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 2 conductor 20 AWG, OM4 Bend Insensitive Fiber	All Sub-Regions
760250309	P-004-DS-HY-8W-F16YL/2X20AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 20 AWG, Singlemode	All Sub-Regions
760250310	P-004-DS-HY-5L-F16AQ/2X20AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 20 AWG, OM3 Bend Insensitive	All Sub-Regions
760250311	P-004-DS-HY-5K-F16AQ/2X20AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 2 conductor 20 AWG, OM4 Bend Insensitive	All Sub-Regions
760250312	P-002-DS-HY-8W-F16YL/4X20AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 20 AWG, Singlemode	All Sub-Regions
760250313	P-002-DS-HY-5L-F16AQ/4X20AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 20 AWG, OM3 Bend Insensitive	All Sub-Regions
760250314	P-002-DS-HY-5K-F16AQ/4X20AWG	Plenum Hybrid Distribution Cable, 2 simplex single fiber, 4 conductor 20 AWG, OM4 Bend Insensitive	All Sub-Regions
760250315	P-004-DS-HY-8W-F16YL/4X20AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 20 AWG, Singlemode	All Sub-Regions
760250316	P-004-DS-HY-5L-F16AQ/4X20AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 20 AWG, OM3 Bend Insensitive	All Sub-Regions
760250317	P-004-DS-HY-5K-F16AQ/4X20AWG	Plenum Hybrid Distribution Cable, 4 simplex single fiber, 4 conductor 20 AWG, OM4 Bend Insensitive	All Sub-Regions

# Powered Fiber Cable

## 1 and 2 Port Extenders

Material ID	Description	Availability
PFU-P-C-O-060-02	60W, 2 Port PoE Extender*	All Sub-Regions
PFU-P-E-O-060-01	60W, 1 Port 5 Gbps PoE Extender	All Sub-Regions

\*The 60W, 2-port PoE Extender provides a maximum of 30W on each port.



## Power Extenders/Fiber Pass-Thru

Material ID	Description	Availability
PFU-48-C-O-060-01	Power Extender, Universal Mount, Outdoor, 48 Vdc, Fiber Pass Through	All Sub-Regions
PFU-12-C-O-060-01	Power Extender, Universal Mount, Outdoor, 12 Vdc, Fiber Pass Through	All Sub-Regions
PFU-P-C-O-060-02	PoE Extender, 2 Port Universal Mount, Outdoor, 2-Port	All Sub-Regions
PFU-P-C-O-060-01	PoE Extender, Universal Mount, Outdoor, 1-Port	All Sub-Regions



## Power Supply

Material ID	Description	Availability
PFU-PX-8M	Power Express Distribution module supports max. 8 Devices	All Sub-Regions - Excluding Argentina
PFU-PX-S1	Power Express Distribution shelf with alarm module	All Sub-Regions - Excluding Argentina
PFU-PX-SF	Power Express Blank Slot Panel	All Sub-Regions - Excluding Argentina
PFU-SPS-1600M	1600W SPS Power Rectifier module	All Sub-Regions - Excluding Argentina
PFU-SPS-C1	SPS Rectifier Controller Display	All Sub-Regions - Excluding Argentina
PFU-SPS-S1	SPS Rectifier Power Distribution Shelf	All Sub-Regions - Excluding Argentina
PFU-SPS-SF	SPS Rectifier Blank Slot Panel	All Sub-Regions - Excluding Argentina




## Surface Mount Boxes

Material ID	Description	Availability
760248944	Kit, SMB, 1 Fiber Port, 1 Power Port, Beige	All Sub-Regions
760248943	Kit, SMB, 1 Fiber Port, 1 Power Port, White	All Sub-Regions
760248942	Kit, SMB, 1 Fiber Port, 1 Power Port, Black	All Sub-Regions
760249095	Kit, SMB, 2 Fiber Ports, 2 Power Ports, Beige	All Sub-Regions
760249094	Kit, SMB, 2 Fiber Ports, 2 Power Ports, White	All Sub-Regions
760249093	Kit, SMB, 2 Fiber Ports, 2 Power Ports, Black	All Sub-Regions



## Plenum Powered Fiber Cable Transition Box

Material ID	Description	Availability
760250853	PFC Transition Box, Plenum rated, cool gray	All Sub-Regions



# Cable Management

## Equipment Racks

Material ID	Product Number	Description	Availability
<b>19" Equipment Racks</b>			
760082479	RK3-45A	Equipment Rack, 2-Post, 3 in (76 mm) Channel x 7 ft (2134 mm) H x 19 in (482.6 mm) Aluminum (45U) 12-24 Tapped Rails, Black	All Subregions
760082487	RK3-52A	Equipment Rack, 2-Post, 3 in (76 mm) Channel x 8 ft (2438 mm) H x 19 in (482.6 mm) Aluminum (52U) 12-24 Tapped Rails, Black	All Subregions
760082495	RK6-45A	Equipment Rack, 2-Post, 6 in (152 mm) Channel x 7 ft (2134 mm) H x 19 in (482.6 mm) Aluminum (45U) 12-24 Tapped Rails, Black	All Subregions
760082503	RK6-52A	Equipment Rack, 2-Post, 6 in (152 mm) Channel x 8 ft (2438 mm) H x 19 in (482.6 mm) Aluminum (52U) 12-24 Tapped Rails, Black	All Subregions
760082511	RK12-45A	Equipment Rack, 2-Post, 12 in (305 mm) Channel x 7ft (2134 mm) H x 19 in (482.6 mm) Aluminum (45U) 12-24 Tapped Rails, Black	All Subregions
760090100	RK12-52A	Equipment Rack, 2-Post, 12 in (305 mm) Channel x 8ft (2438 mm) H x 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black	All Subregions
760090118	RK3-45S	Equipment Rack, 2-Post, 3 in (76 mm) Channel x 7 ft (2134 mm) H x 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black	All Subregions
760090126	RK3-52S	Equipment Rack, 2-Post, 3 in (76 mm) Channel x 8 ft (2438 mm) H x 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black	All Subregions
760090134	RK6-45S	Equipment Rack, 2-Post, 6 in (152 mm) Channel x 7 ft (2134 mm) H x 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black	All Subregions
760090142	RK6-52S	Equipment Rack, 2-Post, 6 in (152 mm) Channel x 8 ft (2438 mm) H x 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black	All Subregions
760090159	RK12-45S	Equipment Rack, 2-Post, 12 in (305 mm) Channel x 7ft (2135 mm) H x 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black	All Subregions
760090167	RK12-52S	Equipment Rack, 2-Post, 12 in (305 mm) Channel x 8ft (2438 mm) H x 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black	All Subregions
760082529	RK4P45-29A	Equipment Rack, 4-Post, 29 in (737 mm) D x 7ft (2134 mm) H x 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black	All Subregions
760082537	RK4P52-29A	Equipment Rack, 4-Post, 29 in (737 mm) D x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black	All Subregions
760082560	RK4P45-36A	Equipment Rack, 4-Post, 36 in (914 mm) D x 7 ft (2134 mm) H x 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black	All Subregions
760082578	RK4P52-36A	Equipment Rack, 4-Post, 36 in (914 mm) D x 8 ft (2438 mm) H x 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black	All Subregions
760175703	RK-4PE-45-29S	Equipment Rack, 4-Post, 29 in (737 mm) D x 7 ft (2134 mm) H x 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black	All Subregions
760175729	RK-4PE-45-36S	Equipment Rack, 4-Post, 36 in (914 mm) D x 7 ft (2134 mm) H x 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black	All Subregions



# Cable Management

## Vertical Cable Managers (VCM)

Material ID	Description	Availability
<b>Vertical Cable Managers</b>		
760244775	DOUBLE SIDED VCM, 84 X 6 INCH	All Subregions
760244776	DOUBLE SIDED VCM, 84 X 8 INCH	All Subregions
760244777	DOUBLE SIDED VCM, 84 X 10 INCH	All Subregions
760244778	DOUBLE SIDED VCM, 84 X 12 INCH	All Subregions
760244779	DOUBLE SIDED VCM, 84 X 6 INCH, BLACK	All Subregions
760244780	DOUBLE SIDED VCM, 84 X 8 INCH, BLACK	All Subregions
760244781	DOUBLE SIDED VCM, 84 X 10 INCH, BLACK	All Subregions
760244782	DOUBLE SIDED VCM, 84 X 12 INCH, BLACK	All Subregions
760244787	SINGLE SIDED VCM, 84 X 6 INCH	All Subregions
760244788	SINGLE SIDED VCM, 84 X 8 INCH	All Subregions
760244789	SINGLE SIDED VCM, 84 X 10 INCH	All Subregions
760244790	SINGLE SIDED VCM, 84 X 12 INCH	All Subregions
760244791	SINGLE SIDED VCM, 84 X 6 INCH, BLACK	All Subregions
760244792	SINGLE SIDED VCM, 84 X 8 INCH, BLACK	All Subregions
760244793	SINGLE SIDED VCM, 84 X 10 INCH, BLACK	All Subregions
760244794	SINGLE SIDED VCM, 84 X 12 INCH, BLACK	All Subregions
760244799	DOUBLE SIDED VCM, 96 X 6 INCH	All Subregions
760244800	DOUBLE SIDED VCM, 96 X 8 INCH	All Subregions
760244801	DOUBLE SIDED VCM, 96 X 10 INCH	All Subregions
760244802	DOUBLE SIDED VCM, 96 X 12 INCH	All Subregions
760244803	DOUBLE SIDED VCM, 96 X 6 INCH, BLACK	All Subregions
760244804	DOUBLE SIDED VCM, 96 X 8 INCH, BLACK	All Subregions
760244805	DOUBLE SIDED VCM, 96 X 10 INCH, BLACK	All Subregions
760244806	DOUBLE SIDED VCM, 96 X 12 INCH, BLACK	All Subregions



# Cable Management

## Vertical Cable Managers (VCM)

Material ID	Description	Availability
<b>Vertical Cable Managers (continued)</b>		
760244811	SINGLE SIDED VCM, 96 X 6 INCH	All Subregions
760244812	SINGLE SIDED VCM, 96 X 8 INCH	All Subregions
760244813	SINGLE SIDED VCM, 96 X 10 INCH	All Subregions
760244814	SINGLE SIDED VCM, 96 X 12 INCH	All Subregions
760244815	SINGLE SIDED VCM, 96 X 6 INCH, BLACK	All Subregions
760244816	SINGLE SIDED VCM, 96 X 8 INCH, BLACK	All Subregions
760244817	SINGLE SIDED VCM, 96 X 10 INCH, BLACK	All Subregions
760244818	SINGLE SIDED VCM, 96 X 12 INCH, BLACK	All Subregions



## Horizontal Cable Manager (HCM)



Material ID	Product Number	Description	Rack Units	Availability
<b>Horizontal Cable Manager</b>				
760072942	HTK-19-SS-1U	19" Single Sided Horizontal Trough Kit, black	1U	All Subregions
760072959	HTK-19-SS-2U	19" Single Sided Horizontal Trough Kit, black	2U	All Subregions
760072967	HTK-19-SS-3U	19" Single Sided Horizontal Trough Kit, black	3U	All Subregions
760128843	HTK-19-DS-1U	19" Double Sided Horizontal Trough Kit, black	1U	All Subregions
760128850	HTK-19-DS-2U	19" Double Sided Horizontal Trough Kit, black	2U	All Subregions
760128868	HTK-19-DS-3U	19" Double Sided Horizontal Trough Kit, black	3U	All Subregions
760172908	HTK-19-SS-1U-SILVER	19" Single Sided Horizontal Trough Kit, silver	1U	All Subregions
760172916	HTK-19-SS-2U-SILVER	19" Single Sided Horizontal Trough Kit, silver	2U	All Subregions
760172924	HTK-19-SS-3U-SILVER	19" Single Sided Horizontal Trough Kit, silver	3U	All Subregions
760038240	HCM-19-SS-1U	19" Patchcord Management	1U	All Subregions
760038257	HCM-19-SS-2U	19" Patchcord Management	2U	All Subregions
760172882	HCM-19-SS-1U-SILVER	19" Patchcord Management, silver	1U	All Subregions
760172890	HCM-19-SS-2U-SILVER	19" Patchcord Management, silver	2U	All Subregions



# Cable Management

## Filler Panels



Material ID	Product Number	Description	Rack Units	Availability
<b>Filler Panels</b>				
760162065	CPP-FPANEL-19-1U	Filler Panel, 1U	1U	All Subregions
760162073	CPP-FPANEL-19-2U	Filler Panel, 2U	2U	All Subregions
760162081	CPP-FPANEL-19-3U	Filler Panel, 3U	3U	All Subregions
760238386	CPPR-FPANEL-19-1U	Filler Panel Recessed Angled, 1U	1U	All Subregions
760238387	CPPR-FPANEL-19-2U	Filler Panel Recessed Angled, 2U	2U	All Subregions
760238388	CPPA-FPANEL-19-1U	Filler Panel Angled, 1U	1U	All Subregions
760238389	CPPA-FPANEL-19-2U	Filler Panel Angled, 2U	2U	All Subregions

CommScope pushes the boundaries of communications technology with game-changing ideas and ground-breaking discoveries that spark profound human achievement.

We collaborate with our customers and partners to design, create and build the world's most advanced networks. It is our passion and commitment to identify the next opportunity and realize a better tomorrow. Discover more at [commscope.com](https://commscope.com)

**COMMSCOPE®**

---

[commscope.com](https://commscope.com)

Visit our website or contact your local CommScope representative for more information.

© 2023 CommScope, Inc. All rights reserved.

All trademarks identified by ™ or © are trademarks or registered trademarks in the US and may be registered in other countries. All product names, trademarks and registered trademarks are property of their respective owners. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services.

CO-112199.8-EN (03/23)