# SSH-M



SnapStak® Plus Adjustable Hanger for 14mm to 25mm Cable - No Grommets Required. For patents, see www.cs-pat.com.

## Product Classification

| | |
|---|---|
| **Product Type** | Hanger kit |
| **Product Brand** | SnapStak® Plus |
| **Ordering Note** | CommScope® non-standard product |

## General Specifications

| | |
|---|---|
| **Accessories** | Hangers |
| **Cables per Hanger** | 1 |
| **Color** | Silver |
| **Hanger Type** | Snap-in hanger |
| **Mounting** | 3/4 in drilled cable ladder |
| **Patent Number** | US 9,866,004 |

## Dimensions

| | |
|---|---|
| **Maximum Stack Height** | 2 |
| **Maximum Stack Height, Coaxial** | 2 |
| **Height** | 67.1 mm \| 2.642 in |
| **Width** | 38.1 mm \| 1.5 in |
| **Length** | 48.5 mm \| 1.909 in |
| **Compatible Cable Diameter Range** | 14–25 mm |
| **Compatible Diameter, maximum** | 25 mm \| 0.984 in |
| **Compatible Diameter, minimum** | 14 mm \| 0.551 in |

## Electrical Specifications

| | |
|---|---|
| **Return Loss Effect, maximum** | 0.1 dB |
| **DTF Effect, maximum** | 0.1 dB |

## Material Specifications



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 27, 2024

# SSH-M

| | |
|---|---|
| **Material Type** | Stainless steel |

## Mechanical Specifications

| | |
|---|---|
| **Vibration Survival** | ≥4 hours at resonant frequency |

## Environmental Specifications

| | |
|---|---|
| **Operating Temperature** | -40 °C to +85 °C (-40 °F to +185 °F) |
| **Corrosion Resistance, minimum with no degredation** | ≥1000 hours in salt spray chamber |
| **Environmental Strength Capability** | Double cable weight |
| **Flammability Test Method** | UL 2043 |

## Packaging and Weights

| | |
|---|---|
| **Height, packed** | 33 cm \| 12.992 in |
| **Width, packed** | 6.4 cm \| 2.52 in |
| **Length, packed** | 26 cm \| 10.236 in |
| **Packaging quantity** | 10 |
| **Weight, gross** | 0.53 kg \| 1.168 lb |

## Regulatory Compliance/Certifications

| Agency | Classification |
|---|---|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

## * Footnotes

| | |
|---|---|
| **Maximum Stack Height** | Fiber, Hybrid, Power |



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 27, 2024