1711825-5

RJ45 Consolidation Point, F/FTP, LZSH, solid, white, 5 m

Product Classification

Regional Availability	Asia | Australia/New Zealand | EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord

General Specifications

ANSI/TIA Category	6A
Cable Type	F/FTP (shielded)
Interface, Connector A	RJ45 plug
Interface, Connector B	RJ45 jack
Jacket Color	White
Pairs, quantity	4

Dimensions

Cord Length	5 m | 16.404 ft
Diameter Over Jacket	5.59 mm | 0.22 in
Compatible Conductor Gauge, solid	23 AWG

Environmental Specifications

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: May 12, 2022

COMMSCOPE®

1711825-5

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: May 12, 2022