MC-PK12M-12-96

Low-Profile Co-location Platform Kit, 12 ft face, 12 in to 50 in OD, includes twelve 96 in pipes

Product Classification

Product Type	Monopole platform kit

General Specifications

Mounting	Monopole, 304.8–1270 mm (12–50 in) OD
Pipe, quantity	12
Sectors, quantity	3

Dimensions

Height	2,438.4 mm | 96 in
Face Width	3.81 m | 12.5 ft
Width	3810 mm | 150 in
Length	1,031.24 mm | 40.6 in
Pipe Length	2,438.4 mm | 96 in
Face Support Pipe Diameter	88.9 mm | 3.5 in
Mounting Diameter, maximum	1270 mm | 50 in
Mounting Diameter, minimum	304.8 mm | 12 in
Pipe Outer Diameter	60.325 mm | 2.375 in

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024

MC-PK12M-12-96

Outline Drawing



Material Specifications

Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Pipe mounts | Plain end pipes (12) | Platform | Ring mount
Packaging quantity	1
Weight, net	700.8 kg | 1545 lb

Regulatory Compliance/Certifications

Agency	Classification

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024

MC-PK12M-12-96

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024