107920704 | 110AB CAT5PSJP 12B



12 Modular Jacks on a 100-Pair Wiring Block, With Mounting Legs

Product Classification

Regional Availability	Asia | Australia/New Zealand | EMEA | Latin America | North America
Portfolio	CommScope®
Product Type	Block

General Specifications

Product Design	110
ANSI/TIA Category	5
Wiring	T568B

Dimensions

Height	91.19 mm | 3.59 in
Width	272.29 mm | 10.72 in
Depth	82.55 mm | 3.25 in
Compatible Conductor Gauge, solid	24 AWG | 26 AWG

Material Specifications

Material Type	Copper alloy

Mechanical Specifications

Plug Insertion Life, minimum	200 times

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	UL | cUL

Packaging and Weights

Packaging quantity	1

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023