

# SSC-760233122E1U | 18 in Pole Top with ant concealment for Ericsson



## Top of Pole 18in Dia Concealment Enclosure for up to six Ericsson 220x/440x/4435 radios

- Enclosure for holding up to 6 Ericsson metro cell radios directly below a multiband canister antenna
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number. Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts. Additional Configurations available utilizing the below kits: -860664823-AMK-001 PTS Load Center Adapter Kit -860664823-AMK-002 (1) 4435 radio, raycap,(3) 220x/440x radios Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Pole top
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, CommScope</b>	CommScope Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   DK   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Light Gray (RAL 7035)   Metallic Silver
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Non-tapered poles   Tapered poles   Wood poles
<b>Radio Compatibility, Ericsson</b>	220x   440x   4435   Diplexer   Power Distribution
<b>Radios Included</b>	None

## Dimensions

<b>Height</b>	1,651 mm   65 in
---------------	------------------

# SSC-760233122E1U | 18 in Pole Top with ant concealment for Ericsson

---

<b>Width</b>	457.2 mm   18 in
<b>Depth</b>	457.2 mm   18 in
<b>Mounting Bolt Circle Diameter</b>	142.748 mm   5.62 in   241.3 mm   9.5 in

## Material Specifications

<b>Finish Aluminum</b>	Chromate
<b>Finish Concealment Covers</b>	Powder coated
<b>Material Type</b>	Aluminum   Steel

## Environmental Specifications

<b>Thermal Compliance</b>	GR-487
---------------------------	--------

## Packaging and Weights

<b>Volume</b>	0.27 m <sup>3</sup>   9.52 ft <sup>3</sup>
<b>Weight (unloaded)</b>	34.019 kg   75 lb

## \* Footnotes

<b>Warranty</b>	For more information, please consult our Product Warranty guidelines
-----------------	--