

SSC-760233122X6 | 18 in Pole Top for C-Band Radios and 4G Antenna



Top of Pole 18in Dia Concealment Enclosure for C-Band and power supply

- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number.

Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

Supports Ericsson C-Band 8863 with 6302 power supply
Coming support of 4415/4426/4478 with additional kit
Supports Samsung RT8808 and Delta 2.0 or ABB power supply

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

Product Classification

Portfolio	CommScope®
Product Type	Pole top
Product Brand	Metro Cell
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, CommScope	CommScope Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022)
Cooling	Passive Cooling
Mounting Options	Concrete poles Fluted poles Metal poles Non-tapered poles Tapered poles Wood poles
Power Supply Compatibility	6302 ABB CC1600 DELTA 2.0 PSU-AC-08
Radio Compatibility, Ericsson	4415 4426 4478 8863

SSC-760233122X6 | 18 in Pole Top for C-Band Radios and 4G Antenna

Radio Compatibility Samsung	RT8808-77A
Radios Included	None
Dimensions	
Height	812.8 mm 32 in
Width	457.2 mm 18 in
Depth	457.2 mm 18 in
Mounting Bolt Circle Diameter	142.748 mm 5.62 in 241.3 mm 9.5 in

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Aluminum Steel

Environmental Specifications

Thermal Compliance	GR-487
---------------------------	--------

Packaging and Weights

Volume	0.134 m ³ 4.72 ft ³
Weight (unloaded)	34.019 kg 75 lb

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
-----------------	--