


# FFXLCLC42

## Base Product



Fiber Patch Cord, LC/UPC/UPC to LC/UPC/UPC, Multimode OM4, 1.6 mm Duplex, Low Smoke Zero Halogen (LSZH)

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin America | Middle East/Africa | North America

### Portfolio

CommScope®

### Product Type

Fiber patch cord, duplex

### Product Brand

SYSTIMAX InstaPATCH® 360

### Product Series

FFX

### Ordering Note

For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration | Replacement for MEA Region: 2105027

## General Specifications

### Color, boot A

Aqua

### Color, connector A

Black

### Color, boot B

Aqua

### Color, connector B

Black

### Interface, Connector A

LC/UPC

### Interface, Connector B

LC/UPC

### Jacket Color

Aqua

### Polarity

Pairs, flipped

### Total Fibers, quantity

2

### Transmission Standards

TIA/EIA-568-C.3

## Dimensions

### Cable Assembly Length Range (m)

1 – 999

### Cable Assembly Length Range (ft)


1 – 999

### Diameter Over Jacket

1.6 mm | 0.063 in

# FFXLCLC42

## Ordering Tree



## Mechanical Specifications

**Cable Retention Strength, maximum** 11.24 lb @ 0 ° | 4.40 lb @ 90 °

## Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM4, LazrSPEED®

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Environmental Space** Dual Rated LSZH/Riser

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# FFXLCLC42

---

## Included Products

- 760021659  
N-002-ZC-5K-F16AQ/E
  - 860655461
- Fiber Indoor Cable, LazrSPEED® 1.6 mm Low Smoke Zero Halogen Riser, 2-fiber Zipcord, Multimode OM4, Feet jacket marking, Aqua jacket color, Eca Flame Rating
  - LC/UPC Connector, Multimode, Aqua