

SYSTIMAX® Ultra-low loss MPO Modules: New Product

Global Communication

CommScope® announces the addition of Ultra-low Loss MPO DM modules to its SYSTIMAX family. SYSTIMAX ULL solutions maximize speed and minimize attenuation. MPO-24 provides highest fiber density and lowest installed cost. MPO-12 supports the legacy system while MPO-8 QSFP provides parallel optic application support. LazrSPEED 550 OM4 and OM5 maximize bandwidth and capacity of the fiber cabling system.

Features and benefits

- G2 ULL DM modules have unpinned rear MPO adapters for MPO-8, MPO-12 or MPO-24
- Shutters automatically actuated by connector insertion, allowing for one-handed operation
- Shutters designed to avoid ferrule contact during connector installation
- Shutter door will illuminate when hit with visual fault locator (VFL)
- New latch assist provides easier module removal for faster moves, adds and changes

Ordering Information:

Please visit eCatalog for product specs <http://www.commscope.com/Product-Catalog/Enterprise/>

SYSTIMAX® G2 ULL DM Modules with Internal Shutters

* Note: Internal shutters are not compatible with iPatch. For iPatch compatible modules, see below.

Part Number	Product Code	Description
760236109	DM08-24LC-WB-ULL	G2 ULL MPO-8 distribution module, 24LC to 3x8f MPOs unpinned, OM5 internal shutters
760236108	DM08-24LC-LS-ULL	G2 ULL MPO-8 distribution module, 24LC to 3x8f MPOs unpinned, OM4 internal shutters
760236111	DM12-24LC-WB-ULL	G2 ULL MPO-12 distribution module, 24LC to 2x12f MPOs unpinned, OM5 internal shutters



Part Number	Product Code	Description
760236110	DM12-24LC-LS-ULL	G2 ULL MPO-12 distribution module, 24LC to 2x12f MPOs unpinned, OM4 internal shutters
760236113	DM24-24LC-WB-ULL	G2 ULL MPO-24 distribution module, 24LC to 1x24f MPO unpinned, OM5 internal shutters
760236112	DM24-24LC-LS-ULL	G2 ULL MPO-24 distribution module, 24LC to 1x24f MPO unpinned, OM4 internal shutters

SYSTIMAX G2 ULL iPatch Ready DM modules

The SYSTIMAX iPatch modules are a component of the imVision® automated infrastructure management (AIM) solution and provide intelligent connectivity.

Part Number	Product Code	Description
760236117	DM08iP-24LC-WB-ULL	G2 ULL MPO-8 distribution module, 24LC to 3x8f MPOs unpinned, OM5 dust caps iPatch
760236116	DM08iP-24LC-LS-ULL	G2 ULL MPO-8 distribution module, 24LC to 3x8f MPOs unpinned, OM4 dust caps iPatch
760236119	DM12iP-24LC-WB-ULL	G2 ULL MPO-12 distribution module, 24LC to 2x12f MPOs unpinned, OM5 dust caps iPatch
760236118	DM12iP-24LC-LS-ULL	G2 ULL MPO-12 distribution module, 24LC to 2x12f MPOs unpinned, OM4 dust caps iPatch
760236121	DM24iP-24LC-WB-ULL	G2 ULL MPO-24 distribution module, 24LC to 1x24f MPO unpinned, OM5 dust caps iPatch
760236120	DM24iP-24LC-LS-ULL	G2 ULL MPO-24 distribution module, 24LC to 1x24f MPO unpinned, OM4 dust caps iPatch

Supporting Documents:

For additional information about Ultra-low loss solutions and the entire High Speed Migration portfolio visit the website at <http://www.commscope.com/Solutions/High-speed-migration-for-enterprise/>

If you need assistance configuring a high-speed migration system contact our [technical assistance center](#)