

QR® 320

Quick Reference Guide

Product Information

COMMSCOPE PRODUCT	AVAILABLE LENGTHS	CABLE WEIGHT (LBS/KFT)	REEL SIZE (INCHES)	SHIPPING WEIGHT	STANDARD PACKAGE
QR 320 JCA	1000ft	47.15	24x12x13	62.15 lbs.	8 Reels
QR 320 JCASS	1000ft	47.15	24x12x13	62.15 lbs.	8 Reels
QR 320 JCAM (.083)*	1000ft	73.0	24x12x13	88.0 lbs.	8 Reels
QR 320 JCAM (.109)*	1000ft	87.75	24x12x13	102.75 lbs.	8 Reels
QR 320 JCA (in 3/4" ConQuest® Conduit)	1000ft	46.0	42x24x24	287.0 lbs.	1 Reel

*Designates the size of the messenger.

Common Tools & Hardware

	MANUFACTURER	PART NUMBER
Center Conductor Cleaner	Ripley	CC-200
	Cable Prep	17670

	MANUFACTURER	PART NUMBER
Cable Cutters	Ripley	CXC
	Klein	63028

	MANUFACTURER	PART NUMBER
Web Slitters	Ripley	MWSS400

	MANUFACTURER	PART NUMBER
Wirevise	Maclean Power Systems	5058
	Maclean Power Systems (0.83)	5056T

Coring Tools

	MANUFACTURER	PART NUMBER
Coring Tool	Ripley	CST320/7QR
	Cable Prep	SCT-F320QR

Finished Trim Dimensions

	CORE DEPTH	CENTER CONDUCTOR STOP LENGTH	JACKET STRIP BACK LENGTH
F-Prep	9/16"	7/16"	3/8"

QR[®] 320

Quick Reference Guide



"F" Fitting Compression Tools

	MANUFACTURER	PART NUMBER
Compression Tool (PPC)	Ripley	CATAS (All Sizes 59, 6, 7, 11,320)
	Ripley	CAT711
	Cable Prep	T-5000CMP-711
	Cable Prep	AT-5000CMP-711
	Cable Prep	PT-5000-711
Compression Tool (Thomas & Betts)	Ripley	CATSNS320/7C QRF
	Ripley	CATAS (All Sizes 59, 6, 7, 11,320)
	Thomas & Betts	L3011B

"F" Fitting Crimp Tools

	MANUFACTURER	PART NUMBER
Hex Crimp Tool (Gilbert)	Ripley	CR41Q (.452" Hex Crimp)
	Cable Prep	ACT-41Q
	Cable Prep	HCT-41Q



1100 CommScope Place SE • P.O. Box 1729
 Hickory, North Carolina 28603 • Tel: 1-866-333-3272 (dBRC)
dbrc@commscope.com • www.commscope.com