

UNMDU-ENCL-14



UNMDU-ENCL-24



UNMDU-ENCL-34

UNMDU-ENCL-28E

## Uniprise® Mixed-Use Network Solutions - Enclosures

CommScope® Uniprise® Mixed-Use Network Solutions are designed as an end-to-end solution specifically for Multi-Dwelling Units (MDU) installations in condominiums, town homes, stick-built homes, and small commercial buildings such as strip malls. The modular and flexible design suits each customer's applications and budget.






Unlike traditional structured wiring systems, Uniprise Mixed-Use Network Solutions provides simultaneous distribution of high-speed data, voice and video signals throughout the home or commercial building. All incoming signals are fed into a media distribution of high-speed data, voice and video signals throughout the home or commercial building. Once the system is installed, all electronic equipment, including cable, satellite, computers, printers and fax machines, can be connected to virtually any outlet in your residential network.

### FEATURES & BENEFITS:

- Enclosures are available in a variety of sizes with a locking hinged door that is reversible for left/right mounting
- Economy Enclosures are a cost effective alternative to the Uniprise Mixed-Use enclosure offering
- Economy Enclosures come with a one piece cover style
- Centralized network environment for voice/data/video/CATV/satellite/security system
- Flexible basic and enhanced network modules allow for easy installation
- Can support Cat 6, Cat 5e, and fiber applications
- All enclosures includes grounding wire, rubber grommets for cable entry ports, mounting hardware, cable ties and a cabling logging system and protective pouch
- Complete control of your home's telephone, video, data CATV, satellite, HDTV, security systems, and more
- Supports EIA/IS-60 CEBus Standard for home automation systems
- Meets TIA/EIA 570-B Residential Wiring Standard

ORDERING INFORMATION

Catalog Number	Descriptions
UNMDU-ENCL-14 (hinged door with lock)	Enclosure, MDU, 14 x 14.375 x 4.625
UNMDU-ENCL-24 (hinged door with lock)	Enclosure, MDU, 24 x 14.375 x 4.625
UNMDU-ENCL-34 (hinged door with lock)	Enclosure, MDU, 34 x 14.375 x 4.625
UNMDU-ENCL-14E (panel cover)	Enclosure, MDU, 14 x 14.375 x 4.17
UNMDU-ENCL-28E (panel cover)	Enclosure, MDU, 28 x 14.375 x 4.17



© 2008 CommScope, Inc. All rights reserved.

Visit our Web site at [www.commscope.com](http://www.commscope.com) or contact your local CommScope representative or BusinessPartner for more information. All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.

This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to Uniprise products or services.