

Verizon NSTD123 Cell Site Infrastructure Solutions: New Product

North America Communication

In accordance with the recently issued Verizon NSTD123 Cell Site Infrastructure Standard, CommScope announces the release of a new family of equipment platforms, ice canopies, and H-frames which are specified for use on all Verizon cell sites by this new standard. Product selection is determined by the number of planned equipment cabinets (1 – 4) and several options are offered for foundation type.

Equipment Platform Options:

- 4' x 6' Platforms specified for 1 Cabinet sites
- 8' x 8' Platforms specified for 2 Cabinet sites
- 8' x 11' Platforms specified for 3 Cabinet sites
- 8' x 14' Platforms specified for 4 Cabinet sites

Platform Foundation Options:


- Helical Anchors ("AR" Options)
- Pier Connections ("PF" Options)
- Adjustable Feet ("DF" Options)

Covered Ice Canopy Options:


- 48" x 48" Canopies specified for 1 Cabinet sites
- 48" x 90" Canopies specified for 2 Cabinet sites
- 48" x 132" Canopies specified for 3 Cabinet sites
- 48" x 174" Canopies specified for 4 Cabinet sites

H-Frame Options:

- 4' H-Frames with 2 Posts
- 8' H-Frames with 3 Posts
- 10' H-Frames with 4 Posts
- All sizes offered with or without Ice Canopy Cover



Platform Base with Helical Anchors



2 Cabinet Ice Canopy

Covered H-Frame

Ordering Information:

Product Type	Description	Part Number
Platforms with Helical Anchors: 7 feet long, 6-inch diameter	1 Cabinet - 4' x 6' Platform with Single Step	MTC3987AR
	2 Cabinet - 8' x 8' Platform with Single Step	MTC3988AR
	3 Cabinet - 8' x 11' Platform with Single Step	MTC4018AR
	4 Cabinet - 8' x 14' Platform with Single Step	MTC3989AR
Platforms with Adjustable Feet	1 Cabinet - 4' x 6' Platform with Single Step	MTC3987DF
	2 Cabinet - 8' x 8' Platform with Single Step	MTC3988DF
	3 Cabinet - 8' x 11' Platform with Single Step	MTC4018DF
	4 Cabinet - 8' x 14' Platform with Single Step	MTC3989DF
Platforms with Pier Connections	1 Cabinet - 4' x 6' Platform with Single Step	MTC3987PF
	2 Cabinet - 8' x 8' Platform with Single Step	MTC3988PF
	3 Cabinet - 8' x 11' Platform with Single Step	MTC4018PF
	4 Cabinet - 8' x 14' Platform with Single Step	MTC3989PF
Ice Canopies	1 Cabinet - 48" x 48" Ice Canopy	MTC401548C
	2 Cabinet - 48" x 90" Ice Canopy	MTC401590C
	3 Cabinet - 48" x 132" Ice Canopy	MTC4015132C
	4 Cabinet - 48" x 174" Ice Canopy	MTC4015174C
H-Frames with Ice Canopy	4' H-Frames with 2 Posts and Ice Canopy	MTC401548HC
	8' H-Frames with 3 Posts and Ice Canopy	MTC401596HC
	10' H-Frames with 4 Posts and Ice Canopy	MTC4015120HC
H-Frames - No Ice Canopy	4' H-Frames with 2 Posts	MTC401548H
	8' H-Frames with 3 Posts	MTC401596H
	10' H-Frames with 4 Posts	MTC4015120H

Supporting Information

Please contact your local CommScope representative or steelproducts@commscope.com for more information.