

# Adjustable Monopole V-Stabilizer™ Kits: New Product

## North American Communication


Announcing the release of new adjustable Monopole V-Stabilizer™ designs which have been added to CommScope’s Universal V-Stabilizer™ family of monopole reinforcement kits. V-Stabilizer kits add extra capacity to existing antenna mounts to enable mounting of additional equipment such as radios or antennas. The new models feature adjustable angled supports that accommodate mounting distances from 32” to 64” and can be used in pairs to provide both vertical and horizontal reinforcement. V-Stabilizers are designed to mount to the pipes of existing mounts ranging from 1.9” to 3.5” OD and can be purchased with or without a ring mount for monopoles ranging from 12” to 50” OD.

**Features:**

- Vertical or Vertical and Horizontal Stabilization
- Ringmount for monopoles from 12” to 50” OD
- Attach to Existing Face Pipes from 1.9” to 3.5” OD

**Specifications:**

- Maximum Additional Dead Load: 1,500 lbs.
- Maximum Additional Front Wind Load: 750 lbs.
- Maximum Additional Side Wind Load: 400 lbs.



**VSRA-MM-B3  
(Pipes not included)**

**Ordering Information:**

Description	Monopole Mounting	Part Number
Monopole V-Stabilizer Kit with Adjustable Angle Supports – Three Sector Kit - Includes Ring mount	12” – 50” OD	<a href="#">VSRA-MM-B3</a>
Monopole V-Stabilizer Kit with Adjustable Angle Supports – Single Sector Kit -No Ring mount	N/A	VSRA-MM-BNR

Related Products – Monopole Reinforcement Kits:

Reinforcement type	Description	Monopole Mounting	Part Number
Vertical	Monopole V-Stabilizer – 3-Sector with 60" Formed Channel Supports	10" – 50" OD	<a href="#">VSR-MS-B</a>
Monopole Kicker Kit	Monopole Kicker Kit – 3-Sector with 36" HD Pipe Kicker	10" – 50" OD	<a href="#">RK-36-3M</a>
	Monopole Kicker Kit – 3-Sector with 60" HD Pipe Kicker	10" – 50" OD	<a href="#">RK-60-3M</a>
Monopole Kicker Kit	Monopole Kicker Kit – 3-Sector with 10' Adjustable HD Pipe Kicker	10" – 30" OD	<a href="#">MTC38523</a>
	Monopole Kicker Kit – 3-Sector with 10' Adjustable HD Pipe Kicker	30" – 60" OD	<a href="#">MTC38523L</a>
Monopole Kicker Kit	Monopole Kicker Kit – 4-Sector with 36" HD Pipe Kicker	10" – 30" OD	<a href="#">RK-36-4S</a>
	Monopole Kicker Kit – 4-Sector with 60" HD Pipe Kicker	10" – 30" OD	<a href="#">RK-60-4S</a>
Monopole Kicker Kit	Monopole Kicker Kit – 4-Sector with 36" HD Pipe Kicker	30" – 60" OD	<a href="#">RK-36-4L</a>
	Monopole Kicker Kit – 4-Sector with 60" HD Pipe Kicker	30" – 60" OD	<a href="#">RK-60-4L</a>

Related Products – Tower Reinforcement Kits:

Reinforcement type	Description	Tower Mounting	Part Number
Vertical	V-Stabilizer Kit with 60" Adjustable Angle Supports	2" – 8" OD	<a href="#">VSRA-TS-B</a>
		8" – 16" OD	<a href="#">VSRAL-TS-B</a>
Dual Vertical & Horizontal	Dual V-Stabilizer Kit with 60" Adjustable Angle Supports	2" – 8" OD	<a href="#">VSRDUALA-TS-B</a>
		8" – 16" OD	<a href="#">VSRDUALAL-TS-B</a>
Vertical	V-Stabilizer Kit – 48" Formed Channel Supports	2" – 8" OD	<a href="#">VSR-TS-B</a>
		8" – 16" OD	<a href="#">VSR-TL-B</a>
Dual Vertical & Horizontal	Dual V-Stabilizer Kit – 60" Pipe Supports	2" – 8" OD	<a href="#">VSRDUAL-TS-B</a>
	Heavy Duty Dual V-Stabilizer Kit– 60" HD Pipe Supports	2" – 8" OD	<a href="#">VSRDUAL-TS-B-HD</a>

Please contact your local CommScope representative or [steelproducts@commscope.com](mailto:steelproducts@commscope.com) for more information.