



G2 Modular Cassette with 12 LC LazrSPEED® 550 Pigtails

OBSOLETE

Replaced By:

760109470  
360G2 Cartridge 12-LC-LS-AQ-PIGTAILS

360G2 Multimode OM4 Fiber Cassette 12 LC, with pigtails, iPatch Ready

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Brand	LazrSPEED®

General Specifications

Adapter Color	Aqua
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	12
Total Ports, quantity, front	12

Dimensions

Height	30.48 mm   1.2 in
Width	91.44 mm   3.6 in
Depth	119.38 mm   4.7 in
Pigtail Length	1.5 m   4.921 ft

Optical Specifications

Fiber Type	OM4, LazrSPEED® 550
Insertion Loss, typical	0.27 dB
Return Loss, minimum	20 dB

## Packaging and Weights

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

700207004 - LazrSPEED® LC Multiport Shuttered Adapter, Aqua, Single Pack  
MFA-LC12-AQ-SHUTTERED

# 700207004 | MFA-LC12-AQ-SHUTTERED



LazrSPEED® LC Multiport Shuttered Adapter, Aqua, Single Pack

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	LazrSPEED®
Product Series	MFA

## General Specifications

Body Style	Ganged
Color	Aqua
Interface	LC/UPC
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	12

## Material Specifications

Alignment Sleeve Material	Zirconia (ceramic)
---------------------------	--------------------

## Optical Specifications

Fiber Mode	Multimode
------------	-----------

## Packaging and Weights

Packaging quantity	1
--------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

