

G2 Modular Cassette with 6 SC OptiSPEED® Multimode Pigtails, Type A

OBSOLETE

Product Classification

| | |
|-----------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | SYSTIMAX® |
| Product Type | Fiber cassette with pigtails |
| Product Brand | OptiSPEED® |

General Specifications

| | |
|------------------------------|------------------|
| Adapter Color | Beige |
| Interface, front | SC/UPC |
| Interface, rear | Stranded pigtail |
| Total Fibers, quantity | 6 |
| Total Ports, quantity, front | 6 |

Dimensions

| | |
|----------------|--------------------|
| Height | 30.48 mm 1.2 in |
| Width | 91.44 mm 3.6 in |
| Depth | 119.38 mm 4.7 in |
| Pigtail Length | 1.5 m 4.921 ft |

Optical Specifications

| | |
|-------------------------|--------|
| Fiber Type | OM1 |
| Insertion Loss, typical | 0.3 dB |
| Return Loss, minimum | 20 dB |

Environmental Specifications

Safety Standard

UL

Packaging and Weights

Packaging quantity


1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

Included Products

| | | |
|-----------------------|---|---|
| 700206956 | – | OptiSPEED® SC Multiport Shuttered Adapter, Beige, Single Pack |
| MFA-SC06-BG-SHUTTERED | | |



OptiSPEED® SC Multiport Shuttered Adapter, Beige, Single Pack

Product Classification

| | |
|-----------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber adapter |
| Product Brand | OptiSPEED® |
| Product Series | MFA |

General Specifications

| | |
|-----------------------|-----------|
| Body Style | Ganged |
| Color | Beige |
| Interface | SC/UPC |
| Mounting | No flange |
| Shuttered | Yes |
| Total Ports, quantity | 6 |

Material Specifications

| | |
|---------------------------|--------------------|
| Alignment Sleeve Material | Zirconia (ceramic) |
|---------------------------|--------------------|

Optical Specifications

| | |
|------------|-----------|
| Fiber Mode | Multimode |
|------------|-----------|

Packaging and Weights

| | |
|--------------------|---|
| Packaging quantity | 1 |
|--------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

| | |
|------------|--|
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

