

# 760066076 | PNL-BK-012-MFA-SC02-AQ



LazrSPEED®, ReadyPATCH® Adapter Pack, Black, 1000-Type, with 6 Multimode duplex SC adapters, aqua

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber adapter pack
<b>Product Brand</b>	LazrSPEED®
<b>Product Series</b>	1000-style

## General Specifications

<b>Application</b>	Used in conjunction with panels and enclosures (rack, wall, and floor mount) that accept 1000 style panels
<b>Adapter Color</b>	Aqua
<b>Adapter Cutout, quantity</b>	12
<b>Adapters, quantity</b>	6
<b>Body Style</b>	Duplex
<b>Interface</b>	SC/UPC
<b>Pigtails Included, quantity</b>	0
<b>Shuttered</b>	No
<b>Total Ports, quantity</b>	6

## Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted

UK-ROHS

Compliant/Exempted



## Included Products

108622895 - LazrSPEED® SC Duplex Adapter, Aqua, Single  
MFA-SC02-AQ Pack

## LazrSPEED® SC Duplex Adapter, Aqua, Single Pack

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber adapter
<b>Product Brand</b>	LazrSPEED®
<b>Product Series</b>	MFA

### General Specifications

<b>Body Style</b>	Duplex
<b>Color</b>	Aqua
<b>Interface</b>	SC/UPC
<b>Mounting</b>	Flange
<b>Shuttered</b>	No
<b>Total Ports, quantity</b>	2
<b>Transmission Standards</b>	TIA/EIA-568-B.3   TIA/EIA-604 FOCIS-3

### Material Specifications

<b>Alignment Sleeve Material</b>	Phosphorous bronze
----------------------------------	--------------------

### Optical Specifications

<b>Fiber Mode</b>	Multimode
-------------------	-----------

### Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

