


760067173 | PNL-BK-012-MFA-LC02-AQ-SHUTTERED



LazrSPEED®, ReadyPATCH® Adapter Pack, Black, 1000-Type, with 6 Multimode duplex LC adapters, aqua, shuttered

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter pack
Product Brand	LazrSPEED®
Product Series	1000-style

General Specifications

Application	Used in conjunction with G2 1U, 2U and 4U adapter panel shelves, surface mount and raised floor enclosures Used in conjunction with panels and enclosures (rack, wall, and floor mount) that accept 1000 style panels
Adapter Color	Aqua
Adapter Cutout, quantity	12
Adapters, quantity	6
Body Style	Duplex
Interface	LC/UPC
Pigtails Included, quantity	0
Shuttered	Yes
Total Ports, quantity	6

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

760067173 | PNL-BK-012-MFA-LC02-AQ- SHUTTERED

ROHS Compliant/Exempted


UK-ROHS Compliant/Exempted



Included Products

760056002 – LazrSPEED® LC Duplex Low Profile Shuttered Adapter, Aqua, Single Pack
MFA-LC02-AQ/LP-SHUTTERED

760056002 | MFA-LC02-AQ/LP-SHUTTERED



LazrSPEED® LC Duplex Low Profile Shuttered Adapter, Aqua, Single Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	LazrSPEED®
Product Series	MFA

General Specifications

Body Style	Duplex
Color	Aqua
Interface	LC/UPC
Interface Feature	Reduced footprint
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	2
Transmission Standards	TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3

Material Specifications

Alignment Sleeve Material	Phosphorous bronze
----------------------------------	--------------------

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

760056002 | MFA-LC02-AQ/LP-SHUTTERED

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

