





# HELIAX® Coaxial Cable, Connectors and Tool Matrix for 4.3-10

HELIAX® Cable	SureFlex Jumpers	4.3-10 Connectors (Field Fit)	4.3-10, 7-16 DIN & N-Type Adaptors	Tools and Port Protection
				
<b>1/4"</b>				
FSJ1-50A	F1A-HMDM-X-P, F1A-HMHM-X-P, F1A-HMHR-X-P Jumpers are available in D-class	F1HM-D F1HR-D	<b>7-16 to 4.3-10 adaptors:</b> TA-DFHM, TA-DMHF, TA-DMHM, TA-DMHM-K  <b>N-Type to 4.3-10 adaptors:</b> TA-NFHF, TA-NFHM, & TA-NMHF	SMALL-CAPKIT SMALL-M-CAPKIT TT-4310* TW-4310
PTS1-50-P	PTS1P-HMHM-X-P PTS1P-HMHR-X-P PTS1P-HMDM-X-P			
LDF1-50		L1HM-D		CPT-F1-D
<b>3/8"</b>				
	LS2-HMHM-X-D <span style="color: red; font-weight: bold;">NEW</span>			TT-4310* TW-4310
FSJ2-50	F2A-HMDM-X-P F2A-HMHM-X-P F2A-HMHR-X-P	F2HM-D	<b>7-16 to 4.3-10 adaptors:</b> TA-DFHM, TA-DMHF, TA-DMHM, TA-DMHM-K  <b>N-Type to 4.3-10 adaptors:</b> TA-NFHF, TA-NFHM, & TA-NMHF	SMALL-CAPKIT CPT-F2-D SMALL-M-CAPKIT TT-4310* TW-4310
PTS2-50-P	PTS2P-HMHM-X-P PTS2P-HMHR-X-P PTS2P-HMDM-X-P	Available		
LDF2-50		L2HM-D		
<b>1/2"</b>				
FSJ4-50B	F4-HMDM-X-SGW-D, F4-HMHM-X-SGW-D, F4-HMHR-X-SGW-D	F4HM-D	<b>7-16 to 4.3-10 adaptors:</b> TA-DFHM, TA-DMHF, TA-DMHM, TA-DMHM-K  <b>N-Type to 4.3-10 adaptors:</b> TA-NFHF, TA-NFHM, & TA-NMHF	CPT-F4-D, SMALL-CAPKIT SMALL-M-CAPKIT TT-4310* TW-4310
FSJ4RK-50B				
AL4RPV-50	L4-HMDM-X-SGW-D, L4-HMHM-X-SGW-D, L4-HMHR-X-SGW-D	L4HM-D		CPT-L4-D, SMALL-CAPKIT SMALL-M-CAPKIT TT-4310* TW-4310
HL4RPV-50				
LDF4-50A				
LDF4RK-50A				
<b>7/8"</b>				
AVA5-50	Factory terminated 7/8" cable assemblies are not available. For 7/8" cable assembly request, purchase your choice of bulk 7/8" cable and field fit 4.3-10 connectors.	A5HF-D & A5HM-D	<b>7-16 to 4.3-10 adaptors:</b> TA-DFHM, TA-DMHF, TA-DMHM, TA-DMHM-K  <b>N-Type to 4.3-10 adaptors:</b> TA-NFHF, TA-NFHM, & TA-NMHF	MCPT-A5-D, SMALL-CAPKIT SMALL-M-CAPKIT TT-4310* TW-4310
AVA5RK-50				SMALL-CAPKIT SMALL-M-CAPKIT TT-4310* TW-4310

\*4.3-10 coupling nut tightening tool. For use with HELIAX Jumpers equipped with factory fitted 4.3-10 connectors.

Visit our [4.3-10 Portfolio Page](#) to learn more.