



LightCrimp®, LightCrimp Plus™ Fiber Optic Deluxe Termination Kit SC /ST, with Microscope

OBSOLETE

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber tool kit
Product Brand	LightCrimp Plus™   LightCrimp®
Product Series	LightCrimp

General Specifications

Interface	LC   SC   ST
-----------	--------------

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Included	0.3um white film   200X Microscope kit with 2.5mm adapter cap   5um light gray film   Alcohol fiber wipes   Ball and hex key   Carrying case   Die set, front and rear lightcrimp   Fiber cleaver   Instruction sheet   Kevlar cutter   LC+ LC/SC cable holder   Miller dual-hole strip tool   Polishing pad   Polishing plate 8.5X11 in   Pro-crimper, LC+ LC/SC/Splice   Resilient polishing pad   SC polishing bushing   ST cable-buffer holder   ST polishing bushing   Slitter tool, 2 mm and 3 mm   Strip length template   Stripper, micro-strip W/.008BLA   Universal 1.25mm microscope adapter   Wrench, open end ¼
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>

ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

- |           |   |   |
|-----------|---|---|
| 1754765-1 | – | Fiber Optic Universal 1.25 mm Adapter for Hand-held Inspection Microscope |
| 1754767-1 | – | Fiber Optic Hand-held Inspection Microscope                               |
| 760243578 | – | Fiber Optic Hand Held Precision Cleaver Tool                              |



Fiber Optic Universal 1.25 mm Adapter for Hand-held Inspection Microscope

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber inspection microscope adapter

General Specifications

Color	Black
-------	-------

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





Fiber Optic Hand-held Inspection Microscope

- High quality glass optics with 200x magnification and an impact resistant ergonomic rubber shell
- Dual illumination lighting and IR-Laser attenuation filter and 500um Field of View (FOV)
- Protected by a padded carrying case with an integrated belt loop and internal adapter storage pocket

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber inspection microscope

General Specifications

Color	Black
-------	-------

Dimensions

Height	31.5 mm   1.24 in
Width	51.6 mm   2.031 in
Length	186.9 mm   7.358 in

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
Weight, net	0.318 kg   0.7 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant





Fiber Optic Hand Held Precision Cleaver Tool

- Provides operator-independent precision quality cleaves in a hand held size
- Includes a blade knife with a 48,000 cleave lifetime
- Suited for field installable mechanical splice connectors, bare fiber adapters and fusion and mechanical splicing
- Supplied with a padded belt case with neck lanyard for convenience and storage

Product Classification

Regional Availability	Asia   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber tool kit

Dimensions

Height	46 mm   1.811 in
Width	53 mm   2.087 in
Length	55 mm   2.165 in

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

Packaging and Weights

Packaging quantity	1
Weight, net	500 g   1.102 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

